



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 30165 Twister Al/Cu Wire Conn, Model 65, Purple, 25/Card

*Ideal*

Catalog Number	30165
Manufacturer	Ideal
Description	Wire Connector, Insulated, Purple Insulation Color, 2 to 3 (Aluminum to Copper);1 to 6 (Copper to Copper) Conductors, 600 V Ac, 0.01 LB
Weight per unit	0.0100 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts)

### Features

Material	Flame-retardant Polypropelene
Voltage Rating	600
Wire Type	ALUMINUM/COPPER

### Material, Color, and Finish

Color	Purple
-------	--------

### Descriptions

Description	TWISTER AL/CU WIRE CONN, MODEL 65,PURPLE, 25/CARD
extra long description	IDEAL 30-165 MODEL 65, PURPLE, 25 C
Features	The only twist-on for aluminum-to-copper connections.The Twister AL/CU Wire Connector is the only UL Listed aluminum-to-copper twist-on connector that prevents aluminum oxidation while providing a secure connection. Filled with an anti-oxidant compound, the Twister AL/CU easily twists on with swept-wings making a comfortable connection with improved conductivity and cooler connections.The live-action spring expands and contracts with aluminum wire to ensure a secure connection while the hexagonal head make

### Manufacturer Information

Brand	Ideal
GTIN	00783250301652
UPC	783250301652

### Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
----------------------	-----------

### Availability

minimum qty	25
-------------	----

### Packaging

Carton	25
Package	125
Weight Per each	0.01



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more aluminum to copper conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F)
standard	CSA C22.2 #188, UL 486C Listed, UL 467 for grounding and bonding,RoHS