

LED **HIGH BAY FIXTURES** LIGHTING THE FUTURE

Superior Life® LED Bay Fixtures are high quality, with elegant industrial design, They consume up to 80% less energy, significantly reducing operating costs and are environmentally friendly. The construction allows excellent heat dispersion and convenient installation.

- BRIGHT AND CONSISTENT
- Uniform light distribution and high lumen output.
- LONG LIFE

There is no need for frequent maintenance which make them ideal for hard to reach areas.

· NO DELAY, QUICK START UP Instant-On, No Flickering or Humming

- REDUCED HEAT OUTPUT
- VIBRATION AND WATER RESISTANT
- · ECO-FRIENDLY, MERCURY FREE
- · COMPACT DESIGN
- SIMPLE INSTALLATION



552XX / 553XX



55222 / 55223



55187



9037X / 9038X



90410 / 90414



90414-ACY



90414-ALU



90383

Key: DIMM = Dimmable / SL = Superior Life® / LM = Lumens

NOTE: Not all product variations listed on the next page are DLC qualified. Visit www.designlights.org/search to confirm qualification. • Published lumens on LED products are approximate and may vary slightly.





















ITEM#	DESCRIPTION	WATT	CCT	LM	LM/W	BEAM	CRI	VOLTS	HOUSING	LIFE	CASI
LED FLAT	T HIGH BAY - 120-277V										
55225	LED FLAT 2' HIGH BAY 90W/40K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SL° DLC	90	40K	11700	130	120°	80	120-277	WHITE	50K	1
55226	LED FLAT 2' HIGH BAY 90W/50K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SL® DLC	90	50K	11790	131	120°	80	120-277	WHITE	50K	1
55222	LED FLAT 2' HIGH BAY 105W/40K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SL® DLC	105	40K	13650	130	120°	82	120-277	WHITE	50K	1
55223	LED FLAT 2' HIGH BAY 105W/50K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SL® DLC	105	50K	13755	131	120°	82	120-277	WHITE	50K	1
55227	LED FLAT 2' HIGH BAY 162W/40K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SL® DLC	162	40K		130	120°	80	120-277	WHITE	50K	1
55228	LED FLAT 2' HIGH BAY 162W/50K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SL® DLC	162		21222	131	120°	80	120-277	WHITE	50K	1
55230	LED FLAT 4' HIGH BAY 223W/40K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SL® DLC	223		28990	130	120°	80	120-277	WHITE	50K	1
55231	LED FLAT 4' HIGH BAY 223W/50K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SL® DLC		50K		131	120°	80	120-277	WHITE	50K	1
55232	LED FLAT 4' HIGH BAY 321W/50K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SL® DLC	321	50K		131	120°	80	120-277	WHITE	50K	1
	ICY KITS FOR 120-277V FLAT HIGH BAYS	JLI	JUIN	42001	101	120	00	120 211	WIIIIL	JUIL	•
55319	EMERGENCY PACK FOR LED FIXTURE 8W/90 MIN										1
55320	EMERGENCY PACK FOR LED FIXTURE 16W/90 MIN										1
55321	EMERGENCY PACK FOR LED FIXTURE 25W/90 MIN										1
	FHIGH BAY - 347-480V										
55360	LED FLAT 2' HIGH BAY 110W/40K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SL® DLC	110	40K	14300	130	120°	80	347-480	WHITE	50K	1
55361	LED FLAT 2' HIGH BAY 110W/50K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SE DLC	110		14410	131	120°			WHITE	50K	1
55362	LED FLAT 2' HIGH BAY 162W/40K/FR LENS/V-HOOKS & 41.3' CHAINS/DIMM - SL* DLC	162		21060	130	120°	80	347-480	WHITE	50K	1
55363	LED FLAT 2' HIGH BAY 162W/50K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SL* DLC	162		21222	131	120°			WHITE	50K	1
55364	LED FLAT 2' HIGH BAY 102W/30K/FR LENS/V-HOOKS & 41.3' CHAINS/DIMM - SL® DLC	223		28990	130	120°	80	347-480	WHITE	50K	1
55365	LED FLAT 4' HIGH BAY 223W/40N/FR LENS/V-HOOKS & 41.3' CHAINS/DIMM - SL® DLC			29213	131	120°		347-480	WHITE	50K	1
55366	LED FLAT 4' HIGH BAY 321W/40K/FR LENS/V-HOOKS & 41.3" CHAINS/DIMM - SL* DLC	321		41730	130	120°	80	347-480	WHITE	50K	•
55367	LED FLAT 4' HIGH BAY 321W/50K/FR LENS/V-HOOKS & 41.3' CHAINS/DIMM - SL® DLC	321		42051	131	120°		347-480	WHITE	50K	1
		JZI	JUK	42001	131	120	00	347-400	WHILE	JUK	- 1
	RIES FOR FLAT HIGH BAYS										- 1
55205	WIRE GUARD WITH CLIPS FOR LED FLAT 2' HIGH BAY - for 90W										1
55211	WIRE GUARD WITH CLIPS FOR LED FLAT 2' HIGH BAY - for 162W										1
55216	WIRE GUARD WITH CLIPS FOR LED FLAT 4' HIGH BAY - for 223W										1
55218	WIRE GUARD WITH CLIPS FOR LED FLAT 4' HIGH BAY - for 321W										1
55220 55221	3.3" PENDANT MOUNT FOR STANDARD FLAT HIGH BAY (1/2" THREADED HOLE)										1
	6" PENDANT MOUNT FOR 480V FLAT HIGH BAY (1/2" THREADED HOLE)										1
LED HIGH		00	401/	11700	100	1000	00	100 077	\A/I IITE	F01/	-
55187	LED 1x4 LOUVERED HIGH BAY/90W/40K/120-277V/DIMMABLE - SL® DLC	90	40K	11700	130	120°	80	120-277	WHITE	50K	1
90410	LED 60W HIGH BAY HOUSING/41K/100-277V - SL®	60	41K	6050	101	110°	75	100-277	SILVER	50K	4
90414	LED 100W HIGH BAY HOUSING/40K/100-277V/DIMMABLE - SL®	100	40K	10200	102	110°	75	100-277	SILVER	50K	4
90414-ACY		96	40K	10675	111	110°	73	100-277	SILVER	50K	4
	LED 96W HIGH BAY HOUSING/14" ALUMINUM REF/40K/100-277V/DIMM - SL° DLC	96	40K	11088	115	110°	73	100-277	SILVER	50K	4
	RIES FOR HIGH BAYS										
90400	16" ACRYLIC REFLECTOR FOR LED HIGH BAY - for 90410 and 90414										8
90402	14" ALUMINUM REFLECTOR FOR LED HIGH BAY - for 90410 and 90414										8
	PASS HIGH BAY		===:			1000			DI 1011		
90375	LED COMPASS HIGH BAY 100W/50K/100-277V/DIMMMABLE - SL®	102	50K		141	120°		100-277	BLACK	50K	1
90377	LED COMPASS HIGH BAY 150W/50K/100-277V/DIMMMABLE - SL®	150	50K		140	120°	83	100-277	BLACK	50K	1
90379	LED COMPASS HIGH BAY 200W/50K/100-277V/DIMMMABLE - SL® DLC	204		25798	126	120°	82	100-277	BLACK	50K	1
90381	LED COMPASS HIGH BAY 240W/50K/100-277V/DIMMMABLE - SL®	242	50K		132	120°	82	100-277	BLACK	50K	1
90383	LED COMPASS HIGH BAY 300W/50K/100-277V/DIMMMABLE - SL® DLC	300	50K		131	120°	82	100-277	BLACK	50K	1
90385	LED COMPASS HIGH BAY 400W/50K/100-277V/DIMMMABLE - SL® DLC	391		49526	126	120°	82	100-277	BLACK	50K	1
90387	LED COMPASS HIGH BAY 500W/50K/100-277V/DIMMMABLE - SL® DLC	511	50K	64837	127	120°	82	100-277	BLACK	50K	1
ACCESSO	RIES FOR COMPASS HIGH BAYS										
	ADJUSTABLE ANGLE MOUNTING BRACKET FOR COMPASS HIGH BAY - SL®										20
90372											
90372	MICROWAVE MOTION SENSOR FOR COMPASS HIGH BAY/100-277V 1-10V DIMMING/KIT										10
	MICROWAVE MOTION SENSOR FOR COMPASS HIGH BAY/100-277V 1-10V DIMMING/KIT 16" ALUMINUM REFLECTOR FOR COMPASS HIGH BAY - SL®										10 20
90370											

Key: DIMM = Dimmable / SL = Superior Life* / LM = Lumens

 $\textbf{\textit{NOTE:}} \ \textit{Not all product variations listed on this page are DLC qualified. Visit www.designlights.org/search to confirm a page of the page of$ qualification. • Published lumens on LED products are approximate and may vary slightly.















