



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

132 Professional Dr.  
72023-0000, AR Cabot  
Phone: 501-605-1780  
Fax: 501-605-1785



## 65221 Led Security Light W/Sensor Black 4000K

Satco

Catalog Number	65221
Manufacturer	Satco
Description	Led Security Light - Dual Head Black Finish 4000K Motion Sensor
Weight per unit	2.8 (lbs/each)
Product Category	Security Lights

### Features

amperage rating	0.167
Ballast Type	Self
Lamp Type	LED
Material	Die Cast Aluminum
Number of Lamps	2
Power Rating	0.9
Reflector Type	Frost
Socket Type	Integrated
Voltage Rating	120
Warranty	5 Year Limited - Fixtures
Wattage	20

### Material, Color, and Finish

fixture material	die-cast aluminum
Style	Utility

### Dimensions and Weight

Height	7.63
Length	7.63
Size	L:7.63 W:4.16 H:4.13
Width	4.16

### Descriptions

Description	LED SECURITY LIGHT W/SENSOR BLACK 4000K
extra long description	SATCO 65/221 2ED DUAL HEAD SECURITY
Long Description	LED Security Light - Dual Head Black Finish 4000K Motion Sensor
Product Type	2ED Dual Head Security Light
Special Features	Warranty: 5-Years ; FCC Compliant: True ; Photo Cell: Has Motion Sensor ; Cct Selectable: False ; CCT (Kelvin Temp): 4000K ; Hours Rated: 50000 ; Beam Angle (degree): 50 ; Indoor Outdoor: Outdoor ; IP Rating: IP65 ; Lens Finish: Frost ; Lens Material: Glass ; Operating Temp: -30C (-22F) to +50C (+122F) ; Watts: 20W ; Lumens: 1900L



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

132 Professional Dr.  
72023-0000, AR Cabot  
Phone: 501-605-1780  
Fax: 501-605-1785

## Manufacturer Information

Brand	Nuvo
GTIN	00045923680397
Manufacturers Part Number	65/221
UPC	045923680397

## Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Commercial LED

## Packaging

Carton	1
Weight	2.8
Weight Per each	2.8

## Uses, Certifications, and Standards

Application	Outdoor
environmental conditions	Wet
Frequency Rating	50/60
Operating Temperature standard	-30C (-22F) to a maximum of +50C (+122F) cULus - Certified