

# Weather-Resistant Receptacle

3232TRWR



Residential Weather-Resistant Receptacles are Tamper-Resistant as required by 2008 National Electrical Code. Listed to the Weather-Resistant supplement of UL498, meeting demanding UL requirements including: Ultraviolet light exposure test; Cold impact test; Accelerated aging test; Stringent material requirements for current-carrying parts, wire binding screws and mounting straps to ensure superior corrosion resistance.



## features & benefits

- WR markings on face per UL Weather-Resistant requirements.
- Patented internal shutter system lets plugs in, but keeps keys and other objects out with automatic shutters that block access.
- Side wire accepts #12 – #14 AWG solid wire. Push wire accepts #14 AWG solid only.
- Low profile face. Traditional contoured face. High-impact resistant thermoplastic construction.
- Safer and more effective than plastic outlet caps. TR markings identify devices as Tamper-Resistant.

## specifications

### General Info

Color: Brown  
Type: Duplex  
Number Of Poles: 2  
Number Of Wires: 3  
Special Features: Weather-Resistant

### Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42  
CSA Standard: Yes  
cULus: Yes  
Federal Spec: No  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121406

**Dimensions**

Depth U S: 1"  
Height U S: 3.31"  
Width U S: 1.32"

**Technical Information**

Amps: 15 Amp  
Volts: 125  
Volts A C: 125

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant