



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

217 Innovation Way
37075-0000, TN Hendersonville
Phone: 615-991-2399
Fax: 000-000-0000



690 Combo 2SWITCHES 1POLE 15A120/277V BN

Pass & Seymour/Legrand

Catalog Number	690
Manufacturer	Pass & Seymour/Legrand
Description	P&S 690 Combo 2SWITCHES 1POLE 15a12
Weight per unit	0.2110 (lbs/each)
Product Category	Combination Devices

Features

action	(2) SP
actuator	Toggle
amperage rating	15
connection	Side wire, non-grounding
Contact Configuration	N-O
Contact Rating	15amp, 120/277vac
operating cycles	30000
Poles	1
Voltage	0.433 V
Voltage Rating	0.43321299639
Wattage	Electrical power is expressed in Amps and Volts.

Material, Color, and Finish

Color	Brown
-------	-------

Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

Descriptions

Description	COMBO 2SWITCHES 1POLE 15A120/277V BN
Long Description	P&S 690 COMBO 2SWITCHES 1POLE 15A12
Product Type	Combo 2SWITCHES 1POLE 15A120/277V BN
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one.

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007690019
UPC	785007690019

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Non-Grounding Combination Two Single Pole Switches

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

217 Innovation Way
37075-0000, TN Hendersonville
Phone: 615-991-2399
Fax: 000-000-0000

Availability

Manufacturer Status Inactive

Status Inactive

Packaging

Carton 1

Package 10

Weight Per each 0.211

Uses, Certifications, and Standards

Application Residential/Commercial

environmental conditions Flammability: UL94 V2

Mounting WALL

Operating Temperature Maximum continuous +60°C, minimum -30°C

standard CULUS, UL20