



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 692WG Combo SW 1P 15A120V Pilot LT 1/25 GRD WH

*Pass & Seymour/Legrand*

Catalog Number	692WG
Manufacturer	Pass & Seymour/Legrand
Description	Single-Pole, Single Pilot Light, Combination Switch, 15A, 120/125AS, White.
Weight per unit	0.2133 (lbs/each)
Product Category	Combination Devices

### Features

action	SP & Pilot Light
actuator	Toggle
amperage rating	15
connection	Side wire
Contact Configuration	N-O
Contact Rating	15 Amp, 120/125 VAC
operating cycles	30k.0
Poles	1
Voltage	120/125 V
Voltage Rating	120/125
Wattage	Pilot Light: 1/25
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

### Descriptions

Description	COMBO SW 1P 15A120V PILOT LT 1/25 GRD WH
extra long description	P&S 692WG COMBO SW 1P 15A120V PILOT
Features	Combination
Long Description	Single-Pole, Single Pilot light, Combination Switch, 15A, 120/125As, White.
Product Type	Combo SW 1P 15A120V Pilot LT 1/25 GRD W
Special Features	Easily accessible break-off for separate or common feed. Long-life red neon lamp in pilot light rated 1/25 Watt, 125V. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007006117
Manufacturers Part Number	692-WG
UPC	785007006117

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	COMBINATION

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	10
Package	50
Weight Per each	0.2133

## Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature	Maximum continuous +60°C, minimum -30°C
standard	CULUS, UL20