



Product Number: 16125

Order Abbreviation: 50PAR30/HAL/S/NFL25 120V

General Description: Tungsten Halogen PAR30 Silver Reflector Lamp 50Watt 120Volt Medium Base NarrowFlood25 Beam

*** Full Case Required**

Product Information

| | |
|-----------------------------------|-----------------------------------|
| Abbrev. With Packaging Info. | 50PAR30HALSNFL25 120V 10/CS 1/SKU |
| Approx. Lumens | 850 |
| Average Rated Life (hr) | 1500 |
| Base | E26 Medium |
| Beam Angle (deg) | 25 |
| Beam Type | NFL |
| Bulb | PAR30 |
| Centerbeam Candlepower (cp) | 2600 |
| Class | C (gas) |
| Color Rendering Index (CRI) | 99 |
| Color Temperature/CCT (K) | 2875 |
| Diameter (in) | 3.752 |
| Diameter (mm) | 95.30 |
| Ecologic | YES |
| Family Brand Name | Halogen Par30 |
| Filament | CC-8 |
| Horizontal Beam Angle (deg) | 25 |
| Lamp Finish | Reflector |
| Maximum Overall Length - MOL (in) | 3.625 |
| Maximum Overall Length - MOL (mm) | 92.075 |
| Nominal Voltage (V) | 120.00 |
| Nominal Wattage (W) | 50.00 |
| Vertical Beam Angle (deg) | 25 |



Footnotes

- State of the Art SPL Optics
- In base up operation, heat may eventually deteriorate paper-lined or plastic sockets.



Product Number: 16125

Order Abbreviation: 50PAR30/HAL/S/NFL25 120V

General Description: Tungsten Halogen PAR30 Silver Reflector Lamp 50Watt 120Volt Medium Base NarrowFlood25 Beam

*** Full Case Required**

Product Information

| | |
|-----------------------------------|-----------------------------------|
| Abbrev. With Packaging Info. | 50PAR30HALSNFL25 120V 10/CS 1/SKU |
| Approx. Lumens | 850 |
| Average Rated Life (hr) | 1500 |
| Base | E26 Medium |
| Beam Angle (deg) | 25 |
| Beam Type | NFL |
| Bulb | PAR30 |
| Centerbeam Candlepower (cp) | 2600 |
| Class | C (gas) |
| Color Rendering Index (CRI) | 99 |
| Color Temperature/CCT (K) | 2875 |
| Diameter (in) | 3.752 |
| Diameter (mm) | 95.30 |
| Ecologic | YES |
| Family Brand Name | Halogen Par30 |
| Filament | CC-8 |
| Horizontal Beam Angle (deg) | 25 |
| Lamp Finish | Reflector |
| Maximum Overall Length - MOL (in) | 3.625 |
| Maximum Overall Length - MOL (mm) | 92.075 |
| Nominal Voltage (V) | 120.00 |
| Nominal Wattage (W) | 50.00 |
| Vertical Beam Angle (deg) | 25 |



Footnotes

- State of the Art SPL Optics
- In base up operation, heat may eventually deteriorate paper-lined or plastic sockets.