




1, 2 & 3 GANG TOGGLE COVERS

**Two Gang Device Mount Switch Cover
(2) SP 125V, 15A**

D21



Catalog #: 5124-0

APPLICATIONS

For use whenever weatherproof protection is required for an "on-off" type switch
N/A

PRODUCT FEATURES

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- Most units supplied with a switch(es) - no need to purchase separate components
- Switch/cover units are supplied with the switch unassembled to the cover

UL LISTED

File E 195978

CSA

Certified

NEMA

3R Rated

GENERAL PRODUCT INFORMATION

Color: Gray

CONFIGURATION

Gangs: 2

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.495

PACKAGING

Package Type: Shrink
 Std. Pkg.: 8
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 49.50
 Ship Carton Length (in.): 10.56
 Ship Carton Width (in.): 6.50
 Ship Carton Height (in.): 8.50
 Ctn Weight (Lbs.): 3.96
 Pallet Qty: 1120.00
 UPC Number: 050169512401
 I2of5: 50050169512406