

Straight Blade Plugs & Connectors

Extra-Hard Use

15 & 20A, 125 & 250V

Ordering Information

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.
Plugs & Connectors				
5266-X	15 125	Plug, Black & White	.230"-.690"	5-15P
5266-XGRY	15 125	Plug, Black & Gray	.230"-.690"	5-15P
5266-XBK	15 125	Plug, Black	.230"-.690"	5-15P
CR5266-X	15 125	Plug, Corrosion-Resistant, Yellow & White	.230"-.690"	5-15P
5269-X	15 125	Connector, Black & White	.230"-.690"	5-15R
5269-XGRY	15 125	Connector, Black & Gray	.230"-.690"	5-15R
5269-XBK	15 125	Connector, Black	.230"-.690"	5-15R
CR5269-X	15 125	Connector, Corrosion-Resistant, Yellow & White	.230"-.690"	5-15R
5366-X	20 125	Plug, Black & White	.230"-.690"	5-20P
5369-X	20 125	Connector, Black & White	.230"-.690"	5-20R
5666-X	15 250	Plug, Black & White	.230"-.690"	6-15P
5669-X	15 250	Connector, Black & White	.230"-.690"	6-15R
5466-X	20 250	Plug, Black & White	.230"-.690"	6-20P
5469-X	20 250	Connector, Black & White	.230"-.690"	6-20R



NEMA
5-15R



NEMA
5-15P



NEMA
6-15R



NEMA
6-15P



NEMA
5-20R



NEMA
5-20P



NEMA
6-20R



NEMA
6-20P

For more information on these and other P&S products refer to our Product Guide or visit our web site.

Straight Blade Plugs & Connectors


Extra-Hard Use

15 & 20A, 125 & 250V



Technical Specifications

3rd Party Compliance	
UL Listed, File Number E146159, Standard UL498, Attachment Plugs and Receptacles. Federal Specification WC596.	
CSA Certified, File Number LR1765, Standard CSA-C22.2 No. 42, General Use Receptacles and Attachment Plugs.	
Conforms to NEMA WD-1.	



**Dimensions for
15 & 20 Amp Plug**

Performance	
Electrical	
Dielectric Withstand Voltage	1500V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	30°C maximum after 50 cycles at 150% rated current
Mechanical	
Cord Accommodations	Round portable service cords of diameters in accordance with the device rating as defined in UL62
Cord Grip Accommodations	.230" – .690" diameter
Terminal Identification	Green = Ground, White = Neutral, Brass = Hot
Terminal Accommodation	#18 AWG min. – #10 AWG max.
Product Identification	Amperage, Voltage, 3rd Party Compliance, NEMA Configuration
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +75°C, minimum -40°C without impact



**Dimensions for
15 & 20 Amp Connector**

Materials			
Back Body	Nylon	Connector Contacts	* Brass
Front Body	Nylon	Terminal Clamp	* Zinc-Plated Steel
Terminal Chamber	Polycarbonate	Terminal Screws	Nickel- or Brass-Plated Steel
Cord Clamp	Nylon	Ground Screws	Nickel-Plated Steel
Insert	Nylon	Cord Clamp Screws	Nickel-Plated Steel
Plug Blades	* Brass	Assembly Screws	Nickel-Plated Steel

*Nickel-Plated for Corrosion-Resistant product.

NEMA Config.	AC HP Rating	NEMA Config.	AC HP Rating
Straight Blade Horsepower Rating for NEMA Configuration Attachment Plugs & Receptacles			
5-15	1/2	5-20	1
6-15	1-1/2*	6-20	2*

*Suitable for 208V motor applications at the HP rating specified.

Warranty

1 Year

Straight Blade Plugs & Connectors

Extra-Hard Use

15 & 20A, 125 & 250V

Ordering Information

Catalog Number	Rating A. V.	Description/Color	Cord Diameter	NEMA Config. No.
Plugs & Connectors				
5266-X	15 125	Plug, Black & White	.230"-.690"	5-15P
5266-XGRY	15 125	Plug, Black & Gray	.230"-.690"	5-15P
5266-XBK	15 125	Plug, Black	.230"-.690"	5-15P
CR5266-X	15 125	Plug, Corrosion-Resistant, Yellow & White	.230"-.690"	5-15P
5269-X	15 125	Connector, Black & White	.230"-.690"	5-15R
5269-XGRY	15 125	Connector, Black & Gray	.230"-.690"	5-15R
5269-XBK	15 125	Connector, Black	.230"-.690"	5-15R
CR5269-X	15 125	Connector, Corrosion-Resistant, Yellow & White	.230"-.690"	5-15R
5366-X	20 125	Plug, Black & White	.230"-.690"	5-20P
5369-X	20 125	Connector, Black & White	.230"-.690"	5-20R
5666-X	15 250	Plug, Black & White	.230"-.690"	6-15P
5669-X	15 250	Connector, Black & White	.230"-.690"	6-15R
5466-X	20 250	Plug, Black & White	.230"-.690"	6-20P
5469-X	20 250	Connector, Black & White	.230"-.690"	6-20R



NEMA
5-15R



NEMA
5-15P



NEMA
6-15R



NEMA
6-15P



NEMA
5-20R



NEMA
5-20P



NEMA
6-20R



NEMA
6-20P

For more information on these and other P&S products refer to our Product Guide or visit our web site.

Straight Blade Plugs & Connectors

Extra-Hard Use


15 & 20A, 125 & 250V



Technical Specifications

3rd Party Compliance

UL Listed, File Number E146159, Standard UL498, Attachment Plugs and Receptacles. Federal Specification WC596.
 CSA Certified, File Number LR1765, Standard CSA-C22.2 No. 42, General Use Receptacles and Attachment Plugs.
 Conforms to NEMA WD-1.



**Dimensions for
15 & 20 Amp Plug**

Performance

Electrical	
Dielectric Withstand Voltage	1500V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	30°C maximum after 50 cycles at 150% rated current
Mechanical	
Cord Accommodations	Round portable service cords of diameters in accordance with the device rating as defined in UL62
Cord Grip Accommodations	.230" – .690" diameter
Terminal Identification	Green = Ground, White = Neutral, Brass = Hot
Terminal Accommodation	#18 AWG min. – #10 AWG max.
Product Identification	Amperage, Voltage, 3rd Party Compliance, NEMA Configuration
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +75°C, minimum -40°C without impact



**Dimensions for
15 & 20 Amp Connector**

Materials

Back Body	Nylon	Connector Contacts	* Brass
Front Body	Nylon	Terminal Clamp	* Zinc-Plated Steel
Terminal Chamber	Polycarbonate	Terminal Screws	Nickel- or Brass-Plated Steel
Cord Clamp	Nylon	Ground Screws	Nickel-Plated Steel
Insert	Nylon	Cord Clamp Screws	Nickel-Plated Steel
Plug Blades	* Brass	Assembly Screws	Nickel-Plated Steel

*Nickel-Plated for Corrosion-Resistant product.

NEMA Config.	AC HP Rating	NEMA Config.	AC HP Rating
Straight Blade Horsepower Rating for NEMA Configuration Attachment Plugs & Receptacles			
5-15	1/2	5-20	1
6-15	1-1/2*	6-20	2*

*Suitable for 208V motor applications at the HP rating specified.

Warranty

1 Year