

Utility Hand Tools

Klein® manufactures the highest quality tools in the industry, supporting linemen and utility workers around the world with premium products—quality and reliability you can count on every day.



**KLEIN
TOOLS**®

Ratcheting Cable Cutter

ACSR



Quick-release lever opens blade at any time during operation.

Unique ratchet action holds cable tight and allows rapid, straight cuts with minimum effort.

ACSR Cable Cutter
(63607)



Cleanly cuts 336 MCM Linnet ACSR and 2/0 triplex steel messenger cable.

- High leverage ratchet mechanism for single-handed cutting of copper and aluminum cables, leaving no burrs or sharp edges.
- Patented two-step ratchet mechanism requires fewer strokes per cut.
- Precision ratcheting mechanism holds cable tight and allows rapid, straight cuts with minimum effort.
- Hardened steel cutting blades for lasting strength and sharpness.
- One-year warranty.

63607

MCM Maximum Cable Capacity

Cat. No.	Copper	Aluminum	Communication Cable	ACSR	Overall Length	Handle Color	Weight (lbs.)
63607	400 MCM (185 mm ²)	600 MCM (300 mm ²)	–	336 MCM (170 mm ²)	10-1/4" (260 mm)	yellow	1.50 (.68 kg)

All dimensions are in inches and (millimeters).

WARNING: Always wear approved eye protection.

WARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.



Lineman's Wrenches

Ratcheting 5-in-1 Lineman's Wrenches

- Bolt-through design allows bolts to pass through the socket.
- 3/4" and 1" x 1-1/8" combination square socket for most common utility hardware.
- Features two popular wrench sizes: 9/16" and 3/4".



Cat. No.	Description	Length	Weight (lbs.)
KT155HD	Ratcheting Lineman's Wrench Heavy-Duty	12" (305 mm)	2.10 (.95 kg)
KT155T	Ratcheting Lineman's Wrench Compact	9-3/8" (238 mm)	1.42 (.64 kg)



⚠WARNING: Never use on or near live electrical circuits.

Lineman's Insulating 4-in-1 and Ratcheting Box Wrench

- Chrome plated finish resists corrosion.
- "See-through" insulating handle confirms metal ends are not connected (Cat. No. KT223X4-INS).
- 1/2", 9/16", 5/8" and 3/4" sizes in one tool; 12-point sockets.
- Reverse ratcheting action by reversing switches on each end of the wrench.

Cat. No.	Description	Socket Size	Length	Weight (lbs.)
KT223X4-INS	Insulating Lineman's Ratcheting Box Wrench	1/2", 9/16", 5/8" & 3/4"	9" (229 mm)	.70 (.32 kg)
KT223X4	Lineman's Ratcheting Box Wrench	1/2", 9/16", 5/8" & 3/4"	9" (229 mm)	.70 (.32 kg)

All dimensions are in inches and (millimeters).

⚠WARNING: Always wear approved eye protection.

⚠WARNING: Do NOT push or hammer wrench.

⚠WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

⚠WARNING: Do NOT extend handle length.



Specialty Wrenches

3-in-1 Impact Socket

- Includes 3/4" (also works with 13/16"), 1" and 1-1/8" square sizes.
- 7/16" hex quick-change adapter included.
- Improved ball detent on socket adapter.
- 13/16" diameter, 6" long hollow shaft allows use on long threaded bolts.

Cat. No.	Description	Length	Weight (lbs.)
NRHD	3-in-1 Impact Socket	7-3/4" (197 mm)	2.0 (.91 kg)
Replacement Parts			
NRHDA	Impact Socket Adapter		



NRHD



NRHDA
Replacement Adapter

Cushion-Grip Screwdriver

Demolition Driver – Keystone-Tip Screwdrivers

- Plated metal strike cap to protect handle from hammer blows.
- Heat treated metal shaft runs complete length of handle to metal strike cap to transfer metal strike force.



602-4DD



602-7DD

Cat. No.	Tip Size	Blade Length	Overall Length	Weight (lbs.)
602-4DD	1/4"	4" (102 mm)	9" (229 mm)	.37 (.17 kg)
602-7DD	5/16"	7" (178 mm)	12-3/8" (314 mm)	.56 (.25 kg)

Utility Hand Tools

Lineman's Milled-Face Hammer

- One milled face for driving staples used in pole-line work and common, unhardened nails.
- Other face is smooth for driving heavier duty hardware.
- Rugged and well-balanced, with the weight to drive lag bolts.
- Forged, tempered-steel head is only 3-3/4" (95 mm) long for use in tight areas.



809-36MF



Milled-Face



Smooth face bends staples
Milled-face drives staples straight

Cat. No.	Head Weight	Overall Length	Weight (lbs.)
809-36MF	36 oz. (1021 g)	14" (356 mm)	2.50 (1.13 kg)

All dimensions are in inches and (millimeters).

▲WARNING: Always wear approved eye protection.

▲WARNING: Do NOT use on live conductors.

See our complete line of **Lineman Equipment and Accessories** at

www.kleintools.com



KLEIN TOOLS

