



## SAFETY DATA SHEET

### METACALK® MC 150+

General purpose firestop sealant

#### SECTION 1 – PRODUCT AND COMPANY INFORMATION

**Product Name**

Metacalk® MC 150+

**Product Codes**

66382, 66383, 66385, 66389, 66648

**Chemical Family**

Organic/Inorganic

**Use**

Firestopping sealant

**Manufacturer's Name**

The RectorSeal Corporation  
2601 Spenwick Drive  
Houston, Texas 77055 USA

**Date of Validation**

August 21, 2017

**Date of Preparation**

August 21, 2017

**HMIS Codes**

Health	1
Flammability	0
Reactivity	0
PPI	B

**Emergency Telephone No.**

Chemtrec 24 Hours  
(800)-424-9300 USA  
(703)-527-3887 International

**Technical Service Telephone No.**

(800)-231-3345 or (713)-263-8001

#### SECTION 2 – HAZARDS IDENTIFICATION

##### GHS CLASSIFICATION

**Physical Hazards:**

None

**Health Hazards**

**Acute Toxicity:**

Oral: Not Classified  
Dermal: Not Classified  
Inhalation: Not Classified  
Skin Corrosion/Irritation: Not Classified  
Serious Eye Damage/Eye Irritation: Not Classified  
Respiratory or Skin Sensitization: Not Classified  
Germ Cell Mutagenicity: Not Classified  
Carcinogenicity: Not Classified  
Reproductive Toxicology: Not Classified  
Target Organ Systemic Toxicity - Single Exposure: Not Classified  
Target Organ Systemic Toxicity - Repeated Exposure: Not Classified

Aspiration Toxicity: Not Classified

## ENVIRONMENTAL HAZARDS

Hazardous to the Aquatic Environment: Not Classified  
Acute aquatic toxicity: Not Classified  
Chronic aquatic toxicity: Not Classified  
Bioaccumulation potential: Not Classified  
Rapid degradability: Not Classified

## GHS Label elements, including precautionary statements

Pictogram: None

Signal Word: None

Hazard Statements:  
None

Precautionary Statements:  
P102 - Keep out of reach of children.  
P264 - Wash hands thoroughly after handling.

## Classification according to EU Directives 67/548/EEC or 1999/45/EC

Labeling Symbols: None

Risk R-Phrases: None

Safety S-Phrases:  
S2: Keep out of the reach of children.

## Summary Of Acute Hazards

May cause skin irritation.

## Route Of Exposure, Signs And Symptoms

### INHALATION

Not a respiratory irritant.

### EYE CONTACT

Contact may cause eye irritation.

### SKIN CONTACT

Contact may cause skin irritation.

### INGESTION

Possible irritation to mucous membranes of the mouth, throat, and stomach.

## SUMMARY OF CHRONIC HAZARDS

None known.

## MEDICAL CONDITIONS AGGRAVATED BY EXPOSURE

Persons with pre-existing skin conditions or chemical allergies may be more susceptible to contact effects of the cured elastomer.

## SECTION 3 – COMPOSITION/INFORMATION ON INGREDIENTS

% by WT

CAS No.    INGREDIENT    UNITS

None as defined by OSHA Hazard Communication Standard 29 CFR 1910.1200.

## SECTION 4 – FIRST AID MEASURES

- If inhaled: Not a respiratory irritant.
- If on skin: Wash with soap and water. If irritation occurs, seek medical attention.
- If in eyes: Immediately flush with large amounts of water. If irritation occurs, seek medical attention.
- If swallowed: If swallowed, call a physician immediately. Only induce vomiting at the instruction of a physician. Never give anything by mouth to an unconscious person.

## SECTION 5 – FIRE FIGHTING MEASURES

### Extinguishing Media

Foam, dry chemical, carbon dioxide or water fog.

**Special Fire Fighting Procedures:** Wear self-contained breathing apparatus (SCBA) and other protective clothing. Hazardous decomposition products possible (see Section 10).

**Unusual Fire And Explosion Hazards:** Heat may build up and rupture closed containers.

## SECTION 6 – ACCIDENTAL RELEASE MEASURES

**Steps To Be Taken In Case Material Is Released Or Spilled:** Wipe up spills to prevent footing hazard. Avoid flushing into sewers, drains, waterways and soil. Wear protective clothing during clean up.

## SECTION 7 – HANDLING AND STORAGE

**Precautions To Be Taken In Handling And Storing:** Keep container closed and upright when not in use. To prevent freezing and possible rupture of container, do not store below 35°F.

**Other Precautions:** Avoid prolonged or repeated contact with skin or clothing. Empty containers may contain residues and vapors; treat as if full and observe all product precautions. Do not reuse empty containers.

KEEP OUT OF REACH OF CHILDREN.

## SECTION 8 – EXPOSURE CONTROLS/PERSONAL PROTECTION

**Respiratory Protection (Specify Type):** None required.

**Ventilation – Local Exhaust:** N/A

**Special:** N/A

**Mechanical (General):** N/A

**Other:** N/A

**Protective Gloves:** None required.

**Eye Protection:** None required.

**Other Protective Clothing Or Equipment:** None required.

**Work/Hygienic Practices:** Where use can result in skin contact, wash exposed areas thoroughly before eating, drinking, smoking, or leaving work area. Launder contaminated clothing before reuse.

## SECTION 9 – PHYSICAL AND CHEMICAL PROPERTIES

Boiling point:	212°F (100°C) @ 760mm Hg
Specific gravity (H2O = 1):	1.5
Vapor pressure (mmHg):	17 @ 68°F (20°C)
Melting point:	N/A
Vapor Density (Air = 1):	N/A
Evaporation rate (Ethyl Acetate = 1):	> 1
Appearance/Odor:	Red paste/Mild odor
Solubility in water:	Soluble
Volatile Organic Compounds (VOC) Content (theoretical percentage by weight):	< 1% or (< 10 g/L)
Flash point:	None
Lower explosion limit:	None
Upper explosion limit:	None

## SECTION 10 – STABILITY AND REACTIVITY

**Stability:** Stable

**Conditions To Avoid:** None.

**Incompatibility (Materials To Avoid):** None known.

**Hazardous Decomposition Products:** CO, CO<sub>2</sub> and fragmented hydrocarbons.

**Hazardous Polymerization:** Will not occur.

SECTION 11 – TOXICOLOGY INFORMATION

**Chronic Health Hazards**

No ingredient in this product is an IARC, NTP or OSHA Lister carcinogen.

Toxicology Data

Ingredient Name

**None**

SECTION 12 – ECOLOGICAL INFORMATION

**Ecological Data**

Ingredient Name:	<b>None</b>
Food Chain Concentration Potential:	N/A
Waterfowl Toxicity:	N/A
BOD:	N/A
Aquatic Toxicity:	N/A

SECTION 13 – DISPOSAL CONSIDERATIONS

**Waste Classification:** Non-regulated solid waste

**Disposal Method:** Approved landfill

Waste from this product is not considered hazardous as defined under the Resource Conservation and Recovery Act (RCRA) 40 CFR 261. Dispose of in accordance with federal, state, and local regulation regarding pollution.

SECTION 14 – TRANSPORTATION INFORMATION

DOT:	Non-regulated
Ocean (IMDG):	Non-regulated
Air (IATA):	Non-regulated
WHMIS (Canada):	Non-regulated

## SECTION 15 – REGULATORY INFORMATION

### Regulatory Data

Ingredient Name:	<b>None</b>
SARA 313	N/A
TSCA Inventory	All components listed
CERCLA RQ	N/A
RCRA Code	N/A

## SECTION 16 – OTHER INFORMATION

This document is prepared pursuant to the OSHA Hazard Communication Standard (29 CFR 1910.1200). The information herein is given in good faith, but no warranty, expressed or implied is made.

Consult RectorSeal for further information: (713) 263-8001



## SAFETY DATA SHEET

### METACALK® MC 150+

General purpose firestop sealant

#### SECTION 1 – PRODUCT AND COMPANY INFORMATION

**Product Name**

Metacalk® MC 150+

**Product Codes**

66382, 66383, 66385, 66389, 66648

**Chemical Family**

Organic/Inorganic

**Use**

Firestopping sealant

**Manufacturer's Name**

The RectorSeal Corporation  
2601 Spenwick Drive  
Houston, Texas 77055 USA

**Date of Validation**

August 21, 2017

**Date of Preparation**

August 21, 2017

**HMIS Codes**

Health	1
Flammability	0
Reactivity	0
PPI	B

**Emergency Telephone No.**

Chemtrec 24 Hours  
(800)-424-9300 USA  
(703)-527-3887 International

**Technical Service Telephone No.**

(800)-231-3345 or (713)-263-8001

#### SECTION 2 – HAZARDS IDENTIFICATION

##### GHS CLASSIFICATION

**Physical Hazards:**

None

**Health Hazards**

**Acute Toxicity:**

Oral: Not Classified

Dermal: Not Classified

Inhalation: Not Classified

Skin Corrosion/Irritation: Not Classified

Serious Eye Damage/Eye Irritation: Not Classified

Respiratory or Skin Sensitization: Not Classified

Germ Cell Mutagenicity: Not Classified

Carcinogenicity: Not Classified

Reproductive Toxicology: Not Classified

Target Organ Systemic Toxicity - Single Exposure: Not Classified

Target Organ Systemic Toxicity - Repeated Exposure: Not Classified

Aspiration Toxicity: Not Classified

## ENVIRONMENTAL HAZARDS

Hazardous to the Aquatic Environment: Not Classified  
Acute aquatic toxicity: Not Classified  
Chronic aquatic toxicity: Not Classified  
Bioaccumulation potential: Not Classified  
Rapid degradability: Not Classified

## GHS Label elements, including precautionary statements

Pictogram: None

Signal Word: None

Hazard Statements:  
None

Precautionary Statements:  
P102 - Keep out of reach of children.  
P264 - Wash hands thoroughly after handling.

## Classification according to EU Directives 67/548/EEC or 1999/45/EC

Labeling Symbols: None

Risk R-Phrases: None

Safety S-Phrases:  
S2: Keep out of the reach of children.

## Summary Of Acute Hazards

May cause skin irritation.

## Route Of Exposure, Signs And Symptoms

### INHALATION

Not a respiratory irritant.

### EYE CONTACT

Contact may cause eye irritation.

### SKIN CONTACT

Contact may cause skin irritation.

### INGESTION

Possible irritation to mucous membranes of the mouth, throat, and stomach.

## SUMMARY OF CHRONIC HAZARDS

None known.

## MEDICAL CONDITIONS AGGRAVATED BY EXPOSURE

Persons with pre-existing skin conditions or chemical allergies may be more susceptible to contact effects of the cured elastomer.

## SECTION 3 – COMPOSITION/INFORMATION ON INGREDIENTS

% by WT

CAS No.

INGREDIENT

UNITS

None as defined by OSHA Hazard Communication Standard 29 CFR 1910.1200.



## SECTION 4 – FIRST AID MEASURES

- If inhaled: Not a respiratory irritant.
- If on skin: Wash with soap and water. If irritation occurs, seek medical attention.
- If in eyes: Immediately flush with large amounts of water. If irritation occurs, seek medical attention.
- If swallowed: If swallowed, call a physician immediately. Only induce vomiting at the instruction of a physician. Never give anything by mouth to an unconscious person.

## SECTION 5 – FIRE FIGHTING MEASURES

### Extinguishing Media

Foam, dry chemical, carbon dioxide or water fog.

**Special Fire Fighting Procedures:** Wear self-contained breathing apparatus (SCBA) and other protective clothing. Hazardous decomposition products possible (see Section 10).

**Unusual Fire And Explosion Hazards:** Heat may build up and rupture closed containers.

## SECTION 6 – ACCIDENTAL RELEASE MEASURES

**Steps To Be Taken In Case Material Is Released Or Spilled:** Wipe up spills to prevent footing hazard. Avoid flushing into sewers, drains, waterways and soil. Wear protective clothing during clean up.

## SECTION 7 – HANDLING AND STORAGE

**Precautions To Be Taken In Handling And Storing:** Keep container closed and upright when not in use. To prevent freezing and possible rupture of container, do not store below 35°F.

**Other Precautions:** Avoid prolonged or repeated contact with skin or clothing. Empty containers may contain residues and vapors; treat as if full and observe all product precautions. Do not reuse empty containers.

KEEP OUT OF REACH OF CHILDREN.

## SECTION 8 – EXPOSURE CONTROLS/PERSONAL PROTECTION

**Respiratory Protection (Specify Type):** None required.

**Ventilation – Local Exhaust:** N/A

**Special:** N/A

**Mechanical (General):** N/A

**Other:** N/A

**Protective Gloves:** None required.

**Eye Protection:** None required.

**Other Protective Clothing Or Equipment:** None required.

**Work/Hygienic Practices:** Where use can result in skin contact, wash exposed areas thoroughly before eating, drinking, smoking, or leaving work area. Launder contaminated clothing before reuse.

## SECTION 9 – PHYSICAL AND CHEMICAL PROPERTIES

Boiling point:	212°F (100°C) @ 760mm Hg
Specific gravity (H2O = 1):	1.5
Vapor pressure (mmHg):	17 @ 68°F (20°C)
Melting point:	N/A
Vapor Density (Air = 1):	N/A
Evaporation rate (Ethyl Acetate = 1):	> 1
Appearance/Odor:	Red paste/Mild odor
Solubility in water:	Soluble
Volatile Organic Compounds (VOC) Content (theoretical percentage by weight):	< 1% or (< 10 g/L)
Flash point:	None
Lower explosion limit:	None
Upper explosion limit:	None

## SECTION 10 – STABILITY AND REACTIVITY

**Stability:** Stable

**Conditions To Avoid:** None.

**Incompatibility (Materials To Avoid):** None known.

**Hazardous Decomposition Products:** CO, CO<sub>2</sub> and fragmented hydrocarbons.

**Hazardous Polymerization:** Will not occur.

## SECTION 11 – TOXICOLOGY INFORMATION

### Chronic Health Hazards

No ingredient in this product is an IARC, NTP or OSHA Lister carcinogen.

Toxicology Data

Ingredient Name

**None**

## SECTION 12 – ECOLOGICAL INFORMATION

### Ecological Data

Ingredient Name:	<b>None</b>
Food Chain Concentration Potential:	N/A
Waterfowl Toxicity:	N/A
BOD:	N/A
Aquatic Toxicity:	N/A

## SECTION 13 – DISPOSAL CONSIDERATIONS

**Waste Classification:** Non-regulated solid waste

**Disposal Method:** Approved landfill

Waste from this product is not considered hazardous as defined under the Resource Conservation and Recovery Act (RCRA) 40 CFR 261. Dispose of in accordance with federal, state, and local regulation regarding pollution.

## SECTION 14 – TRANSPORTATION INFORMATION

DOT:	Non-regulated
Ocean (IMDG):	Non-regulated
Air (IATA):	Non-regulated
WHMIS (Canada):	Non-regulated

## SECTION 15 – REGULATORY INFORMATION

### Regulatory Data

Ingredient Name:	<b>None</b>
SARA 313	N/A
TSCA Inventory	All components listed
CERCLA RQ	N/A
RCRA Code	N/A

## SECTION 16 – OTHER INFORMATION

This document is prepared pursuant to the OSHA Hazard Communication Standard (29 CFR 1910.1200). The information herein is given in good faith, but no warranty, expressed or implied is made.

Consult RectorSeal for further information: (713) 263-8001