



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 670WG Combo 2 Switches 1P 20A 120/277V WH

*Pass & Seymour/Legrand*

Catalog Number	670WG
Manufacturer	Pass & Seymour/Legrand
Description	Combination Switch, 1 Pole, 20 A, 120/277 V Ac, #14 to #12 Awg Wire Size, White, 1.32 (L) X 0.94 (W) X 4.06 (H) In, Toggle Actuator, Wall Mount, 0.22 LB
Weight per unit	0.2160 (lbs/each)
Product Category	Combination Devices

### Features

action	(2) SP
actuator	Toggle
amperage rating	20
connection	Side wire
Contact Rating	20 Amp, 120/277 VAC
indoor/outdoor	Indoor
Load Rating	20 A @ 120/277 VAC
Load Type	LED, Fluorescent, Xenon, Universal, CFL, Incandescent, Halogen
Material	Thermoplastic
Number of Gangs	1
Number of Switches	2.0
operating cycles	30k.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120/277 V
Wall Plate Included	NO
Wattage	Electrical power is expressed in Amps and Volts.

### Material, Color, and Finish

Finish	SATIN
--------	-------

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

### Descriptions

Description	COMBO 2 SWITCHES 1P 20A 120/277V WH
extra long description	P&S 670WG COMBO 2 SWITCHES 1P 20A 1
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007006049
Manufacturers Part Number	670WG
UPC	785007006049

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	COMBINATION

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.216

## Uses, Certifications, and Standards

environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature	Maximum continuous +60°C, minimum -30°C
standard	CULUS, UL20