



856A	2"	4.968	.843	6.050	1.400	2.400
855A	1 1/2"	4.968	.843	6.050	1.400	2.400
854A	1 1/4"	2.875	.687	3.080	1.625	1.940
853A	1"	2.622	.687	2.510	1.330	1.570
852A	3/4"	2.096	.531	2.325	.830	1.380
851A	1/2"	1.842	.472	2.140	.635	1.085
850A	3/8"	1.432	.402	1.800	.440	.750
PART No.	TRADE SIZE	"A"	"B"	"C"	MIN	MAX