

Bells Vibrating 720



Edwards 720 fully enclosed, non-adjustable bells are suitable for use in residential, commercial and OEM applications. They may be operated off of a 592 transformer or DC power. They are also suitable for AC powered security systems with a battery standby.

Features and Specifications


- Attractive snap-on covers
- Corrosion resistant metallic finish
- Enclosed binding posts

Ordering Information

| Description | Cat. No. | Operating Voltage | Current | VA | dB at 1m/10ft. | DC Coil Res (Ohms) |
|--------------------------------|----------|-------------------|---------|-----|----------------|--------------------|
| Fully Enclosed, Non Adjustable | 720 | 6-8V AC 3-6V DC | 1.20 A | 7.0 | 88/78 | 1.5 |

Weights and Dimensions

| Cat. No. | Approx. Net Weight (lb.) | Approx. Shipping Weight (lb.) |
|----------|--------------------------|-------------------------------|
| 720 | 0.44 | 0.46 |



Bells Vibrating 720



Edwards 720 fully enclosed, non-adjustable bells are suitable for use in residential, commercial and OEM applications. They may be operated off of a 592 transformer or DC power. They are also suitable for AC powered security systems with a battery standby.

Features and Specifications

- Attractive snap-on covers
- Corrosion resistant metallic finish
- Enclosed binding posts

Ordering Information

| Description | Cat. No. | Operating Voltage | Current | VA | dB at 1m/10ft. | DC Coil Res (Ohms) |
|--------------------------------|----------|-------------------|---------|-----|----------------|--------------------|
| Fully Enclosed, Non Adjustable | 720 | 6-8V AC 3-6V DC | 1.20 A | 7.0 | 88/78 | 1.5 |

Weights and Dimensions

| Cat. No. | Approx. Net Weight (lb.) | Approx. Shipping Weight (lb.) |
|----------|--------------------------|-------------------------------|
| 720 | 0.44 | 0.46 |

