

Project: _____ Type: _____ Prepared By: _____ Date: _____



Features and Benefits

- Energy efficient replacement for incandescent and halogen lamps
- Constructed from durable plastic which lowers risk of breakage
- Rated for use in enclosed and open fixtures in dry or damp locations
- Frosted lens produces smooth diffuse light
- Longer lifespan compared to legacy equivalents minimizes replacement and maintenance costs
- ENERGY STAR Compliant

Technical Specifications		
<p>Performance</p> <hr/> <p>Product Type: A-Line</p> <p>Input Wattage: 9.5W</p> <p>Typical Lumen Output: 800</p> <p>Efficacy: 84 lm/W</p> <p>Color Temperature: 3000K Warm White</p> <p>CRI: 80</p>	<p>L70 Lifespan: 15,000 Hours</p> <p>Dimmable: No</p> <p>Construction</p> <hr/> <p>Bulb Shape: A19</p> <p>Base Type: E26</p> <p>Beam Angle: 230°</p> <p>For Use Outdoors in Open Fixtures: No</p>	<p>Other</p> <hr/> <p>Equivalency: 60W Incandescent</p> <p>Warranty (Years): RAB warrants that our LED products will be free from defects in materials and workmanship for a period of three (3) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty.</p> <p>Electrical</p> <hr/> <p>Power Factor: 0.7</p> <p>Operating Temperature: -20°C - 45°C</p> <p>Input Voltage: 120V</p>

Technical Specifications (continued)

Electrical

Operating Frequency:

60 Hz

Electrical Characteristics

Input Current @ 120V:

125mA

Flicker:

<30%

Compliance

UL Listed:

Yes

ENERGY STAR V2.0:

This product is ENERGY STAR® Version 2.0 Certified

Energy Star ID:

2330080


CEC Status:

Not lawful for sale in California

Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	12	10	7.6	5.1
PALLET	3456	45.4	40	46.1

Dimension



Light Distribution

