

Specifications

Photo is representative

Eaton AHCL520C

Eaton Arrow Hart Color Coded Locking Connector, #14-8 AWG, 20A, Industrial, 125V, Back, Yellow, Black, Ultra grip, Nylon, L5-20, Two-pole, Three-wire, Nylon, 0.38 - 1.00" (9.5 - 25.4mm), -40°C (w/o impact) to 60°C (-40°F to 140°F)

General specifications

PRODUCT NAME	Eaton Arrow Hart Color Coded Locking Connector
CATALOG NUMBER	AHCL520C
UPC	032664755798
PRODUCT LENGTH/DEPTH	2.23 in
PRODUCT HEIGHT	3.71 in
PRODUCT WIDTH	2.1 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	RoHS Compliant NAFTA
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Color Coded Locking

Product specifications

SPECIAL FEATURES	Voltage Color Coding
TYPE	Locking Connector
AMPERAGE RATING	20A
VOLTAGE RATING	125 V
APPLICATION	Industrial
WIRING METHOD	Back
NUMBER OF WIRES	3
NUMBER OF POLES	Two-pole
COLOR	Yellow Black
CORD DIAMETER	0.38-1 in (9.5-25.4 mm)
MATERIAL	Nylon
OPERATING TEMPERATURE	-40 to 60 °C (-40 to 140 °F)
ALLOWABLE WIRE SIZE	#14-8 AWG
NEMA CONFIGURATION	L5-20
TORQUE RATING	14 lbf-inch
DESIGN TYPE	Ultra grip
FACE/BODY MATERIAL	Nylon

Resources

MULTIMEDIA

[Eaton Arrow Hart color coded locking devices](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - AHCL520C](#)

[Arrow Hart color coded industrial grade L5-20 locking devices spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.