

# Specifications

Photo is representative

## Eaton C0050E3A

Eaton Type MTE industrial control transformer, pv: 208/277v, taps: none, sv: 120v, 55°C, 50 va

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0050E3A
<b>UPC</b>	786680550003
<b>PRODUCT LENGTH/DEPTH</b>	3.61 in
<b>PRODUCT HEIGHT</b>	3.26 in
<b>PRODUCT WIDTH</b>	3 in
<b>PRODUCT WEIGHT</b>	2.8 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed CSA Certified cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability
<b>PRODUCT TYPE</b>	Industrial control transformer



Powering Business Worldwide

## Physical Attributes

**COIL MATERIAL** Copper windings

**DESIGN** MTE

**TAP SIZE** None

## Performance Ratings

**PRIMARY VOLTAGE** 208/277 V

**TEMPERATURE RATING** 55°C

**VOLT AMPERE RATING** 50 VA

**SECONDARY VOLTAGE** 120 V

## Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - C0050E3A](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2026 Eaton. All Rights Reserved.

# Specifications

Photo is representative

## Eaton C0050E3A

Eaton Type MTE industrial control transformer, pv: 208/277v, taps: none, sv: 120v, 55°C, 50 va

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0050E3A
<b>UPC</b>	786680550003
<b>PRODUCT LENGTH/DEPTH</b>	3.61 in
<b>PRODUCT HEIGHT</b>	3.26 in
<b>PRODUCT WIDTH</b>	3 in
<b>PRODUCT WEIGHT</b>	2.8 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Listed CSA Certified cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability
<b>PRODUCT TYPE</b>	Industrial control transformer



Powering Business Worldwide

## Physical Attributes

**COIL MATERIAL** Copper windings

**DESIGN** MTE

**TAP SIZE** None

## Performance Ratings

**PRIMARY VOLTAGE** 208/277 V

**TEMPERATURE RATING** 55°C

**VOLT AMPERE RATING** 50 VA

**SECONDARY VOLTAGE** 120 V

## Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - C0050E3A](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2026 Eaton. All Rights Reserved.