

Specifications



Photo is representative



Eaton C0100E2AFB

Eaton Type MTE industrial control transformer, Eaton industrial control transformer MTE, pv: 240 x 480v, 230 x 460v, 220 x 440v, taps: none, sv: 120/115/110v, 55°C, 100 va , cu magnet wire

General specifications

PRODUCT NAME	Eaton Type MTE industrial control transformer
CATALOG NUMBER	C0100E2AFB
UPC	786680420849
PRODUCT LENGTH/DEPTH	3.49 in
PRODUCT HEIGHT	4.35 in
PRODUCT WIDTH	3.38 in
PRODUCT WEIGHT	7.9 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Listed cUL Certified CSA Certified
CATALOG NOTES	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

COIL MATERIAL	Copper windings
DESIGN	MTE
TAP SIZE	None

Miscellaneous

MODIFICATION 1	Factory-mounted two-pole primary fuse block for non-rejection type fuses
SPECIAL FEATURES	Primary fuse block

Performance Ratings

PRIMARY VOLTAGE	220 x 440 V, 230 x 460 V, 240 x 480 V
TEMPERATURE RATING	55°C
VOLT AMPERE RATING	100 VA
SECONDARY VOLTAGE	120/115/110 V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C0100E2AFB
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

