



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Industrial Control Transformer

**C0150E2A**

**UPC:**786680422584

### Dimensions:

- **Height:** 3.189 IN
- **Length:** 4.016 IN
- **Width:** 3.74 IN

**Weight:**6.7 LB

**Notes:**Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Primary Voltage:** 240 X 480V, 230 X 460V, 220 X 440V
- **Secondary Voltage:** 120/115/110V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 150 VA

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [MTE Control Transformer 150 VA Series 2 - C0150E2A](#)
- [Eaton Specification Sheet - C0150E2A](#)



**Certifications:**

- UL Listed
- CSA Certified
- cUL Certified

**Product compliance:**

- RoHS Compliant

---

© 2016 Eaton. All rights reserved.