

# Eaton AHCL1430R

Catalog Number: AHCL1430R

Eaton Arrow Hart Color Coded Locking Receptacle, #14-8 AWG, 30A, Industrial, 125/250V, Orange, Black, Ultra grip, Glass filled Nylon, L14-30, Three-pole, Four-wire, Glass-filled Nylon, -40°C (w/o impact) to 70°C (-40°F to 158°F)



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart Color Coded Locking Receptacle	AHCL1430R
	<b>UPC</b>
	032664758546

<b>Product Length/Depth</b>	<b>Product Height</b>
1.62 in	3.64 in

<b>Product Width</b>	<b>Product Weight</b>
1.06 in	0.33 lb

<b>Warranty</b>	<b>Compliances</b>
Refer to warranty document.	RoHS Compliant
	NAFTA

**Certifications**

- CSA Certified
- UL Listed
- NOM
- Federal Specification Classification 6233 01

## Product specifications

### Special features

Voltage Color Coding

### Color

Orange

Black

### Face/body material

Glass filled nylon

### Wiring method

Back and side

### Material

Glass filled nylon

### Allowable wire size

#14-8 AWG

### Amperage Rating

30A

### Number Of Poles

Three-pole

### Type

Locking Receptacle

### NEMA configuration

L14-30

### Design type

Ultra grip

### Number of wires

4

### Operating temperature

-40 to 70 °C (-40 to 158 °F)

### Voltage rating

125/250 V

### Application

Industrial

### Torque rating

20 lbf-inch

## Resources

### Multimedia

[Eaton Arrow Hart color coded locking devices](#)

[Arrow Hart industrial color coded locking devices](#)

### Specifications and datasheets

[Arrow Hart color coded industrial grade L14-30 locking devices spec sheet](#)

[Eaton Specification Sheet - AHCL1430R](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)