

# Specifications

Photo is representative



## Eaton C0200E1B

Eaton Type MTE industrial control transformer, pv: 120 x 240v, taps: none, sv: 24v, 55°C, 200 va

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0200E1B
<b>UPC</b>	786680423000
<b>PRODUCT LENGTH/DEPTH</b>	5.5 in
<b>PRODUCT HEIGHT</b>	7.5 in
<b>PRODUCT WIDTH</b>	5 in
<b>PRODUCT WEIGHT</b>	7.7 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified UL Listed cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

### Physical Attributes

<b>COIL MATERIAL</b>	Copper windings
<b>DESIGN</b>	MTE
<b>TAP SIZE</b>	None

### Performance Ratings

<b>PRIMARY VOLTAGE</b>	120 x 240 V
<b>TEMPERATURE RATING</b>	55°C
<b>VOLT AMPERE RATING</b>	200 VA
<b>SECONDARY VOLTAGE</b>	24 V

### Resources

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - C0200E1B](#)

**WARRANTY GUIDES**

[Selling Policy 25-000 -  
Distribution and Control  
Products and Services](#)

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

Photo is representative



## Eaton C0200E1B

Eaton Type MTE industrial control transformer, pv: 120 x 240v, taps: none, sv: 24v, 55°C, 200 va

### General specifications

<b>PRODUCT NAME</b>	Eaton Type MTE industrial control transformer
<b>CATALOG NUMBER</b>	C0200E1B
<b>UPC</b>	786680423000
<b>PRODUCT LENGTH/DEPTH</b>	5.5 in
<b>PRODUCT HEIGHT</b>	7.5 in
<b>PRODUCT WIDTH</b>	5 in
<b>PRODUCT WEIGHT</b>	7.7 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	CSA Certified UL Listed cUL Certified
<b>CATALOG NOTES</b>	Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

### Physical Attributes

<b>COIL MATERIAL</b>	Copper windings
<b>DESIGN</b>	MTE
<b>TAP SIZE</b>	None

### Performance Ratings

<b>PRIMARY VOLTAGE</b>	120 x 240 V
<b>TEMPERATURE RATING</b>	55°C
<b>VOLT AMPERE RATING</b>	200 VA
<b>SECONDARY VOLTAGE</b>	24 V

### Resources

**SPECIFICATIONS AND DATASHEETS** [Eaton Specification Sheet - C0200E1B](#)

**WARRANTY GUIDES**

[Selling Policy 25-000 -  
Distribution and Control  
Products and Services](#)

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

