

Rigid Metal Conduit, IMC or EMT Pipe Hangers



Applications

- Unique design accommodates more sizes of conduit with fewer clamps for lower inventories.
- Suitable for Rigid, IMC and EMT.
- Suitable for conduit runs on vertical and horizontal beams.

Material/Finish

- Malleable iron/zinc plated



Illustrated Features



Single line of conduit running parallel to beam using “CH” hanger.



Doubles lines of conduit running perpendicular to beam using “CHD” hanger.

| Catalog Number | Trade Size (Inches) | Dimensions in Inches/Millimeters | | | | Weight Lbs./Kgs. Per 100 | | |
|---|---------------------|----------------------------------|-----------|-----------|-----------|--------------------------|--------------|---|
| | | A | B | C | D | | | |
| Type AJ — For Single Line Conduit | | | | | | | | |
|  | AJ-50-75 | 1/2-3/4 | 1.75/44.5 | 1.31/33.3 | 1.53/38.9 | 2.44/62.0 | 56.30/25.54 |  |
| | AJ-100 | 1 | 2.06/52.3 | 1.41/35.8 | 1.81/46.0 | 2.75/69.9 | 62.50/28.35 | |
| | AJ-125-150 | 1-1/4—1-1/2 | 2.69/68.3 | 2.06/52.3 | 2.63/66.8 | 3.69/93.7 | 115.60/52.44 | |
| | AJ-200 | 2 | 3.31/84.1 | 2.31/58.7 | 3.13/79.5 | 4.31/109.5 | 137.50/62.37 | |

Rigid Metal Conduit, IMC or EMT Pipe Hangers



Applications

- Unique design accommodates more sizes of conduit with fewer clamps for lower inventories.
- Suitable for Rigid, IMC and EMT.
- Suitable for conduit runs on vertical and horizontal beams.

Material/Finish

- Malleable iron/zinc plated



Illustrated Features



Single line of conduit running parallel to beam using "CH" hanger.



Doubles lines of conduit running perpendicular to beam using "CHD" hanger.

| Catalog Number | Trade Size (Inches) | Dimensions in Inches/Millimeters | | | | Weight Lbs./Kgs. Per 100 | | |
|---|---------------------|----------------------------------|-----------|-----------|-----------|--------------------------|--------------|---|
| | | A | B | C | D | | | |
| Type AJ — For Single Line Conduit | | | | | | | | |
|  | AJ-50-75 | 1/2-3/4 | 1.75/44.5 | 1.31/33.3 | 1.53/38.9 | 2.44/62.0 | 56.30/25.54 |  |
| | AJ-100 | 1 | 2.06/52.3 | 1.41/35.8 | 1.81/46.0 | 2.75/69.9 | 62.50/28.35 | |
| | AJ-125-150 | 1-1/4—1-1/2 | 2.69/68.3 | 2.06/52.3 | 2.63/66.8 | 3.69/93.7 | 115.60/52.44 | |
| | AJ-200 | 2 | 3.31/84.1 | 2.31/58.7 | 3.13/79.5 | 4.31/109.5 | 137.50/62.37 | |