

Specifications



Photo is representative

Eaton CDR3034 RS

Eaton Crouse-Hinds series PowerMate CDR receptacle, 30A, Three-wire, four-pole, Style 2, Copper-free aluminum, Reverse service, 600 Vac/250 Vdc

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Crouse-Hinds series PowerMate CDR receptacle |
| CATALOG NUMBER | CDR3034 RS |
| UPC | 662276277212 |
| PRODUCT LENGTH/DEPTH | 2.88 in |
| PRODUCT HEIGHT | 3.38 in |
| PRODUCT WIDTH | 3.38 in |
| PRODUCT WEIGHT | 2.2 lb |



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

AMPERAGE RATING 30A

| | |
|-----------------------|-----------|
| | Locations |
| STANDARDS TYPE | NEC/CEC |
| NEMA RATING | 4X |

| | |
|-------------------------|-----------------------|
| GROUNDING TYPE | Style 2 |
| CONFIGURATION | Three-wire, four-pole |
| VOLTAGE RATING | 600 Vac/250 Vdc |
| MATERIAL | Copper-free aluminum |
| SPECIAL FEATURES | Reverse service |

Resources

BROCHURES [PowerMate Drilling Pin and Sleeve Devices brochure](#)

CATALOGS [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

CERTIFICATION REPORTS [PowerMate Drilling Pin and Sleeve Devices UL certification \(Receptacles\)](#)

INSTALLATION INSTRUCTIONS [IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - CDR3034 RS](#)

[PowerMate Connectors](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:




Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton CDR3034 RS

Eaton Crouse-Hinds series PowerMate CDR receptacle, 30A, Three-wire, four-pole, Style 2, Copper-free aluminum, Reverse service, 600 Vac/250 Vdc

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Crouse-Hinds series PowerMate CDR receptacle |
| CATALOG NUMBER | CDR3034 RS |
| UPC | 662276277212 |
| PRODUCT LENGTH/DEPTH | 2.88 in |
| PRODUCT HEIGHT | 3.38 in |
| PRODUCT WIDTH | 3.38 in |
| PRODUCT WEIGHT | 2.2 lb |



Certifications and compliances

| | |
|----------------------------|------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous |
|----------------------------|------------------------|

Product specifications

| | |
|------------------------|-----|
| AMPERAGE RATING | 30A |
|------------------------|-----|

| | |
|-----------------------|-----------|
| | Locations |
| STANDARDS TYPE | NEC/CEC |
| NEMA RATING | 4X |

| | |
|-------------------------|-----------------------|
| GROUNDING TYPE | Style 2 |
| CONFIGURATION | Three-wire, four-pole |
| VOLTAGE RATING | 600 Vac/250 Vdc |
| MATERIAL | Copper-free aluminum |
| SPECIAL FEATURES | Reverse service |

Resources

BROCHURES [PowerMate Drilling Pin and Sleeve Devices brochure](#)

CATALOGS [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

CERTIFICATION REPORTS [PowerMate Drilling Pin and Sleeve Devices UL certification \(Receptacles\)](#)

INSTALLATION INSTRUCTIONS [IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - CDR3034 RS](#)

[PowerMate Connectors](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

