



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

BR4242L400R 1PH 400A Mlo 42/42 Cir. Al Bus Nema 3R *Eaton Corp*

Catalog Number	BR4242L400R
Manufacturer	Eaton Corp
Description	Eaton BR Main Lug Loadcenter, With Flush or Nema Type 3R Cover, Outdoor, 400 A, 46, Aluminum, Nema 3R, 42 Circuits, 42 Spaces, Four-Wire, Three-Phase, Type BR 1-Inch Breakers, 208Y/120, 240V, (1) 250–750 Kcmil or (2) #3/0–250 Kcmil
Weight per unit	67.0 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

amperage rating	400 A
Cover Type	Cover included
dimensions	6.3800 IN X 16.3100 IN X 54.0000 IN
interrupt rating	25 kAIC
number of spaces	42
Phase	Single-phase

Dimensions and Weight

Depth	6.38
Height	54
Width	16.31

Descriptions

Description	1PH 400A MLO 42/42 CIR. AL BUS NEMA 3R
extra long description	ETN BR4242L400R Eaton BR main lug l
Features	Eaton's BR 1-inch main lug load center is used when a sub-panel is needed to add circuits to an existing service. BR load centers house the branch circuit breakers and the wiring required to distribute power to individual circuits.
Long Description	Eaton BR main lug loadcenter,With flush or NEMA type 3R cover, Outdoor, 400 A,46,Aluminum,NEMA 3R,42 Circuits,42 Spaces,Four-wire,Three-phase,Type BR 1-inch breakers,208Y/120,240V,(1) 250–750 kcmil or (2) #3/0–250 kcmil
Product Type	Eaton BR Main Lug Loadcenter

Manufacturer Information

Brand	Eaton
GTIN	00786685924007
Manufacturers Part Number	BR4242L400R
UPC	786685924007



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Main lug loadcenter

Packaging

Carton	1
Weight Per each	67

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting standard	Surface Mount UL 67,UL 50