



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BRN230GF BR 2 Pole 30A GFST 120/240V 10 Kaic *Eaton Corp*

Catalog Number	BRN230GF
Manufacturer	Eaton Corp
Description	Eaton BR Gfci Circuit Breaker, Ground Fault Personnel Protection Circuit Breakers, Pigtail Neutral, 30 A, 10 Kaic, Two-Pole, 120/240 V, GFTCB, Common, #14-4 Awg, Ground Fault Circuit Interrupter, GFI
Weight per unit	1.0 (lbs/each)
Product Category	Distribution Equipment

Features

dimensions 4.2500 IN X 3.0000 IN X 2.0000 IN

Descriptions

Description	BR 2 POLE 30A GFST 120/240V 10 KAIC
extra long description	ETN BRN230GF BR 2 POLE 30A GFST, 12
Features	Eaton's residential BR Circuit Breakers are used in load centers, panelboards, or similar devices. They are made for a wide range of applications and include: BR 1" circuit breakers and accessories for BR-style load centers; arc fault circuit interrupters (AFCI); and ground fault circuit interrupters (GFCI).
Long Description	EATON BR GFCI CIRCUIT BREAKER, GROUND FAULT PERSONNEL PROTECTION CIRCUIT BREAKERS, PIGTAIL NEUTRAL, 30 A, 10 KAIC, TWO-POLE, 120/240 V, GFTCB, COMMON, #14-4 AWG, GROUND FAULT CIRCUIT INTERRUPTER, GFI
Product Type	BR 2 Pole 30A GFST, 120/240V, 10 Kaic

Manufacturer Information

Brand	Eaton
GTIN	00786676043809
Manufacturers Part Number	BRN230GF
UPC	786676043809

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers

Packaging

Carton	1
Weight Per each	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Conventional Energy - Conventional Energy
Marine Vessels and Equipment - Marine Vessels and Equipment -
Other
Generation - Renewable Energy - Alternative
Energy
Datacenters - IT Space: CI and Hyper Converged
Other

standard

UL 943, UL 489