



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHHT Handle Tie Bar For 2 - 1 Pole CH BRKRS

Eaton Corp

Catalog Number	CHHT
Manufacturer	Eaton Corp
Description	Eaton CH 3/4-Inchch Loadcenter and Breaker Accessories - Handle Tie, Handle Tie, CH, 0.75 In, Used With (2) Single-Pole CH Breakers
Weight per unit	0.0100 (lbs/each)
Product Category	Circuit Breaker Accessories

### Features

amperage rating	225
interrupt rating	10
loadcenter type	CH
media	Yes
Phase	3

### Dimensions and Weight

Depth	1
Height	0.5
Width	0.5

### Descriptions

Description	HANDLE TIE BAR FOR 2 - 1 POLE CH BRKRS
extra long description	ETN CHHT Handle Tie Bar-(2) - 1 Pol
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH 3/4-inchch Loadcenter and Breaker Accessories - Handle Tie,Handle tie,CH,0.75 in,Used with (2) single-pole CH breakers
Product Type	Handle Tie Bar-(2) - 1 Pole CH Breakers
Special Features	Used with (2) single-pole CH breakers



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113099071
Manufacturers Part Number	CHHT
UPC	782113099071

## Taxonomies, Classifications, and Categories

Category Description	LOADCENTER ACCESSORIES
Type	Accessory

## Packaging

Carton	1
Package	25
Weight Per each	0.01

## Uses, Certifications, and Standards

Application	Other
standard	UL 489