



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHM1G7N7NS Metered Ring Surf Pop (1) 14-50R (2) 5-20r2gfi

Eaton Corp

Catalog Number	CHM1G7N7NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Metered-Ring, Ground Fault, Non-Ground Fault, Non-Ground Fault, Top, Surface, Circuits: 4, Nema 5-20R2GFI, Nema 14-50R, Nema 5-20r2gfi
Weight per unit	26.0 (lbs/each)
Product Category	Metered Power Outlet Panels

Features

dimensions	31.0000 IN X 10.0000 IN X 7.8000 IN
------------	-------------------------------------

Dimensions and Weight

Depth	31.0000
Height	7.8000
Width	10.0000

Descriptions

Also Known As...	Meter Socket Meter Box
Description	METERED RING SURF POP (1) 14-50R (2) 5-20R2GFI
extra long description	ETN CHM1G7N7NS RNG SURF POP (1) 14-
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Metered-ring, Ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 14-50R, NEMA 5-20R2GFI
Product Type	RNG Surf Pop (1) 14-50R (2) 5-20r2gfi

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114215586
Manufacturers Part Number	CHM1G7N7NS
UPC	782114215586

Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Pedestal mount metered

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	26

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL 231,UL Listed file E163588