



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHP22N125R CH Pon Loadctr 125A Convertible 22 Space N3R

*Eaton Corp*

Catalog Number	CHP22N125R
Manufacturer	Eaton Corp
Description	Eaton CH Convertible Loadcenter, 125A, Convertible, 22 Spaces, Nema 3R
Weight per unit	23.0 (lbs/each)
Product Category	Single Phase Convertible Load

### Features

amperage rating	125
interrupt rating	10
media	Yes
number of spaces	22
Phase	1

### Dimensions and Weight

Depth	21
Height	5.19
Size	X2
Width	14.31

### Descriptions

Description	CH PON LOADCNTR 125A CONVERTIBLE 22 SPACE N3R
extra long description	ETN CHP22N125R CH PON LC, 125A, CON
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH convertible loadcenter, 125A, convertible, 22 spaces, NEMA 3R
Product Type	CH Pon LC, 125A, Conv, 22SP, N3R
Special Features	Cover included

### Manufacturer Information

Brand	Eaton
GTIN	00786689058586
Manufacturers Part Number	CHP22N125R
UPC	786689058586



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... LOADCENTERS & COVERS

Type ..... Convertible loadcenter

## Packaging

Carton ..... 1

Weight Per each ..... 23

## Uses, Certifications, and Standards

Application ..... Residential Bldgs & Facilities - Residential Bldgs & Facilities -

Other

standard ..... UL 67,UL 50