



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHPLGF HNDL Padlock Device For 1P 3/4 GFI BRKRS

Eaton Corp

| | |
|------------------|---|
| Catalog Number | CHPLGF |
| Manufacturer | Eaton Corp |
| Description | Eaton Breaker, Handle Padlock Device, Single- or Two-Pole Type Chgfi Circuit Breakers |
| Weight per unit | 0.0500 (lbs/each) |
| Product Category | Circuit Breaker Accessories |

Features

| | |
|------------|-----------------------------------|
| dimensions | 6.0000 IN X 4.5000 IN X 1.0000 IN |
|------------|-----------------------------------|

Descriptions

| | |
|------------------------|---|
| Description | HNDL PADLOCK DEVICE FOR 1P 3/4 GFI BRKRS |
| extra long description | ETN CHPLGF HNDL PADLOCK DEVICE FOR |
| Features | Specially designed for easy installation, Eaton's BR 1-inch load centers house the branch circuit breakers and the wiring required to distribute power to individual circuits. They serve as main breaker for service entrances or as main lug when adding circuits to existing service. The main breaker protects the entire panel and can be used as a service disconnect. The branch breakers protect the wires leading to individual electrical loads such as fixtures and outlets. |
| Long Description | Eaton breaker, Handle padlock device,Single- or two-pole Type CHGFI circuit breakers |
| Product Type | HNDL Padlock Device For 1P 3/4 GFI S |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00782114213629 |
| Manufacturers Part Number | CHPLGF |
| UPC | 782114213629 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------------|
| Category Description | Fault Sensing Breakers (AFCI/GFCI) |
| Type | Accessory |

Packaging

| | |
|-----------------|------|
| Carton | 10 |
| Package | 100 |
| Weight Per each | 0.05 |

Uses, Certifications, and Standards

| | |
|-------------|--------|
| Application | Other |
| standard | UL 489 |