

Eaton C0500E1B

Catalog Number: C0500E1B

Eaton Type MTE industrial control transformer, pv: 120 x 240v, taps: none

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0500E1B

UPC
786680423086

Product Length/Depth	Product Height
6.11 in	5.14 in

Product Width	Product Weight
5.25 in	17.4 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications UL Listed CSA Certified cUL Certified

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material
Copper windings

Design
MTE

Tap size
None

Performance Ratings

Primary voltage
120 x 240 V

Temperature rating
55°C

Volt ampere rating
500 VA

Secondary voltage
24 V

Resources

[Specifications and datasheets](#)

[Eaton Specification Sheet - C0500E1B](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton C0500E1B

Catalog Number: C0500E1B

Eaton Type MTE industrial control transformer, pv: 120 x 240v, taps: none

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0500E1B

UPC
786680423086

Product Length/Depth	Product Height
6.11 in	5.14 in

Product Width	Product Weight
5.25 in	17.4 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications UL Listed CSA Certified cUL Certified

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material
Copper windings

Design
MTE

Tap size
None

Performance Ratings

Primary voltage
120 x 240 V

Temperature rating
55°C

Volt ampere rating
500 VA

Secondary voltage
24 V

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0500E1B](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)