



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C0500E2AFB 500 Va Type Mte Control Transformer With Primary F *Eaton Corp*

Catalog Number	C0500E2AFB
Manufacturer	Eaton Corp
Description	Eaton Type Mte Industrial Control Transformer, PV: 240 X 480V, 230 X 460V, 220 X 440V, SV: 120/115/110V, 55°C, 500 Va
Weight per unit	19.4 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

dimensions	5.5100 IN X 5.2300 IN X 6.1400 IN
kva rating	500 VA
Primary Voltage	230 x 460 V240 x 480 V220 x 440 V
Secondary Voltage	120/115/110 V
Tap Size	NONE

Descriptions

Description	500 VA TYPE MTE CONTROL TRANSFORMER WITH PRIMARY F
extra long description	ETN C0500E2AFB 500VA Type MTE CPT W
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton type MTE industrial control transformer, pv: 240 x 480v, 230 x 460v, 220 x 440v, sv: 120/115/110v, 55°C, 500 va
Product Type	500VA Type Mte CPT W/ Prim Fuse Block

Manufacturer Information

Brand	Eaton Corp
GTIN	00786680420962
Manufacturers Part Number	C0500E2AFB
UPC	786680420962

Taxonomies, Classifications, and Categories

Type	Industrial Control Transformer
------	--------------------------------

Packaging

Carton	1
Weight Per each	19.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Other
standard	CSA Certified,UL Listed,cUL Certified,RoHS Compliant
Temperature Rating	55°C