



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C371E1 Operator Mechanism

Eaton Corp

Catalog Number	C371E1
Manufacturer	Eaton Corp
Description	Type C371 Circuit Breaker Operator Mechanism, 150A Frame, Flange Mounted, 6.5-16 Variable Depth Mounting Range, HMCP and Series C-Ehd, FDB, FD, FDC, HFD, Ed-Frame, For Nema 1-12 Enclosures, With 4-Inch Handle
Weight per unit	5.9 (lbs/each)
Product Category	Circuit Breaker Accessories

Features

amperage rating	150A
dimensions	16.8000 IN X 6.8000 IN X 5.1000 IN
media	Yes

Descriptions

Description	OPERATOR MECHANISM
extra long description	ETN C371E1 OPERATOR MECHANISM
Features	Eaton's Electrical Sector under the Eaton brand offers the widest variety of molded case circuit breakers available today. Designed for electrical and machinery OEMs serving a range of industries and applications these proven designs incorporate the latest in innovation with the high reliability that has been our hallmark since the advent of the circuit breaker in the 1920s
Long Description	Type C371 Circuit Breaker Operator Mechanism, 150A frame, Flange mounted, 6.5-16 variable depth mounting range, HMCP and Series C-EHD, FDB, FD, FDC, HFD, ED-frame, For NEMA 1-12 enclosures, With 4-inch handle
Product Type	Operator Mechanism

Manufacturer Information

Brand	Eaton
GTIN	00782113599533
Manufacturers Part Number	C371E1
UPC	782113599533

Taxonomies, Classifications, and Categories

Category Description	Powerdefense Breakers
Type	Molded case circuit breaker accessory

Packaging

Carton	1
Weight Per each	5.9



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	FLANGE
standard	UL Listed, IEC/EN 60947-4-1, IEC Rated