

Industrial grade straight blade  
& locking devices





















**ARROW/HART**

# Arrow Hart

**EATON**

*Powering Business Worldwide*

# Arrow Hart quick reference guide

Pole-Wire	Amp.	V/AC	NEMA Configuration	Page	Grip			Receptacle		Flanged		
					Style	Plug	Connector	Single	Duplex	Inlet	Outlet	
2P-2W	15	125	L1-15		9	Safety	7546	7506	CWL115R	7540	CWL115FI	CWL115FO
	20	125	L2-20		10	Safety	CWL220P	CWL220C	CWL220R			CWL220FO
2P-3W	15	125	5-15		6, 7	Ultra	AH5266 AH5266BK AH8215HG	AH5269 AH5269BK AH8219HG			AH5278 AH5278C	AH5246 AH5279C
						Safety	AH5266A AH8215HGA AH8215HGAC AH8215HGC	AH8219HGC				
					7	Quick	AH5965BK AH5965Y AH8115W	AH5969BK AH5969Y AH8119W				
	15	125	L5-15		9	Safety	CWL515P CWL515PAN	CWL515C CWL515CAN	CWL515R IGL515R	4700 5792 IG4700	CWL515FI	CWL515FO
	15	250	6-15		7	Ultra	AH5666	AH5669			AH5678C	AH5679C
6					Safety	AH8225HGA AH8225HGAC						
7					Quick	AH5666BK AH5666Y	AH5669BK AH5669Y					
	15	250	L6-15		9	Safety	CWL615P	CWL615C	CWL615R IGL615R	6580	CWL615FI	CWL615FO
	15	277	L7-15		9	Safety	CWL715P	CWL715C	CWL715R	4750	CWL715FI	CWL715FO
	20	125	5-20		6, 7	Ultra	AH5366 AH8315HG	AH5369 AH8319HG			AH5778C	AH5779C
6					Safety	AH8315HGA AH8315HGAC						
7					Quick	AH5364BK AH5364Y	AH5369BK AH5369Y					
	20	125	L5-20		10	Ultra	AHL520P AHL520PBK	AHL520C AHL520CBK	AHL520R AHIGL520R		AHL520FI	AHL520FO
	20	250	6-20		7	Ultra	AH5466	AH5469			AH5878C	AH5879C
6					Safety	AH8325HG AH8325HGAC						
7					Quick	AH5464BK AH5464Y	AH5469BK AH5469Y					
	20	250	L6-20		10	Ultra	AHL620P	AHL620C	AHL620R AHIGL620R		AHL620FI	AHL620FO
	20	277	L7-20		10	Ultra	AHL720P	AHL720C	AHL720R AHIGL720R		AHL720FI	AHL720FO
	20	347	L24-20		10	Safety	L2420P		L2420R			
	20	480	L8-20		10	Ultra	AHL820P	AHL820C	AHL820R AHIGL820R		AHL820FI	AHL820FO
	20	600	L9-20		11	Auto	CWL920P	CWL920C	CWL920R		CWL920FI	CWL920FO
	30	125	L5-30		12	Ultra	AHL530P AHIGL530P	AHL530C	AHL530R AHIGL530R		AHL530FI	AHL530FO
30						250	L6-30		13	Ultra	AHL630P	AHL630C
	30	277	L7-30		13	Ultra	AHL730P	AHL730C	AHL730R AHIGL730R		AHL730FI	AHL730FO
	30	480	L8-30		13	Ultra	AHL830P	AHL830C	AHL830R AHIGL830R		AHL830FI	AHL830FO
	30	600	L9-30		13	Auto	CWL930P	CWL930C	CWL930R		CWL930FI	CWL930FO

# Arrow Hart quick reference guide

































Pole-Wire	Amp.	V/AC	NEMA Configuration	Page	Grip			Receptacle		Flanged		
					Style	Plug	Connector	Single	Duplex	Inlet	Outlet	
<b>3P-3W</b>	15/10	125/250	Non-NEMA Locking		9	Safety	4767 4767AN	4755	7582	7580		
	20	125/250	L10-20		11	Ultra	AHL1020P	AHL1020C	AHL1020R		AHL1020FI	AHL1020FO
	20	125/250	Non-NEMA Locking		12	Safety	9965C	7314C	7310B		7327N	7328N
	20	250	L11-20		10	Ultra	AHL1120P	AHL1120C	AHL1120R		AHL1120FI	AHL1120FO
	20	480	L12-20		11	Auto	CWL1220P	CWL1220C	CWL1220R		CWL1220FI	CWL1220FO
	30	125/250	L10-30		14	Ultra	AHL1030P	AHL1030C	AHL1030R		AHL1030FI	AHL1030FO
	30	125/250	Non-NEMA Locking		14	Ultra	AH3331N	AH3333N	AH3330-2		AH3337N	AH3336N
	30	250	L11-30		13	Ultra	AHL1130P	AHL1130C	AHL1130R		AHL1130FI	AHL1130FO
	30	480	L12-30		13	Auto	CWL1230P	CWL1230C	CWL1230R		CWL1230FI	CWL1230FO
	30	600	L13-30		14	Auto	CWL1330P	CWL1330C	CWL1330R		CWL1330FI	CWL1330FO
<b>3P-4W</b>	20	125/250	L14-20		12	Ultra	AHL1420P AHL1420PBK	AHL1420C AHL1420CBK	AHL1420R AHIGL1420R		AHL1420FI AHL1420FIBK	AHL1420FO AHL1420FOBK
	20	250	L15-20		10	Ultra	AHL1520P AHL1520PBK	AHL1520C AHL1520CBK	AHL1520R AHIGL1520R		AHL1520FI	AHL1520FO
	20	480	L16-20		11	Ultra	AHL1620P AHL1620PBK	AHL1620C AHL1620CBK	AHL1620R AHIGL1620R		AHL1620FI	AHL1620FO
	30	125/250	L14-30		14	Ultra	AHL1430P	AHL1430C	AHL1430R AHIGL1430R		AHL1430FI	AHL1430FO
	30	250	L15-30		13	Ultra	AHL1530P	AHL1530C	AHL1530R AHIGL1530R		AHL1530FI	AHL1530FO
	30	480	L16-30		13	Ultra	AHL1630P	AHL1630C	AHL1630R		AHL1630FI	AHL1630FO
	30	600	L17-30		14	Ultra	AHL1730P	AHL1730C	AHL1730R		AHL1730FI	AHL1730FO
	<b>4P-4W</b>	20	120/208	Non-NEMA Locking		11	Safety	7411C	7413C	7410B		7408N
20		120/208	L18-20		11	Ultra	AHL1820P	AHL1820C	AHL1820R		AHL1820FI	AHL1820FO
20		277/480	L19-20		12	Ultra	AHL1920P	AHL1920C	AHL1920R		AHL1920FI	AHL1920FO
20		347/600	L20-20		12	Ultra	AHL2020P	AHL2020C	AHL2020R		AHL2020FI	AHL2020FO
30		120/208	Non-NEMA Locking		14	Ultra	AH3431N	AH3433N	AH3430		AH3434N	AH3436N
30		120/208	L18-30		14	Ultra	AHL1830P	AHL1830C	AHL1830R		AHL1830FI	AHL1830FO
30		277/480	L19-30		15	Ultra	AHL1930P	AHL1930C	AHL1930R		AHL1930FI	AHL1930FO
30		347/600	L20-30		15	Ultra	AHL2030P	AHL2030C	AHL2030R		AHL2030FI	AHL2030FO
<b>4P-5W</b>	20	120/208	L21-20		11	Ultra	AHL2120P AHL2120PBK AHL2120PF	AHL2120C AHL2120CBK AHL2120CF	AHL2120R AHIGL2120R		AHL2120FI	AHL2120FO
	20	277/480	L22-20		12	Ultra	AHL2220P	AHL2220C	AHL2220R		AHL2220FI	AHL2220FO
	20/10	250/600	Non-NEMA Locking		9	Ultra	AH3521BK	AH3523BK			AH3524BK	AH3525BK
	20	347/600	L23-20		12	Ultra	AHL2320P	AHL2320C	AHL2320R		AHL2320FI	AHL2320FO
	30	120/208	L21-30		14	Ultra	AHL2130P AHL2130PF	AHL2130C AHL2130CF	AHL2130R AHIGL2130R		AHL2130FI	AHL2130FO
	30	277/480	L22-30		15	Ultra	AHL2230P AHL2230PF	AHL2230C AHL2230CF	AHL2230R AHIGL2230R		AHL2230FI	AHL2230FO
	30	347/600	L23-30		15	Ultra	AHL2330P AHL2330PF	AHL2330C AHL2330CF	AHL2330R AHIGL2330R		AHL2330FI	AHL2330FO



Table of Contents	Page
Straight blade features & benefits	5
Straight blade devices	6
Locking features & benefits	8
Locking devices	9
Accessories	16
Straight blade dimensions	17
Locking dimensions	18
Straight blade specifications	20
Locking specifications	22
Certifications & compliances	26



## Complete line of wiring devices for industrial & heavy construction environments

Arrow Hart plugs and connectors deliver superior performance in the most demanding environments. From everyday commercial use to heavy-duty industrial applications, Arrow Hart plugs and connectors ensure long lasting, dependable service.

- A variety of grip styles enabling numerous applications
- Easily identified amperage/voltage ratings clearly marked on devices
- Rugged construction to ensure longer service life



### Ultra grip

Built with a contemporary flare and oval ergonomic design for a comfortable yet secure feel, ultra grip plug and connectors offer excellent reliability and durability. A dual dovetail design provides superior cord grip retention, and the grommet allows usage across a wide range of cord diameters. Additionally, reversible inserts in the cord grip allow for exceptional clamp force on large diameter cords.



### Safety grip


Safety grip plugs and connectors combine durability and fast installation. Featuring dual-range external cord grip, safety grips provides positive cord gripping while limiting strain on conductors. The neoprene gasket seals around the cord for added terminal protection from external elements. The nylon construction is rugged and durable for dependable use.



### Quick grip

Quick grip plugs and connectors are designed for quick, secure installation and easy, long-lasting use. They feature rugged nylon construction and a roomy wiring chamber for fast and easy installation. Our scalloped ergonomic design provides a comfortable grip during installation and operation.

# Arrow Hart industrial grade ultra grip straight blade plugs & connectors redesign



# Arrow Hart hospital grade straight blade plugs & connectors



AH8215HG







AH8219HG







AH8119W

## 15A Hospital Grade Straight Blade Plugs & Connectors

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.
125	2P-3W	 	Ultra grip plug	Black & white	AH8215HG
			Safety grip plug	Clear	AH8215HGAC
		Safety grip angled body plug	Black & white	AH8215HGAC	
		Safety grip angled body plug	Clear	AH8215HGAC	
		Quick grip plug	White	AH8115W	
		Ultra grip connector	Black & white	AH8219HG	
		Safety grip connector	Clear	AH8219HGAC	
		Quick grip connector	White	AH8119W	
250	2P-3W	 	Safety grip angled plug	Black & white	AH8225HGAC
			Safety grip angled plug	Clear	AH8225HGAC

## 20A Hospital Grade Straight Blade Plugs & Connectors

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.
125	2P-3W	 	Ultra grip plug	Black & white	AH8315HG
			Safety grip angled plug	Black & white	AH8315HGAC
		Safety grip angled plug	Clear	AH8315HGAC	
		Ultra grip connector	Black & white	AH8319HG	
250	2P-3W	 	Safety grip angled plug	Black & white	AH8325HG
			Safety grip angled plug	Clear	AH8325HGAC

Accessories: page 16



Dimensions & cord diameters: page 17

Spec information: page 20 & 21

Compliances: page 26

# Arrow Hart industrial grade straight blade devices

## 15A Straight Blade Devices

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.
125	2P-3W		Ultra grip plug	Black & white	AH5266
			Ultra grip plug	Black	AH5266BK
		Safety grip angled body plug	Black & white	AH5266A	
		Ultra grip connector	Black & white	AH5269	
		Ultra grip connector	Black	AH5269BK	
		Flanged outlet, back wire	Black & white	AH5279C	
		Flanged outlet, back wire, metal	Steel	AH5246	
		Flanged inlet, back wire	Black & white	AH5278C	
Flanged inlet, back wire, metal	Steel	AH5278			
250	2P-3W		Ultra grip plug	Black & white	AH5666
			Ultra grip connector	Black & white	AH5669
		Flanged outlet, back wire, nylon	Black & white	AH5679C	
		Flanged inlet, back wire, nylon	Black & white	AH5678C	



AH5266





AH5269



AH5278C

## 20A Straight Blade Devices

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.
125	2P-3W		Ultra grip plug	Black & white	AH5366
			Ultra grip connector	Black & white	AH5369
		Flanged outlet, back wire, nylon	Black & white	AH5779C	
		Flanged inlet, back wire, nylon	Black & white	AH5778C	
250	2P-3W		Ultra grip plug	Black & white	AH5466
			Ultra grip connector	Black & white	AH5469
		Flanged outlet, back wire	Black & white	AH5879C	
		Flanged inlet, back wire	Black & white	AH5878C	





AH5269



AH5278C

## 15A Quick Grip Straight Blade Plugs & Connectors

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.
125	2P-3W		Quick grip plug	Black	AH5965BK
			Quick grip plug	Yellow	AH5965Y
		Quick grip connector	Black	AH5969BK	
		Quick grip connector	Yellow	AH5969Y	
250	2P-3W		Quick grip plug	Black	AH5666BK
			Quick grip plug	Yellow	AH5666Y
		Quick grip connector	Black	AH5669BK	
		Quick grip connector	Yellow	AH5669Y	





AH5278C



AH5965BK

## 20A Quick Grip Straight Blade Plugs & Connectors

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.
125	2P-3W		Quick grip plug	Black	AH5364BK
			Quick grip plug	Yellow	AH5364Y
		Quick grip connector	Black	AH5369BK	
		Quick grip connector	Yellow	AH5369Y	
250	2P-3W		Quick grip plug	Black	AH5464BK
			Quick grip plug	Yellow	AH5464Y
		Quick grip connector	Black	AH5469BK	
		Quick grip connector	Yellow	AH5469Y	

Accessories: page 16  
 Dimensions & cord diameters: page 17  
 Spec information: page 20 & 21  
 Compliances: page 26


# Arrow Hart industrial grade ultra grip locking plug & connector redesign

Tri-combo screws




Amperage/voltage & catalog number clearly marked

Terminal body assembly screws backed out for fast wiring and assembly



Tri-combo screws


Reversible inserts allow for minimal gap and consistent look and grip regardless of cable size




Grommet helps prevent debris from entering wire terminal chamber



Double dovetail provides for superior cord grip alignment and retention



Large cord range\* (Up to 1.16")



Longer bosses on cord grip allow for excellent clamp force on large diameter cords



Oval & flared ergonomic design

IP20 rating



## Receptacles



The amperage/voltage can now be found directly printed on many single receptacles.

\*Small body or 3-W devices



# Arrow Hart industrial grade locking devices









## 15/10A Industrial Grade Locking Devices

V/AC	Pole-Wire	NON-NEMA	Description	Color	Catalog No.
125/ 250	3P-3W	  Receptacle    Plug	Safety grip plug	Black & white	4767
			Safety grip angled body plug	Black & white	4767AN
			Safety grip connector	Black & white	4755
			Duplex receptacle	Black	7580
			Single receptacle	Black	7582



CWL515P

## 15A Industrial Grade Locking Devices

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.		
125	2P-2W	  L1-15R    L1-15P	Safety grip plug, cord dia. .312-.468"	Black	7546		
			Safety grip plug	Black	7548		
			Safety grip connector, cord dia. .312-.625"	Black	7506		
			Duplex receptacle	Black	7540		
			Single receptacle	Black	CWL115R		
			Flanged outlet	Black	CWL115FO		
			Flanged inlet	Black	CWL115FI		
			2P-3W	  L5-15R    L5-15P	Safety grip plug	Black & white	CWL515P
					Safety grip angled body plug	Black & white	CWL515PAN
					Safety grip connector	Black & white	CWL515C
Safety grip angled body connector	Black & white	CWL515CAN					
Duplex receptacle	Black	4700					
Duplex combination straight blade & locking	Black	5792					
Single receptacle	Black	CWL515R					
Duplex receptacle, isolated ground	Orange	IG4700					
Single receptacle, isolated ground	Orange	IGL515R					
Flanged outlet	Black & white	CWL515FO					
Flanged inlet	Black & white	CWL515FI					
250	2P-3W	  L6-15R    L6-15P	Safety grip plug	Black & white	CWL615P		
			Safety grip connector	Black & white	CWL615C		
			Duplex receptacle	Black	6580		
			Single receptacle	Black	CWL615R		
			Single receptacle, isolated ground	Orange	IGL615R		
			Flanged outlet	Black & white	CWL615FO		
			Flanged inlet	Black & white	CWL615FI		
277	2P-3W	  L7-15R    L7-15P	Safety grip plug	Black & white	CWL715P		
			Safety grip connector	Black & white	CWL715C		
			Duplex receptacle	Black	4750		
			Single receptacle	Black	CWL715R		
			Flanged outlet	Black & white	CWL715FO		
			Flanged inlet	Black & white	CWL715FI		



CWL515C



CWL515R





CWL515FO



CWL515FI

## 20/10A Industrial Grade Locking Devices

V/AC	Pole-Wire	NON-NEMA	Description	Color	Catalog No.
250/ 600	4P-5W	  Receptacle    Plug	Ultra grip plug	Black & white	AH3521BK
			Ultra grip connector	Black & white	AH3523BK
			Flanged outlet	Black	AH3525BK
			Flanged inlet	Black	AH3524BK

Accessories: page 16

Dimensions & cord diameters: page 18 & 19

Spec information: page 20-25

Compliances: page 26

# Arrow Hart industrial grade locking devices



AHL520P



AHL520C



AHL520R











AHL520FO



AHL520FI

## 20A Industrial Grade Locking Devices

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.		
125	2P-3W	 L5-20R L5-20P	Ultra grip plug	Black & white	AHL520P		
			Ultra grip plug	Black	AHL520PBK		
		Ultra grip connector	Black & white	AHL520C			
		Ultra grip connector	Black	AHL520CBK			
		Single receptacle	Black	AHL520R			
		Single receptacle, isolated ground	Orange	AHIGL520R			
		Flanged outlet	Black & white	AHL520FO			
		Flanged inlet	Black & white	AHL520FI			
		250	2P-2W	 L2-20R L2-20P	Safety grip plug	Black & white	CWL220P
Safety grip connector	Black & white				CWL220C		
Single receptacle	Black			CWL220R			
Flanged outlet	Black & white			CWL220FO			
2P-3W	 L6-20R L6-20P		Ultra grip plug	Black & white	AHL620P		
			Ultra grip connector	Black & white	AHL620C		
			Single receptacle	Black	AHL620R		
			Single receptacle, isolated ground	Orange	AHIGL620R		
			Flanged outlet	Black & white	AHL620FO		
			Flanged inlet	Black & white	AHL620FI		
			3P-3W	 L11-20R L11-20P	Ultra grip plug, 3-phase	Black & white	AHL1120P
					Ultra grip connector, 3-phase	Black & white	AHL1120C
Single receptacle, 3-phase	Black	AHL1120R					
Flanged outlet, 3-phase	Black & white	AHL1120FO					
Flanged inlet, 3-phase	Black & white	AHL1120FI					
3P-4W	 L15-20R L15-20P	Ultra grip plug, 3-phase	Black & white	AHL1520P			
		Ultra grip plug, 3-phase	Black	AHL1520PBK			
		Ultra grip connector, 3-phase	Black & white	AHL1520C			
		Ultra grip connector, 3-phase	Black	AHL1520CBK			
		Single receptacle, 3-phase	Black	AHL1520R			
		Single receptacle, isolated ground, 3-phase	Orange	AHIGL1520R			
		Flanged outlet, 3-phase	Black & white	AHL1520FO			
		Flanged inlet, 3-phase	Black & white	AHL1520FI			
277	2P-3W	 L7-20R L7-20P	Ultra grip plug	Black & white	AHL720P		
			Ultra grip connector	Black & white	AHL720C		
			Single receptacle	Black	AHL720R		
			Single receptacle, isolated ground	Orange	AHIGL720R		
			Flanged outlet	Black & white	AHL720FO		
			Flanged inlet	Black & white	AHL720FI		
347	2P-3W	 L24-20R L24-20P	Safety grip plug	Black & white	L2420P		
			Single receptacle	Black	L2420R		
480	2P-3W	 L8-20R L8-20P	Ultra grip plug	Black & white	AHL820P		
			Ultra grip connector	Black & white	AHL820C		
			Single receptacle	Black	AHL820R		
			Single receptacle, isolated ground	Orange	AHIGL820R		
			Flanged outlet	Black & white	AHL820FO		
			Flanged inlet	Black & white	AHL820FI		

Accessories: page 16









Dimensions & cord diameters: page 18 & 19

Spec information: page 20-25

Compliances: page 26

# Arrow Hart industrial grade locking devices

## 20A Industrial Grade Locking Devices

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.		
480	3P-3W	 L12-20R L12-20P	Auto grip plug, 3-phase	Black & white	CWL1220P		
			Auto grip connector, 3-phase	Black & white	CWL1220C		
			Single receptacle, 3-phase	Black	CWL1220R		
			Flanged outlet, 3-phase	Black & white	CWL1220FO		
			Flanged inlet, 3-phase	Black & white	CWL1220FI		
			3P-4W	 L16-20R L16-20P	Ultra grip plug, 3-phase	Black & white	AHL1620P
Ultra grip plug, 3-phase	Black	AHL1620PBK					
Ultra grip connector, 3-phase	Black & white	AHL1620C					
Ultra grip connector, 3-phase	Black	AHL1620CBK					
Single receptacle, 3-phase	Black	AHL1620R					
Single receptacle, isolated ground, 3-phase	Orange	AHIGL1620R					
Flanged outlet, 3-phase	Black & white	AHL1620FO					
Flanged inlet, 3-phase	Black & white	AHL1620FI					
600	2P-3W	 L9-20R L9-20P			Auto grip plug	Black & white	CWL920P
					Auto grip connector	Black & white	CWL920C
			Single receptacle	Black	CWL920R		
			Flanged outlet	Black & white	CWL920FO		
			Flanged inlet	Black & white	CWL920FI		
			120/208	4P-4W	 L18-20R L18-20P	Ultra grip plug, 3-phase	Black & white
Ultra grip connector, 3-phase	Black & white	AHL1820C					
Single receptacle, 3-phase	Black	AHL1820R					
Flanged outlet, 3-phase	Black & white	AHL1820FO					
Flanged inlet, 3-phase	Black & white	AHL1820FI					
4P-4W	 Receptacle Plug	Safety grip plug, 3-phase		Gray	7411C		
		Safety grip connector, 3-phase		Gray	7413C		
		Single receptacle, 3-phase		Black	7410B		
		Flanged outlet, 3-phase		Gray	7409N		
4P-5W	 L21-20R L21-20P	Ultra grip plug, 3-phase		Black & white	AHL2120P		
		Ultra grip plug, 3-phase		Black	AHL2120PBK		
		Ultra grip plug, 3-phase, flat cable		Black & white	AHL2120PF		
		Ultra grip connector, 3-phase		Black & white	AHL2120C		
		Ultra grip connector, 3-phase		Black	AHL2120CBK		
4P-5W	 L21-20R L21-20P	Ultra grip connector, 3-phase, flat cable	Black & white	AHL2120CF			
		Single receptacle, 3-phase	Black	AHL2120R			
		Single receptacle, isolated ground, 3-phase	Orange	AHIGL2120R			
		Flanged outlet, 3-phase	Black & white	AHL2120FO			
		Flanged inlet, 3-phase	Black & white	AHL2120FI			
125/250	3P-3W	 L10-20R L10-20P	Ultra grip plug	Black & white	AHL1020P		
			Ultra grip connector	Black & white	AHL1020C		
			Single receptacle	Black	AHL1020R		
			Flanged outlet	Black & white	AHL1020FO		
			Flanged inlet	Black & white	AHL1020FI		



AHL1210P



AHL2120C



AHL2120R



AHL2120FO



AHL2120FI

Accessories: page 16

Dimensions & cord diameters: page 18 & 19

Spec information: page 20-25

Compliances: page 26 & 27

# Arrow Hart industrial grade locking devices



AHL2220P



AHL2220C



AHL2220R















AHL2220FO





AHL2220FI

## 20A Industrial Grade Locking Devices

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.		
125/250	3P-3W	 Receptacle	Safety grip plug	Gray	9965C		
			Safety grip connector	Gray	7314C		
		 Plug	Single receptacle	Black	7310B		
			Flanged outlet	Gray	7328N		
			Flanged inlet	Gray	7327N		
277/480	3P-4W	 L14-20R	Ultra grip plug	Black & white	AHL1420P		
			Ultra grip plug	Black	AHL1420PBK		
		 L14-20P	Ultra grip connector	Black & white	AHL1420C		
			Ultra grip connector	Black	AHL1420CBK		
		Single receptacle	Black	AHL1420R			
		Single receptacle, isolated ground	Orange	AHIGL1420R			
		Flanged outlet	Black & white	AHL1420FO			
		Flanged inlet	Black & white	AHL1420FI			
		277/480	4P-4W	 L19-20R	Ultra grip plug, 3-phase	Black & white	AHL1920P
					Ultra grip connector, 3-phase	Black & white	AHL1920C
 L19-20P	Single receptacle, 3-phase			Black	AHL1920R		
	Flanged outlet, 3-phase			Black & white	AHL1920FO		
	Flanged inlet, 3-phase			Black & white	AHL1920FI		
277/480	4P-5W	 L22-20R	Ultra grip plug, 3-phase	Black & white	AHL2220P		
			Ultra grip connector, 3-phase	Black & white	AHL2220C		
		 L22-20P	Single receptacle, 3-phase	Black	AHL2220R		
			Flanged outlet, 3-phase	Black & white	AHL2220FO		
			Flanged inlet, 3-phase	Black & white	AHL2220FI		
347/600	4P-4W	 L20-20R	Ultra grip plug, 3-phase	Black & white	AHL2020P		
			Ultra grip connector, 3-phase	Black & white	AHL2020C		
		 L20-20P	Single receptacle, 3-phase	Black	AHL2020R		
			Flanged outlet, 3-phase	Black & white	AHL2020FO		
			Flanged inlet, 3-phase	Black & white	AHL2020FI		
347/600	4P-5W	 L23-20R	Ultra grip plug, 3-phase	Black & white	AHL2320P		
			Ultra grip connector, 3-phase	Black & white	AHL2320C		
		 L23-20P	Single receptacle, 3-phase	Black	AHL2320R		
			Flanged outlet, 3-phase	Black & white	AHL2320FO		
			Flanged inlet, 3-phase	Black & white	AHL2320FI		

## 30A Industrial Grade Locking Devices

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.
125	2P-3W	 L5-30R	Ultra grip plug	Black & white	AHL530P
			Ultra grip plug, isolated ground	Orange	AHIGL530P
		 L5-30P	Ultra grip connector	Black & white	AHL530C
			Single receptacle	Black	AHL530R
		Single receptacle, isolated ground	Orange	AHIGL530R	
		Flanged outlet	Black & white	AHL530FO	
		Flanged inlet	Black & white	AHL530FI	

Accessories: page 16

Dimensions & cord diameters: page 18 & 19









Spec information: page 20-25

Compliances: page 27



# Arrow Hart industrial grade locking devices

## 30A Industrial Grade Locking Devices

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.			
250	2P-3W	 L6-30R L6-30P	Ultra grip plug	Black & white	AHL630P			
			Ultra grip connector	Black & white	AHL630C			
		Single receptacle	Black	AHL630R				
		Single receptacle, isolated ground	Orange	AHIGL630R				
		Flanged outlet	Black & white	AHL630FO				
		Flanged inlet	Black & white	AHL630FI				
	3P-3W	 L11-30R L11-30P	Ultra grip plug, 3-phase	Black & white	AHL1130P			
			Ultra grip connector, 3-phase	Black & white	AHL1130C			
			Single receptacle, 3-phase	Black	AHL1130R			
			Flanged outlet, 3-phase	Black & white	AHL1130FO			
Flanged inlet, 3-phase			Black & white	AHL1130FI				
3P-4W	 L15-30R L15-30P	Ultra grip plug, 3-phase	Black & white	AHL1530P				
		Ultra grip connector, 3-phase	Black & white	AHL1530C				
		Single receptacle, 3-phase	Black	AHL1530R				
		Single receptacle, isolated ground, 3-phase	Orange	AHIGL1530R				
		Flanged outlet, 3-phase	Black & white	AHL1530FO				
		Flanged inlet, 3-phase	Black & white	AHL1530FI				
		277	2P-3W	 L7-30R L7-30P	Ultra grip plug	Black & white	AHL730P	
Ultra grip connector	Black & white				AHL730C			
Single receptacle	Black				AHL730R			
Single receptacle, isolated ground	Orange				AHIGL730R			
Flanged outlet	Black & white				AHL730FO			
Flanged inlet	Black & white				AHL730FI			
480	2P-3W				 L8-30R L8-30P	Ultra grip plug	Black & white	AHL830P
		Ultra grip connector	Black & white	AHL830C				
		Single receptacle	Black	AHL830R				
		Single receptacle, isolated ground	Orange	AHIGL830R				
		Flanged outlet	Black & white	AHL830FO				
		Flanged inlet	Black & white	AHL830FI				
	3P-3W	 L12-30R L12-30P	Auto grip plug, 3-phase	Black & white	CWL1230P			
			Auto grip connector, 3-phase	Black & white	CWL1230C			
			Single receptacle, 3-phase	Black	CWL1230R			
			Flanged outlet, 3-phase	Black & white	CWL1230FO			
			Flanged inlet, 3-phase	Black & white	CWL1230FI			
	3P-4W	 L16-30R L16-30P	Ultra grip plug, 3-phase	Black & white	AHL1630P			
			Ultra grip connector, 3-phase	Black & white	AHL1630C			
			Single receptacle, 3-phase	Black	AHL1630R			
			Flanged outlet, 3-phase	Black & white	AHL1630FO			
			Flanged inlet, 3-phase	Black & white	AHL1630FI			
			600	2P-3W	 L9-30R L9-30P	Auto grip plug	Black & white	CWL930P
						Auto grip connector	Black & white	CWL930C
						Single receptacle	Black	CWL930R
Flanged outlet	Black & white	CWL930FO						
Flanged inlet	Black & white	CWL930FI						



AHL630P



AHL630C



AHL730R



AHL830R



AHL1630R

Accessories: page 16

Dimensions & cord diameters: page 18 & 19

Spec information: page 20-25

Compliances: page 27

# Arrow Hart industrial grade locking devices



AHL2130P



AHL2130C



AHL2130R



AHL2130FO



AHL2130FI

## 30A Industrial Grade Locking Devices

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.
600	3P-3W	 L13-30R L13-30P	Auto grip plug, 3-phase	Black & white	CWL1330P
			Auto grip connector, 3-phase	Black & white	CWL1330C
			Single receptacle, 3-phase	Black	CWL1330R
			Flanged outlet, 3-phase	Black & white	CWL1330FO
			Flanged inlet, 3-phase	Black & white	CWL1330FI
			3P-4W	 L17-30R L17-30P	Ultra grip plug, 3-phase
Ultra grip connector, 3-phase	Black & white	AHL1730C			
Single receptacle, 3-phase	Black	AHL1730R			
Flanged outlet, 3-phase	Black & white	AHL1730FO			
Flanged inlet, 3-phase	Black & white	AHL1730FI			
120/208	4P-4W	 L18-30R L18-30P			Ultra grip plug, 3-phase
			Ultra grip connector, 3-phase	Black & white	AHL1830C
			Single receptacle, 3-phase	Black	AHL1830R
			Flanged outlet, 3-phase	Black & white	AHL1830FO
			Flanged inlet, 3-phase	Black & white	AHL1830FI
			4P-4W	 Receptacle Plug	Ultra grip plug, 3-phase
Ultra grip connector, 3-phase	Black & white	AH3433N			
Single receptacle, 3-phase	Black	AH3430			
Flanged outlet, 3-phase	Black & white	AH3436N			
Flanged inlet, 3-phase	Black & white	AH3434N			
4P-5W	 L21-30R L21-30P	Ultra grip plug, 3-phase			Black & white
		Ultra grip plug, 3-phase, flat cable	Black & white	AHL2130PF	
		Ultra grip connector, 3-phase	Black & white	AHL2130C	
		Ultra grip connector, 3-phase, flat cable	Black & white	AHL2130CF	
		Single receptacle, 3-phase	Black	AHL2130R	
		Single receptacle, isolated ground, 3-phase	Orange	AHIGL2130R	
125/250	3P-3W	 L10-30R L10-30P	Flanged outlet, 3-phase	Black & white	AHL2130FO
			Flanged inlet, 3-phase	Black & white	AHL2130FI
			Ultra grip plug	Black & white	AHL1030P
			Ultra grip connector	Black & white	AHL1030C
			Single receptacle	Black	AHL1030R
			Flanged outlet	Black & white	AHL1030FO
3P-3W	 Receptacle Plug	Flanged inlet	Black & white	AHL1030FI	
		Ultra grip plug	Black & white	AH3331N	
		Ultra grip connector	Black & white	AH3333N	
		Single receptacle	Black & white	AH3330-2	
		Flanged outlet	Black & white	AH3336N	
		Flanged inlet	Black & white	AH3337N	
3P-4W	 L14-30R L14-30P	Ultra grip plug	Black & white	AHL1430P	
		Ultra grip connector	Black & white	AHL1430C	
		Single receptacle	Black	AHL1430R	
		Single receptacle, isolated ground	Orange	AHIGL1430R	
		Flanged outlet	Black & white	AHL1430FO	
		Flanged inlet	Black & white	AHL1430FI	

Accessories: page 16





Dimensions & cord diameters: page 18 & 19

Spec information: page 20-25

Compliances: page 27

# Arrow Hart industrial grade locking devices

## 30A Industrial Grade Locking Devices

V/AC	Pole-Wire	NEMA	Description	Color	Catalog No.
277/480	4P-4W	 L19-30R L19-30P	Ultra grip plug, 3-phase	Black & white	AHL1930P
			Ultra grip connector, 3-phase	Black & white	AHL1930C
			Single receptacle, 3-phase	Black	AHL1930R
			Flanged outlet, 3-phase	Black & white	AHL1930FO
			Flanged inlet, 3-phase	Black & white	AHL1930FI
4P-5W	 L22-30R L22-30P	Ultra grip plug, 3-phase	Black & white	AHL2230P	
		Ultra grip plug, 3-phase, flat cable	Black & white	AHL2230PF	
		Ultra grip connector, 3-phase	Black & white	AHL2230C	
		Ultra grip connector, 3-phase, flat cable	Black & white	AHL2230CF	
		Single receptacle, 3-phase	Black	AHL2230R	
		Single receptacle, isolated ground, 3-phase	Orange	AHIGL2230R	
		Flanged outlet, 3-phase	Black & white	AHL2230FO	
Flanged inlet, 3-phase	Black & white	AHL2230FI			
347/600	4P-4W	 L20-30R L20-30P	Ultra grip plug, 3-phase	Black & white	AHL2030P
			Ultra grip connector, 3-phase	Black & white	AHL2030C
			Single receptacle, 3-phase	Black	AHL2030R
			Flanged outlet, 3-phase	Black & white	AHL2030FO
			Flanged inlet, 3-phase	Black & white	AHL2030FI
4P-5W	 L23-30R L23-30P	Ultra grip plug, 3-phase	Black & white	AHL2330P	
		Ultra grip plug, 3-phase, flat cable	Black & white	AHL2330PF	
		Ultra grip connector, 3-phase	Black & white	AHL2330C	
		Ultra grip connector, 3-phase, flat cable	Black & white	AHL2330CF	
		Single receptacle, 3-phase	Black	AHL2330R	
		Single receptacle, isolated ground, 3-phase	Orange	AHIGL2330R	
		Flanged outlet, 3-phase	Black & white	AHL2330FO	
Flanged inlet, 3-phase	Black & white	AHL2330FI			



AHL2230P



AHL2230C



AHL2230R



AHL2230FO



AHL2230FI

Accessories: page 16  
 Dimensions & cord diameters: page 18 & 19  
 Spec information: page 20-25  
 Compliances: page 27

# Arrow Hart industrial grade accessories



BS1



BM2



BL1



WLRs1



7420



WP1

## Accessories for Industrial Grade Straight Blade & Locking Devices

Amp	Electrical Characteristics					Boot		Receptacle Covers			FI/FO Cover	Receptacle (1-Gang) 302/304 Stainless Steel Wallplates					
	NEMA	Pole-Wire	G/NG	Voltage	Phase	Plug	Conn.	Heavy-duty Single	Duplex	Standard Single		Standard Single	Duplex	Mid-size Single	Duplex	Oversized Single	Duplex
10/15	NON	3P-3W	NG	277/480	—	BS1	BS2	WLRs1	—	7420	WP1	93091	—	93991	—	93891	—
15	L1-15	2P-2W	NG	125	—	—	—	WLRs1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	5-15	2P-3W		125	—	BS1	BS2	WLRs1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	L5-15	2P-3W	G	125	—	BS1	BS2	WLRs1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	6-15	2P-3W		250	—	BS1	BS2	WLRs1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	L6-15	2P-3W	G	250	—	BS1	BS2	WLRs1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	L7-15	2P-3W	G	277	—	BS1	BS2	WLRs1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
20/10	NON	4P-5W	G	250/600	—	BL1	BL2	—	—	—	WP2	93111	—	PJ720*	—	—	—
20	5-20	2P-3W		125	—	BS1	BS2	WLRs1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	L5-20	2P-3W	G	125	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L2-20	2P-2W	NG	250	—	BS1	BS2	WLRs1	—	7420	WP1	93091	—	93991	—	93891	—
	6-20	2P-3W		250	—	BS1	BS2	WLRs1	WLRD1	7420	WP1	93091	93101	93991	93901	93891	93801
	L6-20	2P-3W	G	250	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L11-20	3P-3W	NG	250	3	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L15-20	3P-4W	G	250	3	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L7-20	2P-3W	G	277	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L8-20	2P-3W	G	480	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L12-20	3P-3W	NG	480	3	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L16-20	3P-4W	G	480	3	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L9-20	2P-3W	G	600	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L18-20	4P-4W	NG	120/208	3	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	NON	4P-4W	NG	120/208	3-Y	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L21-20	4P-5W	G	120/208	3-Y	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L10-20	3P-3W	NG	277/480	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	NON	3P-3W	NG	277/480	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L14-20	3P-4W	G	277/480	—	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L19-20	4P-4W	NG	277/480	—	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L22-20	4P-5W	G	277/480	—	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L20-20	4P-4W	NG	347/600	—	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
L23-20	4P-5W	G	347/600	—	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—	
30	L5-30	2P-3W	G	125	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L6-30	2P-3W	G	250	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L11-30	3P-3W	NG	250	3	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L15-30	3P-4W	G	250	3	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L7-30	2P-3W	G	277	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L8-30	2P-3W	G	480	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L12-30	3P-3W	NG	480	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L16-30	3P-4W	G	480	3	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L9-30	2P-3W	G	600	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L13-30	3P-3W	NG	600	3	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L17-30	3P-4W	G	600	3	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L18-30	4P-4W	NG	120/208	3	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	NON	4P-4W	NG	120/208	3-Y	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L21-30	4P-5W	G	120/208	3-Y	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L10-30	3P-3W	NG	277/480	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	NON	3P-3W	NG	277/480	—	BM1	BM2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L14-30	3P-4W	G	277/480	—	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L19-30	4P-4W	NG	277/480	3-Y	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L22-30	4P-5W	G	277/480	3-Y	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L20-30	4P-4W	NG	347/600	3-Y	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—
	L23-30	4P-5W	G	347/600	3-Y	BL1	BL2	WLRs2	—	7420	WP2	93111	—	PJ720*	—	—	—


Note: \*Polycarbonate only (B, GY, V, W)



# Arrow Hart industrial grade straight blade plug & connector dimensions


**Table 1. Ultra Grip Plugs & Connectors**

Family	A	B	C	D	Cord Diameter
Ultra grip plug	1.38" (35.1mm)	2.07" (52.6mm)	1.69" (42.9mm)	1.55" (39.4mm)	0.25 - 0.66" (6.4-16.8mm)
Ultra grip connector	1.38" (35.1mm)	2.89" (73.4mm)	1.69" (42.9mm)	1.55" (39.4mm)	0.25 - 0.66" (6.4-16.8mm)




**Table 2. Safety Grip Plugs & Connectors**

Family	A	B	C	D	Cord Diameter
Safety grip plug, hospital grade	1.40" (35.6mm)	2.11" (53.6mm)	1.53" (38.9mm)	1.45" (36.8mm)	0.30-0.65" (7.6-16.6mm)
Safety grip plug, angled, hospital grade	1.39" (35.3mm)	1.29" (32.8mm)	1.52" (38.6mm)	2.09" (53.1mm)	0.30-0.65" (7.6-16.6mm)
Safety grip plug, angled	1.38" (35.1mm)	1.30" (33.0mm)	1.51" (38.4mm)	2.07" (52.6mm)	0.30-0.65" (7.6-16.6mm)
Safety grip connector, hospital grade	1.38" (35.1mm)	2.98" (75.7mm)	1.52" (38.6mm)	1.45" (36.8mm)	0.30-0.65" (7.6-16.6mm)




**Table 3. Quick Grip Plugs & Connectors**

Family	A	B	C	D	Cord Diameter
Quick grip plug	1.40" (35.6mm)	1.96" (50.0mm)	1.67" (42.4mm)	1.46" (37.1mm)	0.23-0.65" (5.8-16.5mm)
Quick grip connector	1.40" (35.6mm)	2.59" (65.8mm)	1.67" (42.4mm)	1.46" (37.1mm)	0.23-0.65" (5.8-16.5mm)



**Table 4. Flanged Inlets & Outlets**



Family	A	B	C	D	E	F
Flanged outlet, nylon	1.14" (29.0mm)	0.92" (23.4mm)	1.72" (43.7mm)	2.56" (65.0mm)	0.25" (6.4mm)	2.09" (53.1mm)
Flanged inlet, nylon	1.14" (29.0mm)	0.92" (23.4mm)	1.72" (43.7mm)	2.56" (65.0mm)	0.25" (6.4mm)	2.09" (53.1mm)
Flanged outlet, metal	1.40" (35.6mm)	1.11" (28.2mm)	1.44" (35.6mm)	2.47" (62.7mm)	0.20" (5.1mm)	2.04" (52.6mm)
Flanged inlet, metal	1.57" (39.9mm)	1.36" (34.5mm)	1.64" (38.9mm)	2.48" (63.0mm)	0.286" (7.3mm)	2.01" (51.1mm)



# Arrow Hart industrial grade locking device dimensions




**Table 5. Ultra Grip Locking Plugs & Connectors**

Family	A	B	C	D	Cord Diameter
Ultra grip plug, 2P-3W, 3P-3W	1.78" (45.2mm)	2.59" (65.8mm)	2.23" (56.6mm)	2.10" (53.3mm)	0.38-1.00" (9.6 - 25.4mm)
Ultra grip plug, 3P-4W, 4P-4W, 4P-5W	2.18" (55.4mm)	2.82" (71.6mm)	2.13" (54.1mm)	2.30" (58.4mm)	0.38-1.16" (9.6 - 29.5mm)
Ultra grip connector, 2P-3W, 3P-3W	1.78" (45.2mm)	3.61" (91.7mm)	2.23" (56.6mm)	2.10" (53.3mm)	0.38-1.00" (9.6 - 25.4mm)
Ultra grip connector, 3P-4W, 4P-4W, 4P-5W	1.97" (50.0mm)	3.84" (97.5mm)	2.46" (62.5mm)	2.30" (58.4mm)	0.38-1.16" (9.6 - 29.5mm)






**Table 6. Safety Grip Locking Plugs & Connectors**

Family	A	B	C	Cord Diameter
Safety grip 15/10A, non-NEMA plug	1.36" (34.5mm)	2.09" (53.1mm)	1.51" (38.4mm)	0.33-0.66" (8.4-16.8mm)
Safety grip NEMA L1-15 plug	1.55" (39.4mm)	1.56" (39.6mm)	1.57" (39.9mm)	0.31-0.47" (7.9-11.9mm)
Safety grip 20A: NEMA L2-20 plug	1.37" (34.8mm)	2.07" (52.6mm)	1.51" (38.4mm)	0.33-0.66" (8.4-16.8mm)
Safety grip 20A: non-NEMA 277/480V/AC plug	1.75" (44.4mm)	2.42" (61.5mm)	2.14" (54.4mm)	0.38-1.00" (9.7-25.4mm)
Safety grip NEMA L24-20 plug	1.82" (46.2mm)	2.63" (66.8mm)	2.12" (53.8mm)	0.33-1.15" (8.4-29.2mm)
Safety grip 20A 2P-3W, 3P-3W plug	1.16" (29.5mm)	2.48" (63.0mm)	2.14" (54.4mm)	0.38-1.00" (9.7-25.4mm)
Safety grip 20A: 4P-4W plug	1.93" (49.0mm)	2.80" (71.1mm)	2.33" (59.2mm)	0.63-1.16" (16.0-29.5mm)
Safety grip 30A: 2P-3W, 3P-3W plug	1.91" (48.5mm)	2.48" (63.0mm)	2.14" (54.4mm)	0.38-1.00" (9.7-25.4mm)
Safety grip 15/10A, non-NEMA connector	1.36" (34.5mm)	2.87" (72.9mm)	1.52" (38.6mm)	0.33-0.66" (8.4-16.8mm)
Safety grip NEMA L1-15 connector	1.28" (32.5mm)	2.04" (51.8mm)	1.36" (34.5mm)	0.30-0.56" (7.6-14.2mm)
Safety grip 20A, NEMA L2-20 connector	1.37" (34.8mm)	2.01" (51.1mm)	1.52" (38.6mm)	0.33-0.66" (8.4-16.8mm)
Safety grip 20A: non-NEMA 277/480V/AC connector	1.75" (44.4mm)	3.32" (84.3mm)	2.14" (54.4mm)	0.38-1.00" (9.7-25.4mm)
Safety grip 20A, 2P-3W, 3P-3W connector	1.83" (46.5mm)	3.90" (99.1mm)	2.13" (54.1mm)	0.38-1.00" (9.7-25.4mm)
Safety grip 20A: 4P-4W connector	1.93" (49.0mm)	3.75" (95.3mm)	2.31" (58.7mm)	0.63-1.16" (16.0-29.5mm)
Safety grip 30A: 2P-3W, 3P-3W connector	1.85" (47.0mm)	3.55" (90.2mm)	2.14" (54.4mm)	0.38-1.00" (9.7-25.4mm)



**Table 7. Locking Plugs & Connectors**




Family	A	B	C	D	Cord Diameter
Plug, NEMA L9-20, L9-30	1.83" (47.5mm)	2.85" (72.3mm)	2.13" (54.1mm)	—	0.30-0.95" (7.6-24.1mm)
Plug, NEMA L12-20, L12-30, L13-30	1.83" (47.0mm)	2.85" (72.3mm)	2.13" (54.1mm)	—	0.38-1.00" (9.5-25.4mm)
Plug, Angled 15A	1.37" (34.8mm)	1.30" (33.0mm)	1.50" (38.1mm)	2.08" (52.8mm)	0.33-0.66" (8.4-16.8mm)
Connector, NEMA L9-20, L9-30	1.83" (47.5mm)	3.90" (99.1mm)	2.13" (54.1mm)	—	0.30-0.95" (7.6-24.1mm)
Connector, NEMA L12-20, L12-30, L13-30	1.83" (47.5mm)	3.90" (99.1mm)	2.13" (54.1mm)	—	0.38-1.00" (9.5-25.4mm)



# Arrow Hart industrial grade locking device dimensions





**Table 8. Locking Receptacles**

Family	A	B	C	D	E	F
Small receptacle, 10/15A	1.40" (35.6mm)	1.53" (38.9mm)	1.72" (43.7mm)	0.82" (20.8mm)	3.22" (81.8mm)	4.03" (102.4mm)
Small receptacle, NEMA L1-15	1.36" (34.5mm)	1.40" (35.6mm)	1.68" (42.7mm)	0.95" (24.1mm)	3.33" (84.6mm)	3.69" (93.7mm)
Small receptacle, NEMA L2-20	1.37" (34.8mm)	1.37" (34.8mm)	2.02" (51.3mm)	1.12" (28.4mm)	3.21" (81.5mm)	3.62" (92.0mm)
Small receptacle, NEMA L5-15, L6-15, L7-15	1.39" (35.3mm)	1.54" (39.1mm)	1.72" (43.7mm)	0.82" (20.8mm)	3.21" (81.5mm)	4.04" (102.6mm)
NEMA L24-20	1.57" (39.9mm)	1.62" (41.1mm)	2.31" (58.7mm)	1.04" (26.5mm)	3.30" (83.8mm)	3.64" (92.5mm)
20A	1.56" (39.6mm)	1.56" (39.6mm)	2.64" (67.1mm)	1.06" (26.9mm)	3.22" (81.8mm)	3.64" (92.5mm)
30A	1.56" (39.6mm)	1.61" (40.9mm)	2.64" (67.1mm)	1.09" (27.7mm)	3.21" (81.5mm)	3.63" (92.2mm)
Duplex receptacle, 10/15A	1.11" (28.2mm)	1.59" (40.4mm)	2.80" (71.1mm)	0.82" (20.8mm)	3.29" (83.6mm)	4.05" (102.9mm)
Duplex receptacle, 15A	1.09" (27.7mm)	1.50" (38.1mm)	2.63" (66.8mm)	0.97" (24.6mm)	3.32" (84.3mm)	3.63" (92.2mm)






**Table 9. Locking Flanged Inlets**

Family	A	B	C	D	E	F
15A: 2P-2W & 2P-3W	1.56" (39.6mm)	1.92" (48.8mm)	1.72" (43.7mm)	2.56" (65.0mm)	0.25" (6.4mm)	2.09" (53.1mm)
20A: 2P-3W & 3P-3W	2.03" (51.6mm)	2.24" (56.9mm)	2.06" (52.3mm)	2.88" (73.2mm)	0.22" (5.6mm)	1.25" (31.8mm)
20A: 3P-4W, 4P-4W, 4P-5W	2.03" (51.6mm)	2.24" (56.9mm)	2.19" (55.6mm)	3.06" (77.7mm)	0.22" (5.6mm)	1.34" (34.0mm)
20A: NEMA L9-20, L12-20	1.94" (49.3mm)	2.09" (53.1mm)	2.04" (51.8mm)	2.88" (73.2mm)	0.20" (5.1mm)	1.25" (31.8mm)
30A: 2P-3W, 3P-3W	2.03" (51.6mm)	2.24" (56.9mm)	2.06" (52.3mm)	2.88" (73.2mm)	0.22" (5.6mm)	1.25" (31.8mm)
30A: 3P-4W, 4P-4W, 4P-5W	2.03" (51.6mm)	2.24" (56.9mm)	2.19" (55.6mm)	3.06" (77.7mm)	0.22" (5.6mm)	1.34" (34.0mm)
30A: NEMA L9-30, L12-30, L13-30	1.94" (49.3mm)	2.02" (51.3mm)	2.12" (53.8mm)	2.88" (73.2mm)	0.19" (4.8mm)	1.25" (31.8mm)



**Table 10. Locking Flanged Outlets**

Family	A	B	C	D	E	F
15A: 2P-2W & 2P-3W	1.14" (29.0mm)	0.92" (23.4mm)	1.72" (43.7mm)	2.56" (65.0mm)	0.25" (6.4mm)	2.09" (53.1mm)
20A: NEMA L2-20	1.48" (37.6mm)	1.69" (42.9mm)	1.56" (39.7mm)	2.50" (63.5mm)	0.54" (13.7mm)	2.06" (52.4mm)
20A: 2P-3W, 3P-3W	2.03" (51.6mm)	2.24" (56.9mm)	2.06" (52.3mm)	2.88" (73.2mm)	0.22" (5.6mm)	1.25" (31.8mm)
20A: 3P-4W, 4P-4W, 4P-5W	2.03" (51.6mm)	2.24" (56.9mm)	2.19" (55.6mm)	3.06" (77.7mm)	0.22" (5.6mm)	1.34" (34.0mm)
20A: NEMA L9-20, L12-20	1.94" (49.3mm)	2.09" (53.1mm)	2.04" (51.8mm)	2.87" (72.9mm)	0.19" (4.8mm)	1.25" (31.8mm)
30A: 2P-3W, 3P-3W	2.03" (51.6mm)	2.24" (56.9mm)	2.06" (52.3mm)	2.88" (73.2mm)	0.22" (5.6mm)	1.25" (31.8mm)
30A: 3P-4W, 4P-4W, 4P-5W	2.03" (51.6mm)	2.24" (56.9mm)	2.19" (55.6mm)	3.06" (77.7mm)	0.22" (5.6mm)	1.34" (34.0mm)
30A: NEMA L9-30, L12-30, L13-30	1.94" (49.3mm)	2.02" (51.3mm)	2.12" (53.8mm)	2.86" (72.6mm)	0.20" (5.1mm)	1.20" (30.5mm)



# Arrow Hart industrial grade straight blade specifications

**Table 11. Specifications for Plugs & Connectors**

	15 & 20A Hospital Grade Plugs & Connectors	15 & 20A Hospital Grade Quick Grip Plugs & Connectors	15 & 20A Plugs & Connectors	15 & 20A Quick Grip Plugs & Connectors
<b>NEMA Config</b>	5-15, 6-15, 5-20, 6-20	5-15	5-15, 6-15, 5-20, 6-20	5-15, 6-15, 5-20, 6-20
<b>Wiring Type</b>	Back wire	Back wire	Back wire	Back wire
<b>Environmental Specifications</b>	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 75°C (-40°F to 167°F)	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 75°C (-40°F to 167°F)	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 75°C (-40°F to 167°F)	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 75°C (-40°F to 167°F)
<b>Electrical Specifications</b>	<b>Dielectric Voltage:</b> Twice the device rating + 1000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	<b>Dielectric Voltage:</b> Twice the device rating + 1000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	<b>Dielectric Voltage:</b> Twice the device rating + 1000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	<b>Dielectric Voltage:</b> Twice the device rating + 1000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)
<b>Mechanical Specifications</b>	<b>Terminal Accommodation:</b> #18 - #12 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #18 - #12 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #16 - #12 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #18 - #12 AWG <b>Voltage Ratings:</b> Permanently marked on device

**Table 12. Materials for Plugs & Connectors**

	15 & 20A Hospital Grade Plugs & Connectors	15 & 20A Hospital Grade Quick Grip Plugs & Connectors	15 & 20A Plugs & Connectors	15 & 20A Quick Grip Plugs & Connectors
<b>NEMA Config</b>	5-15, 6-15, 5-20, 6-20	5-15	5-15, 6-15, 5-20, 6-20	5-15, 6-15, 5-20, 6-20
<b>Outer Shell</b>	Nylon	Nylon	Nylon	Nylon
<b>Interior Body</b>	Nylon	N/A	Nylon	N/A
<b>Terminal Retainer</b>	Polycarbonate	Polycarbonate	Polycarbonate	Polycarbonate
<b>Blades</b>	0.060" thick brass	0.060" thick brass	0.062" thick brass	0.060" thick brass
<b>Line Contacts</b>	0.031" thick brass	0.031" thick brass	0.031" thick brass	0.031" thick brass
<b>Terminal Clamps</b>	Steel, zinc plated	Steel, zinc plated	Steel, zinc plated	Steel, zinc plated
<b>Terminal Screws</b>	#8-32 steel, brass plated (hot) and zinc plated (neutral screw)	#8-32 steel, brass plated (hot) and nickel plated (neutral screw)	#8-32 steel, brass plated (hot) and nickel plated (neutral screw)	#8-32 steel, brass plated (hot) and nickel plated (neutral screw)
<b>Ground Contact</b>	Brass	Brass	0.041" thick brass	Brass
<b>Ground Screw</b>	#8-32 steel, zinc plated (green)	#8-32 steel, zinc plated (green)	#8-32 steel, zinc plated (green)	#8-32 steel, zinc plated (green)
<b>Assembly/ Mounting Screws</b>	Steel, nickel plated	Steel, zinc plated	Steel, nickel plated	Steel, zinc plated
<b>Cord Clamp</b>	Nylon	Nylon	Nylon	Nylon
<b>Cord Clamp Screws</b>	Steel	Steel	Steel	Steel
<b>Gasket/Dust Shield</b>	EPDM	N/A	EPDM	N/A



# Arrow Hart industrial grade straight blade specifications

**Table 13. Specifications for Flanged Inlets & Outlets**

	15 & 20A Flanged Inlets	15 & 20A Flanged Outlets
<b>NEMA Config</b>	5-15, 6-15, 5-20, 6-20	5-15, 6-15, 5-20, 6-20
<b>Wiring Type</b>	Side wire	Side wire
<b>Environmental Specifications</b>	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 105°C (-40°F to 221°F)	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 105°C (-40°F to 221°F)
<b>Electrical Specifications</b>	<b>Dielectric Voltage:</b> Twice the device rating + 1000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) at maximum rated current (DC)	<b>Dielectric Voltage:</b> Twice the device rating + 1000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
<b>Mechanical Specifications</b>	<b>Terminal Accommodation:</b> #14 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #14 AWG <b>Voltage Ratings:</b> Permanently marked on device

**Table 14. Materials for Flanged Inlets & Outlets**

	15 & 20A Flanged Inlets	15 & 20A Flanged Outlets
<b>NEMA Config</b>	5-15, 6-15, 5-20, 6-20	5-15, 6-15, 5-20, 6-20
<b>Outer Shell</b>	Nylon (except 5278 steel)	Nylon (except 5246) steel
<b>Interior Body</b>	Lexan (except 5278 urea)	Nylon
<b>Terminal Retainer</b>	Lexan (except 5278 urea)	Lexan (except 5246) nylon
<b>Blades</b>	0.062" thick brass	N/A
<b>Line Contacts</b>	N/A	0.031" thick brass
<b>Terminal Clamps</b>	Steel	Steel
<b>Terminal Screws</b>	#8-32 steel (except 5278 #8-32 brass)	#8-32 steel (except 5246, brass)
<b>Ground Screw</b>	#8-32 steel (except 5278 #8-32 brass)	#8-32 steel (green)
<b>Assembly Screws/ Rivets</b>	Steel screws (except 5278 steel rivets, zinc plated)	Steel screws (except 5246C steel rivets)

# Arrow Hart industrial grade locking specifications

**Table 15. Specifications for Plugs & Connectors**

	15A Plugs & Connectors	15A Plugs & Connectors	15 & 20A Plugs & Connectors, 2-Pole 2-Wire
<b>NEMA Config</b>	L5-15, L6-15, L7-15	Non-NEMA 10/15A	L1-15, L2-20
<b>Wiring Type</b>	Back wire	Back wire	Back wire
<b>Environmental Specifications</b>	<b>Flammability:</b> Meets UL94 requirements; V0 rated <b>Temperature Rating:</b> -40°C to 60°C (-40°F to 140°F)	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 60°C (-40°F to 140°F)	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 60°C (-40°F to 140°F)
<b>Electrical Specifications</b>	<b>Dielectric Voltage:</b> Twice the device rating + 1000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 250 cycles of overload at 200% of rated current (DC)	<b>Dielectric Voltage:</b> Twice the device rating + 1000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 50 cycles of overload at 150% of rated current (DC)	<b>Dielectric Voltage:</b> Twice the device rating + 1000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 50 cycles of overload at 150% of rated current (DC)
<b>Mechanical Specifications</b>	<b>Terminal Accommodation:</b> #16 - #12 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #16 - #12 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #16 - #12 AWG <b>Voltage Ratings:</b> Permanently marked on device

**Table 17. Materials for Plugs & Connectors**

	15A Plugs & Connectors	15A Plugs & Connectors	15 & 20A Plugs & Connectors, 2-Pole 2-Wire
<b>NEMA Config</b>	L5-15, L6-15, L7-15	Non-NEMA 10/15A	L1-15, L2-20
<b>Outer Shell</b>	Nylon	Nylon	Nylon
<b>Interior Body</b>	Nylon	Nylon	Nylon
<b>Terminal Retainer</b>	Polycarbonate	Polycarbonate	Nylon
<b>Blades</b>	Brass	Brass	Brass
<b>Line Contacts</b>	Brass	Brass, tin plated	Brass (except L2-20 tin plated)
<b>Terminal Clamps</b>	Steel, zinc plated	Steel, zinc plated	Steel, zinc plated
<b>Terminal Screws</b>	#8-32 steel, brass plated, nickel plated (neutral screw)	#8-32 steel, brass plated, nickel plated (neutral screw)	Brass
<b>Ground Screw</b>	#8-32 brass plated (green)	#8-32 steel, brass plated (green)	Brass
<b>Assembly Screws</b>	Steel, nickel plated	Steel, nickel plated	Steel, nickel plated (except L1-15 steel)
<b>Gasket/Dust Shield</b>	EPDM	Neoprene	Neoprene
<b>Cord Clamp Screws</b>	Steel, nickel plated	Steel, nickel plated	Steel, nickel plated
<b>Cord Clamp</b>	Nylon	Nylon	Nylon

**Table 16. Specifications for Plugs & Connectors**

	20 & 30A Ultra Grip Plugs & Connectors	20 & 30A Auto Grip Plugs & Connectors	20A Safety Grip Plugs & Connectors
<b>NEMA Config</b>	L5-20, L6-20, L11-20, L15-20, L7-20, L8-20, L16-20, L18-20, L21-20, L10-20, L14-20, L19-20, L22-20, L20-20, L23-20, L5-30, L6-30, L11-30, L15-30, L7-30, L8-30, L16-30, L17-30, L18-30, L21-30, L10-30, L14-30, L19-30, L22-30, L20-30, L23-30, Non-NEMA 30A	L12-20, L9-20, L12-30, L9-30, L13-30	L24-20, Non-NEMA 20A
<b>Wiring Type</b>	Back wire	Back wire	Back wire
<b>Environmental Specifications</b>	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 60°C (-40°F to 140°F), (except flat cable: -40°C to 75°C (-40°F to 167°F))	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 60°C (-40°F to 140°F)	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 60°C (-40°F to 140°F), (except L24-20, -40°C to 75°C (-40°F to 167°F))
<b>Electrical Specifications</b>	<b>Dielectric Voltage:</b> Twice the device rating + 1000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) 50 cycles of overload at 150% of rated current (DC)	<b>Dielectric Voltage:</b> Twice the device rating + 1000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) 50 cycles of overload at 150% of rated current (DC)	<b>Dielectric Voltage:</b> Twice the device rating + 1000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) 50 cycles of overload at 150% of rated current (DC)
<b>Mechanical Specifications</b>	<b>Terminal Accommodation:</b> #16 - #8 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #18 - #8 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #16 - #8 AWG (except L24-20 #18 - #8) <b>Voltage Ratings:</b> Permanently marked on device

# Arrow Hart industrial grade locking specifications

**Table 18. Materials for Plugs & Connectors**

	20 & 30A Ultra Grip Plugs & Connectors	20 & 30A Auto Grip Plugs & Connectors	20A Safety Grip Plugs & Connectors
<b>NEMA Config</b>	L5-20, L6-20, L11-20, L15-20, L7-20, L8-20, L16-20, L18-20, L21-20, L10-20, L14-20, L19-20, L22-20, L20-20, L23-20, L5-30, L6-30, L11-30, L15-30, L7-30, L8-30, L16-30, L17-30, L18-30, L21-30, L10-30, L14-30, L19-30, L22-30, L20-30, L23-30, Non-NEMA 30A	L12-20, L9-20, L12-30, L9-30, L13-30	L24-20, Non-NEMA 20A
<b>Outer Shell</b>	Nylon	Nylon	Nylon
<b>Interior Body</b>	Nylon	Nylon	Nylon
<b>Terminal Retainer</b>	Polycarbonate	Polycarbonate	Polycarbonate
<b>Blades</b>	Brass	Brass	Brass
<b>Line Contacts</b>	Brass, tin plated	Brass	Brass
<b>Terminal Clamps</b>	Steel, tin plated	Steel	Steel
<b>Terminal Screws</b>	#10-32 brass, zinc plated (neutral screw)	#10-32 steel, nickel plated (neutral screw)	#8-32 brass zinc plated (neutral screw), (except L24-20 brass)
<b>Ground Screw</b>	#10-32 brass	#10-32 brass	#8-32 brass plated (green)
<b>Assembly Screws</b>	Steel, nickel plated	Steel, zinc plated	Steel, nickel plated
<b>Gasket/Dust Shield</b>	EPDM	EPDM	Neoprene
<b>Cord Clamp Screws</b>	Steel, nickel plated	Steel, zinc plated	Steel, nickel plated
<b>Cord Clamp</b>	Nylon	Nylon	Nylon

**Table 19. Specifications for Receptacles**

	15A Single & Duplex Receptacles	15A Single & Duplex Receptacles	15A Isolated Ground Receptacles	20A Single Receptacle
<b>NEMA Config</b>	L5-15, L6-15, L7-15, Non-NEMA 15/10A	L1-15	L5-15, L6-15	L2-20, L24-20
<b>Wiring Type</b>	Back & side wire	Back & side wire	Back & side wire	Back & side wire
<b>Environmental Specifications</b>	<b>Flammability:</b> Meets UL94 requirements; V0 rated <b>Temperature Rating:</b> -40°C to 115°C (-40°F to 239°F)	<b>Flammability:</b> Meets UL94 requirements; V0 rated <b>Temperature Rating:</b> -40°C to 105°C (-40°F to 221°F)	<b>Flammability:</b> Meets UL94 requirements; V0 rated <b>Temperature Rating:</b> -40°C to 115°C (-40°F to 239°F)	<b>Flammability:</b> Meets UL94 requirements; V0 rated, (except L24-20; V2 rated) <b>Temperature Rating:</b> -40°C to 105°C (-40°F to 221°F), (except L24-20, -40°C to 115°C (-40°F to 239°F))
<b>Electrical Specifications</b>	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC), (except Non-NEMA 15/10A, Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC))	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
<b>Mechanical Specifications</b>	<b>Terminal Accommodation:</b> #14 - #10 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #14 - #10 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #14 - #10 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #14 - #10 AWG <b>Voltage Ratings:</b> Permanently marked on device

**Table 20. Materials for Receptacles**

	15A Single & Duplex Receptacles	15A Single & Duplex Receptacles	15A Isolated Ground Receptacles	20A Single Receptacle
<b>NEMA Config</b>	L5-15, L6-15, L7-15	L1-15	L5-15, L6-15	L2-20, L24-20
<b>Face</b>	Glass-filled nylon	Glass-filled nylon	Glass-filled nylon	Glass-filled nylon
<b>Base</b>	Glass-filled nylon	Glass-filled nylon	Glass-filled nylon	Glass-filled nylon
<b>Mounting Strap</b>	0.050" thick pre-plated steel	0.050" thick steel, zinc plated	0.050" thick pre-plated steel	0.050" thick steel, zinc plated (except L24-20, brass)
<b>Auto Ground Clip</b>	Yes	N/A	Yes	N/A
<b>Line Contacts</b>	0.036" thick brass	0.036" thick bronze	0.036" thick brass	0.032" thick brass, bronze (except L24-20, brass)
<b>Terminal Screws</b>	#8-32 brass screws, nickel plated	#8-32 brass	#8-32 brass screws, nickel plated	#8-32 brass, tin plated (except L24-20, brass)
<b>Ground Screw</b>	#8-32 brass screw (green)	N/A	#8-32 brass screw (green)	N/A (except L24-20, brass)
<b>Mounting Screws</b>	Steel, zinc plated	Steel, zinc plated	Steel, zinc plated	Steel, zinc plated

# Arrow Hart industrial grade locking specifications

**Table 21. Specifications for Receptacles**

	20A Single Receptacles	30A Single Receptacles	20 & 30A Isolated Ground Single Receptacles
<b>NEMA Config</b>	L5-20, L6-20, L7-20, L8-20, L9-20, L10-20, L11-20, L12-20, L14-20, L15-20, L16-20, L18-20, L19-20, L20-20, L21-20, L22-20, L23-20, Non-NEMA 20A	L5-30, L6-30, L7-30, L8-30, L9-30, L10-30, L11-30, L12-30, L13-30, L14-30, L15-30, L16-30, L17-30, L18-30, L19-30, L20-30, L21-30, L22-30, L23-30, Non-NEMA 30A	L5-20, L6-20, L7-20, L8-20, L5-30, L6-30, L7-30, L8-30, L14-20, L15-20, L16-20, L14-30, L15-30, L16-30, L21-20, L22-20, L23-20, L21-30, L22-30, L23-30
<b>Wiring Type</b>	Back & side wire	Back & side wire	Back & side wire
<b>Environmental Specifications</b>	<b>Flammability:</b> Meets UL94 requirements; V0 rated <b>Temperature Rating:</b> -40°C to 60°C (-40°F to 140°F)	<b>Flammability:</b> Meets UL94 requirements; V0 rated <b>Temperature Rating:</b> -40°C to 60°C (-40°F to 140°F)	<b>Flammability:</b> Meets UL94 requirements; V0 rated <b>Temperature Rating:</b> -40°C to 70°C (-40°F to 158°F)
<b>Electrical Specifications</b>	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
<b>Mechanical Specifications</b>	<b>Terminal Accommodation:</b> #14 - #8 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #14 - #8 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #14 - #8 AWG <b>Voltage Ratings:</b> Permanently marked on device

**Table 22. Materials for Receptacles**

	20A Single Receptacles	30A Single Receptacles	20 & 30A Isolated Ground Single Receptacles
<b>NEMA Config</b>	L5-20, L6-20, L7-20, L8-20, L9-20, L10-20, L11-20, L12-20, L14-20, L15-20, L16-20, L18-20, L19-20, L20-20, L21-20, L22-20, L23-20, Non-NEMA 20A	L5-30, L6-30, L7-30, L8-30, L9-30, L10-30, L11-30, L12-30, L13-30, L14-30, L15-30, L16-30, L17-30, L18-30, L19-30, L20-30, L21-30, L22-30, L23-30, Non-NEMA 30A	L5-20, L6-20, L7-20, L8-20, L5-30, L6-30, L7-30, L8-30, L14-20, L15-20, L16-20, L14-30, L15-30, L16-30, L21-20, L22-20, L23-20, L21-30, L22-30, L23-30
<b>Face</b>	Glass-filled nylon	Glass-filled nylon	Glass-filled nylon
<b>Base</b>	Glass-filled nylon	Glass-filled nylon	Glass-filled nylon
<b>Mounting Strap</b>	0.050" thick steel, zinc plated	0.050" thick steel, zinc plated	0.050" thick steel, zinc plated
<b>Line Contacts</b>	0.041" thick brass	0.041" thick brass	0.041" thick brass
<b>Terminal Screws</b>	#10-32 brass, nickel plated (neutral screw)	#10-32 brass, nickel plated (neutral screw)	#10-32 brass, nickel plated (neutral screw)
<b>Ground Screw</b>	#10-32 brass (green)	#10-32 brass (green)	#10-32 brass (green)
<b>Terminal Clamps/Plates</b>	0.041" thick brass	0.041" thick brass	0.041" thick brass
<b>Ground Contacts</b>	0.041" thick brass	0.041" thick brass	0.041" thick brass
<b>Back Plate</b>	0.041" thick brass, nickel plated	0.041" thick brass, nickel plated	0.041" thick brass, nickel plated
<b>Mounting Screws</b>	Steel, zinc plated	Steel, zinc plated	Steel, zinc plated

**Table 23. Specifications for Flanged Inlets & Outlets**

	15A Flanged Inlets & Outlets	15 & 20A Flanged Inlets & Outlets	20 & 30A Flanged Inlets & Outlets
<b>NEMA Config</b>	L5-15, L6-15, L7-15	L1-15, L2-20	AHL520FI, AHL520FO, AHL620FI, AHL830FI, AHL1120FO, AHL1430FI, AHL1430FO, AHL2130FI, AHL2130FO
<b>Wiring Type</b>	Back wire	Side wire	Back wire
<b>Environmental Specifications</b>	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 75°C (-40°F to 167°F)	<b>Flammability:</b> Meets UL94 requirements; V0 rated <b>Temperature Rating:</b> -40°C to 105°C (-40°F to 221°F)	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 60°C (-40°F to 140°F)
<b>Electrical Specifications</b>	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Flanged outlets: max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC); flanged inlets; max. 30°C (86°F) @ maximum rated current (DC)	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Flanged outlets: max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC); flanged inlets; max. 30°C (86°F) @ maximum rated current (DC)	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Flanged outlets: max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC); flanged inlets; max. 30°C (86°F) @ maximum rated current (DC)
<b>Mechanical Specifications</b>	<b>Terminal Accommodation:</b> #14 - #10 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #14 - #8 AWG (L2-20 #14 - #10 AWG) <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #14 - #8 AWG <b>Voltage Ratings:</b> Permanently marked on device

# Arrow Hart industrial grade locking specifications

**Table 24. Materials for Flanged Inlets & Outlets**

	15A Flanged Inlets & Outlets	15 & 20A Flanged Inlets & Outlets	20 & 30A Flanged Inlets & Outlets
<b>NEMA Config</b>	L5-15, L6-15, L7-15	L1-15, L2-20	AHL520FI, AHL520FO, AHL620FI, AHL830FI, AHL1120FO, AHL1430FI, AHL1430FO, AHL2130FI, AHL2130FO
<b>Outer Shell</b>	Nylon	Plated brass	Nylon
<b>Interior Body</b>	Nylon	GF Nylon (L1-15FI, Phenolic)	Nylon
<b>Terminal Retainer</b>	Polycarbonate	N/A	Polycarbonate
<b>Blades</b>	0.062" thick brass	0.062" thick brass	0.062" thick brass
<b>Line Contacts</b>	0.031" thick brass	0.031" thick brass (L1-15, 0.032" thick bronze)	0.031" thick brass
<b>Terminal Clamps</b>	Steel	N/A	Steel
<b>Terminal Screws</b>	#8-32 brass	#6-32 brass	#10-32 brass, nickel plated (neutral screw)
<b>Ground Screw</b>	#8-32 brass (green)	#6-32 brass (green)	#10-32 brass (green)
<b>Assembly Screws</b>	Steel, zinc plated	Steel, zinc plated	Steel, zinc plated
<b>Mounting Screws</b>	Steel, zinc plated	Steel, zinc plated	Steel, zinc plated

**Table 25. Specifications for Flanged Inlets & Outlets**

	20 & 30A Flanged Inlets	20 & 30A Flanged Outlets	20 & 30A Flanged Outlets
<b>NEMA Config</b>	L7-20, L8-20, L5-30, L6-30, L7-30, L10-20, L11-20, L10-30, L11-30, L14-20, L15-20, L16-20, L15-30, L16-30, L17-30, L18-20, L19-20, L20-20, L18-30, L19-30, L20-30, L21-20, L22-20, L23-20, L22-30, L23-30, Non-NEMA 20 & 30A, Non-NEMA 20/10A	L8-20, L6-30, L7-30, L8-30, L10-20, L14-20, L15-20, L16-20, L15-30, L16-30, L17-30, L21-20, L22-20, L23-20, L22-30, L23-30	L6-20, L7-20, L5-30, L10-30, L11-30, L18-20, L19-20, L20-20, L18-30, L19-30, L20-30, Non-NEMA 20 & 30A, Non-NEMA 20/10A
<b>Wiring Type</b>	Back wire	Back wire	Back wire
<b>Environmental Specifications</b>	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 60°C (-40°F to 140°F)	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 60°C (-40°F to 140°F)	<b>Flammability:</b> Meets UL94 requirements; V2 rated <b>Temperature Rating:</b> -40°C to 60°C (-40°F to 140°F)
<b>Electrical Specifications</b>	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) @ maximum rated current (DC)	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)	<b>Dielectric Voltage:</b> ≤300V: 2000V, 301-600V: 3000V per UL498 <b>Current Interrupting:</b> Yes, at full-rated current <b>Temperature Rise:</b> Max. 30°C (86°F) after 50 cycles of overload @ 150% of rated current (DC)
<b>Mechanical Specifications</b>	<b>Terminal Accommodation:</b> #14 - #8 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #14 - #8 AWG <b>Voltage Ratings:</b> Permanently marked on device	<b>Terminal Accommodation:</b> #14 - #8 AWG <b>Voltage Ratings:</b> Permanently marked on device

**Table 26. Materials for Flanged Inlets & Outlets**

	20 & 30A Flanged inlets	20 & 30A Flanged Outlets	20 & 30A Flanged Outlets
<b>NEMA Config</b>	L7-20, L8-20, L5-30, L6-30, L7-30, L10-20, L11-20, L10-30, L11-30, L14-20, L15-20, L16-20, L15-30, L16-30, L17-30, L18-20, L19-20, L20-20, L18-30, L19-30, L20-30, L21-20, L22-20, L23-20, L22-30, L23-30, Non-NEMA 20 & 30A, Non-NEMA 20/10A	L8-20, L6-30, L7-30, L8-30, L10-20, L14-20, L15-20, L16-20, L15-30, L16-30, L17-30, L21-20, L22-20, L23-20, L22-30, L23-30	L6-20, L7-20, L5-30, L10-30, L11-30, L18-20, L19-20, L20-20, L18-30, L19-30, L20-30, Non-NEMA 20 & 30A, Non-NEMA 20/10A
<b>Outer Shell</b>	Nylon	Nylon	Nylon
<b>Interior Body</b>	Nylon	Nylon	Nylon
<b>Terminal Retainer</b>	Polycarbonate	Polycarbonate	Polycarbonate
<b>Blades</b>	0.062" thick brass	N/A	N/A
<b>Line Contacts</b>	N/A	0.031" thick brass	0.031" thick brass
<b>Terminal Clamps</b>	Steel	Steel	Steel
<b>Terminal Screws</b>	#10-32 brass, nickel plated (neutral screw)	#10-32 brass, nickel plated (neutral screw)	#10-32 brass, nickel plated (neutral screw)
<b>Ground Screw</b>	#10-32 brass (green)	#10-32 brass (green)	#10-32 brass (green)
<b>Assembly Screws</b>	Steel, zinc plated	Steel, zinc plated	Steel, zinc plated
<b>Mounting Screws</b>	Steel, zinc plated	Steel, zinc plated	Steel, zinc plated



# Arrow Hart straight blade & locking certifications & compliances

## Straight Blade

Catalog No.	cULus	UL	FCS	CSA	RoHS
AH8215HG	•	•	•	•	•
AH8215HGCG	•	•	•	•	•
AH8215HGGA	•	•	•	•	•
AH8215HGAC	•	•	•	•	•
AH8115W	•	•	•	•	•
AH5266	•	•	•	•	•
AH5266BK	•	•	•	•	•
AH5266A	•	•	•	•	•
AH5965BK	•	•	•	•	•
AH5965Y	•	•	•	•	•
AH8219HG	•	•	•	•	•
AH8219HGCG	•	•	•	•	•
AH8119W	•	•	•	•	•
AH5269	•	•	•	•	•
AH5269BK	•	•	•	•	•
AH5969BK	•	•	•	•	•
AH5969Y	•	•	•	•	•
AH5279C	•	•	•	•	•
AH5246	•	•	•	•	•
AH5278C	•	•	•	•	•
AH5278	•	•	•	•	•
AH8225HGGA	•	•	•	•	•
AH8225HGAC	•	•	•	•	•
AH5666	•	•	•	•	•
AH5666BK	•	•	•	•	•
AH5666Y	•	•	•	•	•
AH5669	•	•	•	•	•
AH5669BK	•	•	•	•	•
AH5669Y	•	•	•	•	•
AH5679C	•	•	•	•	•
AH5678C	•	•	•	•	•
AH8315HG	•	•	•	•	•
AH8315HGGA	•	•	•	•	•
AH8315HGAC	•	•	•	•	•
AH5366	•	•	•	•	•
AH5364BK	•	•	•	•	•
AH5364Y	•	•	•	•	•
AH8319HG	•	•	•	•	•
AH5369	•	•	•	•	•
AH5369BK	•	•	•	•	•
AH5369Y	•	•	•	•	•
AH5779C	•	•	•	•	•
AH5778C	•	•	•	•	•
AH8325HG	•	•	•	•	•
AH8325HGAC	•	•	•	•	•
AH5466	•	•	•	•	•
AH5464BK	•	•	•	•	•
AH5464Y	•	•	•	•	•
AH5469	•	•	•	•	•
AH5469BK	•	•	•	•	•
AH5469Y	•	•	•	•	•
AH5879C	•	•	•	•	•
AH5878C	•	•	•	•	•

## Locking

Catalog No.	cULus	UL	CSA	FCS	RU	RUus	NOM	NAFTA	RoHS
4767	•	•	•	•	•	•	•	•	•
4767AN	•	•	•	•	•	•	•	•	•
4755	•	•	•	•	•	•	•	•	•
7580	•	•	•	•	•	•	•	•	•
7582	•	•	•	•	•	•	•	•	•
7546	•	•	•	•	•	•	•	•	•
7548	•	•	•	•	•	•	•	•	•
7506	•	•	•	•	•	•	•	•	•
7540	•	•	•	•	•	•	•	•	•
CWL115R	•	•	•	•	•	•	•	•	•
CWL115FO	•	•	•	•	•	•	•	•	•
CWL115FI	•	•	•	•	•	•	•	•	•
CWL515P	•	•	•	•	•	•	•	•	•
CWL515PAN	•	•	•	•	•	•	•	•	•
CWL515C	•	•	•	•	•	•	•	•	•
CWL515CAN	•	•	•	•	•	•	•	•	•
4700	•	•	•	•	•	•	•	•	•
5792	•	•	•	•	•	•	•	•	•
CWL515R	•	•	•	•	•	•	•	•	•
IG4700	•	•	•	•	•	•	•	•	•
IGL515R	•	•	•	•	•	•	•	•	•
CWL515FO	•	•	•	•	•	•	•	•	•
CWL515FI	•	•	•	•	•	•	•	•	•
CWL615P	•	•	•	•	•	•	•	•	•
CWL615C	•	•	•	•	•	•	•	•	•
6580	•	•	•	•	•	•	•	•	•
CWL615R	•	•	•	•	•	•	•	•	•
IGL615R	•	•	•	•	•	•	•	•	•
CWL615FO	•	•	•	•	•	•	•	•	•
CWL615FI	•	•	•	•	•	•	•	•	•
CWL715P	•	•	•	•	•	•	•	•	•
CWL715C	•	•	•	•	•	•	•	•	•
4750	•	•	•	•	•	•	•	•	•
CWL715R	•	•	•	•	•	•	•	•	•
CWL715FO	•	•	•	•	•	•	•	•	•
CWL715FI	•	•	•	•	•	•	•	•	•
AH3521BK	•	•	•	•	•	•	•	•	•
AH3523BK	•	•	•	•	•	•	•	•	•
AH3525BK	•	•	•	•	•	•	•	•	•
AH3524BK	•	•	•	•	•	•	•	•	•
AHL520P	•	•	•	•	•	•	•	•	•
AHL520PBK	•	•	•	•	•	•	•	•	•
AHL520C	•	•	•	•	•	•	•	•	•
AHL520CBK	•	•	•	•	•	•	•	•	•
AHL520R	•	•	•	•	•	•	•	•	•
AHIGL520R	•	•	•	•	•	•	•	•	•
AHL520FO	•	•	•	•	•	•	•	•	•
AHL520FI	•	•	•	•	•	•	•	•	•
CWL220P	•	•	•	•	•	•	•	•	•
CWL220C	•	•	•	•	•	•	•	•	•
CWL220R	•	•	•	•	•	•	•	•	•
CWL220FO	•	•	•	•	•	•	•	•	•
AHL620P	•	•	•	•	•	•	•	•	•
AHL620C	•	•	•	•	•	•	•	•	•
AHL620R	•	•	•	•	•	•	•	•	•
AHIGL620R	•	•	•	•	•	•	•	•	•
AHL620FO	•	•	•	•	•	•	•	•	•
AHL620FI	•	•	•	•	•	•	•	•	•

## Locking

Catalog No.	cULus	UL	CSA	FCS	NOM	NAFTA	RoHS
AHL1120P	•	•	•	•	•	•	•
AHL1120C	•	•	•	•	•	•	•
AHL1120R	•	•	•	•	•	•	•
AHL1120FO	•	•	•	•	•	•	•
AHL1120FI	•	•	•	•	•	•	•
AHL1520P	•	•	•	•	•	•	•
AHL1520PBK	•	•	•	•	•	•	•
AHL1520C	•	•	•	•	•	•	•
AHL1520CBK	•	•	•	•	•	•	•
AHL1520R	•	•	•	•	•	•	•
AHIGL1520R	•	•	•	•	•	•	•
AHL1520FO	•	•	•	•	•	•	•
AHL1520FI	•	•	•	•	•	•	•
AHL720P	•	•	•	•	•	•	•
AHL720C	•	•	•	•	•	•	•
AHL720R	•	•	•	•	•	•	•
AHIGL720R	•	•	•	•	•	•	•
AHL720FO	•	•	•	•	•	•	•
AHL720FI	•	•	•	•	•	•	•
L2420P	•	•	•	•	•	•	•
L2420R	•	•	•	•	•	•	•
AHL820P	•	•	•	•	•	•	•
AHL820C	•	•	•	•	•	•	•
AHL820R	•	•	•	•	•	•	•
AHIGL820R	•	•	•	•	•	•	•
AHL820FO	•	•	•	•	•	•	•
AHL820FI	•	•	•	•	•	•	•
CWL1220P	•	•	•	•	•	•	•
CWL1220C	•	•	•	•	•	•	•
CWL1220R	•	•	•	•	•	•	•
CWL1220FO	•	•	•	•	•	•	•
CWL1220FI	•	•	•	•	•	•	•
AHL1620P	•	•	•	•	•	•	•
AHL1620PBK	•	•	•	•	•	•	•
AHL1620C	•	•	•	•	•	•	•
AHL1620CBK	•	•	•	•	•	•	•
AHL1620R	•	•	•	•	•	•	•
AHIGL1620R	•	•	•	•	•	•	•
AHL1620FO	•	•	•	•	•	•	•
AHL1620FI	•	•	•	•	•	•	•
CWL920P	•	•	•	•	•	•	•
CWL920C	•	•	•	•	•	•	•
CWL920R	•	•	•	•	•	•	•
CWL920FO	•	•	•	•	•	•	•
CWL920FI	•	•	•	•	•	•	•
AHL1820P	•	•	•	•	•	•	•
AHL1820C	•	•	•	•	•	•	•
AHL1820R	•	•	•	•	•	•	•
AHL1820FO	•	•	•	•	•	•	•
AHL1820FI	•	•	•	•	•	•	•
7411C	•	•	•	•	•	•	•
7413C	•	•	•	•	•	•	•
7410B	•	•	•	•	•	•	•
7409N	•	•	•	•	•	•	•
7408N	•	•	•	•	•	•	•
AHL2120P	•	•	•	•	•	•	•
AHL2120PBK	•	•	•	•	•	•	•
AHL2120PF	•	•	•	•	•	•	•

Parts are manufactured and designed in accordance with article 4 of the European Union's RoHS2 directive 2011/65/EU

# Arrow Hart locking certifications & compliances

## Locking

Catalog No.	cULus	UL	CSA	FCS	NOM	NAFTA	ROHS
AHL2120C	•						•
AHL2120CBK	•						•
AHL2120CF							•
AHL2120R		•	•	•			•
AHIGL2120R		•	•				•
AHL2120FO		•	•				•
AHL2120FI	•						•
AHL1020P	•						•
AHL1020C	•						•
AHL1020R		•		•			•
AHL1020FO		•	•				•
AHL1020FI	•						•
9965C	•						•
7314C	•						•
7310B		•					•
7328N		•					•
7327N	•						•
AHL1420P	•						•
AHL1420PBK	•						•
AHL1420C	•						•
AHL1420CBK	•						•
AHL1420R		•	•	•			•
AHIGL1420R		•	•				•
AHL1420FOBK		•	•				•
AHL1420FO		•	•				•
AHL1420FIBK	•						•
AHL1420FI	•						•
AHL1920P	•						•
AHL1920C	•						•
AHL1920R		•					•
AHL1920FO		•					•
AHL1920FI	•						•
AHL2220P	•						•
AHL2220C	•						•
AHL2220R		•	•				•
AHL2220FO		•	•				•
AHL2220FI	•						•
AHL2020P	•						•
AHL2020C	•						•
AHL2020R		•					•
AHL2020FO	•						•
AHL2020FI	•						•
AHL2320P	•						•
AHL2320C	•						•
AHL2320R		•	•				•
AHL2320FO		•	•				•
AHL2320FI	•						•
AHL530P	•						•
AHIGL530P	•						•
AHL530C	•						•
AHL530R		•	•	•			•
AHIGL530R		•	•				•
CWL530FO		•	•				•
CWL530FI	•						•
AHL630P	•						•
AHL630C	•						•
AHL630R		•	•	•			•
AHIGL630R		•	•				•

## Locking

Catalog No.	cULus	UL	CSA	FCS	NOM	NAFTA	ROHS
AHL630FO		•	•				•
AHL630FI	•						•
AHL1130P	•						•
AHL1130C	•						•
AHL1130R		•					•
AHL1130FO		•					•
AHL1130FI	•						•
AHL1530P	•						•
AHL1530C	•						•
AHL1530R		•	•	•			•
AHIGL1530R		•	•				•
AHL1530FO		•	•				•
AHL1530FI	•						•
AHL730P	•						•
AHL730C	•						•
AHL730R		•	•	•			•
AHIGL730R		•	•				•
AHL730FO		•	•				•
AHL730FI	•						•
AHL830P	•						•
AHL830C	•						•
AHL830R		•	•				•
AHIGL830R		•	•				•
AHL830FO		•	•				•
AHL830FI	•						•
CWL1230P							•
CWL1230C							•
CWL1230R							•
CWL1230FO							•
CWL1230FI							•
AHL1630P	•						•
AHL1630C	•						•
AHL1630R		•	•				•
AHL1630FO		•	•				•
AHL1630FI	•						•
CWL930P	•						•
CWL930C	•						•
CWL930R		•	•				•
CWL930FO		•	•				•
CWL930FI	•						•
CWL1330P		•	•				•
CWL1330C		•	•				•
CWL1330R		•	•				•
CWL1330FO		•	•				•
CWL1330FI		•	•				•
AHL1730P	•						•
AHL1730C	•						•
AHL1730R		•	•				•
AHL1730FO		•	•				•
AHL1730FI	•						•
AHL1830P	•						•
AHL1830C	•						•
AHL1830R		•	•				•
AHL1830FO		•	•				•
CWL1830FI	•						•
AH3431N	•						•
AH3433N	•						•
AH3430	•						•

## Locking

Catalog No.	cULus	UL	CSA	FCS	NOM	NAFTA	ROHS
AH3436N	•						•
AH3434N	•						•
AHL2130P	•						•
AHL2130PF							•
AHL2130C	•						•
AHL2130CF							•
AHL2130R		•		•			•
AHIGL2130R		•	•				•
AHL2130FO		•	•				•
AHL2130FI	•						•
AHL1030P	•						•
AHL1030C	•						•
AHL1030R		•					•
AHL1030FO		•	•				•
AHL1030FI	•						•
AH3331N	•						•
AH3333N	•						•
AH3330-2		•					•
AH3336N		•					•
AH3337N	•						•
AHL1430P	•						•
AHL1430C	•						•
AHL1430R		•	•	•			•
AHIGL1430R		•	•				•
AHL1430FO		•	•				•
AHL1430FI	•						•
AHL1930P	•						•
AHL1930C	•						•
AHL1930R		•					•
AHL1930FO		•					•
AHL1930FI	•						•
AHL2230P	•						•
AHL2230PF	•						•
AHL2230C	•						•
AHL2230CF	•						•
AHL2230R		•	•				•
AHIGL2230R		•	•				•
AHL2230FO		•	•				•
AHL2230FI	•						•
AHL2030P	•						•
AHL2030C	•						•
AHL2030R		•					•
AHL2030FO		•					•
AHL2030FI	•						•
AHL2330P	•						•
AHL2330PF	•						•
AHL2330C	•						•
AHL2330CF	•						•
AHL2330R		•	•				•
AHIGL2330R		•	•				•
AHL2330FO		•	•				•
AHL2330FI	•						•
AHL2030C	•						•
AHL2030R		•					•
AHL2030FO		•					•
AHL2030FI	•						•
AHL2330P	•						•
AHL2330PF	•						•
AHL2330C	•						•
AHL2330CF	•						•
AHL2330R		•	•				•
AHIGL2330R		•	•				•
AHL2330FO		•	•				•
AHL2330FI	•						•

Parts are manufactured and designed in accordance with article 4 of the European Union's RoHS2 directive 2011/65/EU

**KEY:** cULus UL CSA FCS Fed Spec NOM NAFTA ROHS

Electrical Sector  
203 Cooper Circle  
Peachtree City, GA 30269  
United States  
Eaton.com  
Arrowhart.com

Electrical Sector  
Canada Operations  
5925 McLaughlin Road  
Mississauga, Ontario, L5R 1B8  
Canada  
EatonCanada.ca  
Arrowhart.com

Electrical Sector  
Mexico Operations  
Carr. Tlalnepantla -  
Cuautitlan Km 178 s/n  
Col. Villa Jardin esq.  
Cerrada 8 de Mayo  
Cuautitlan, Mexico CP 54800  
Mexico  
Eaton.mx  
Arrowhart.com

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

© 2014 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. E225-0049-13  
February 2014

Eaton is a registered trademark.  
All other trademarks are property  
of their respective owners.



*Powering Business Worldwide*