



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## D10250D Female Slpon 12-10 Non-Ip *Panduit Corporation*

|                  |   |
|------------------|---|
| Catalog Number   | D10250D   |
| Manufacturer     | Panduit Corporation   |
| Description      | The Vibration Resistant Female Disconnect In Metallic Brass Helps Overcome The Failures Caused By High Vibration. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 12-10 Awg (4.0-6.0 MM <sup>2</sup> ). It Is 0.72"(18.3 MM) Long and 0.3" (7.6 MM) Wide. The Disconnect Is Non-Insulated, Is Tin-Plated, Has A Standard Barrel Configuration and A Sleeved Barrel. It Comes In A Boxes Of 500. |
| Weight per unit  | 1.7 (lbs/each)  |
| Product Category | Small Terminals & Connectors  |

### Features

|                |               |
|----------------|---------------|
| connection     | Standard      |
| insulation     | Non-Insulated |
| Material       | Brass         |
| Voltage Rating | 2000          |
| Wire Size      | #10           |

### Material, Color, and Finish

|        |            |
|--------|------------|
| Finish | Tin-Plated |
|--------|------------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | FEMALE SLPON 12-10 NON-IP   |
| extra long description | PAN D10-250-D Pan-Term® D10-250-D L   |
| Long Description       | The vibration resistant female disconnect in metallic brass helps overcome the failures caused by high vibration. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 12-10 AWG (4.0-6.0 mm <sup>2</sup> ). It is 0.72"(18.3 mm) long and 0.3" (7.6 mm) wide. The disconnect is non-insulated, is tin-plated, has a standard barrel configuration and a sleeved barrel. It comes in a boxes of 500. |
| Product Type           | Pan-Term® D10-250-D Loose Piece Disconnect  |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | PANDUIT        |
| GTIN                      | 00074983822058 |
| Manufacturers Part Number | D10-250-D      |
| UPC                       | 074983822058   |

### Taxonomies, Classifications, and Categories

|                      |             |
|----------------------|-------------|
| Category Description | SPLIT BOLTS |
| Type                 | Disconnect  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 500  |
| Weight Per each | 1.68 |

## Uses, Certifications, and Standards

|                    |   |
|--------------------|---|
| Mounting           | 1932-09-01  |
| standard           | UL Recognized, UL Listed 20H3 E78522; CSA Certified LR31212 |
| Temperature Rating | 302 Degrees Fahrenheit (150 Degrees Celsius)                |