



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## D1060MW Electronic Minute Countdown Timer-White

Nsi Industries

Catalog Number	D1060MW
Manufacturer	Nsi Industries
Description	Interval Timer 60 Min 120V White
Weight per unit	0.3400 (lbs/each)
Product Category	Electronic Time Switches

### Features

action	SPST
Base	Screw
Contact Rating	120 VAC
Phase	Single Phase
Poles	1
Timing Range	10-20-30-60 Minutes

### Dimensions and Weight

Size	H=5.00 - W=3.00
------	-----------------

### Descriptions

Description	ELECTRONIC MINUTE COUNTDOWN TIMER-WHITE
extra long description	TORK D1060MW Interval Timer 60 Min
Features	Tork 10, 20, 30, 60 Minute Electronic Countdown Timer In-Wall Time Switch APPLICATIONS: Whole House Fans, Indoor/Outdoor Lighting, Bathroom Fans and Lights, Self Storage. FEATURES: COLOR: White VARIABLE TIMING: Button push changes time ON setting. 10, 20, 30, 60 minute. LED DISPLAY: Indicator moves to new range as timer counts down. TAMPER RESISTANT: Time ON interval preset. EASY SET: No adjustments, just wire and go, WIRING: Requires a neutral. CONTACT RATINGS: VOLTAGE: 125VAC /60Hz GENERAL PURPOSE: 120V
Long Description	Interval Timer 60 Min 120V White
Product Type	Interval Timer 60 Min 120V White
Special Features	White 10-20-30-60 Minute Electronic In Wall Time Switch

### Manufacturer Information

Brand	NSi
GTIN	00786261140265
Manufacturers Part Number	D1060MW
UPC	786261140265

### Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Electronic Auto Off In Wall Time Switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.34

## Uses, Certifications, and Standards

Application	NSI
environmental conditions	32-122 F
Frequency Rating	60 Hz
Mounting	Screw Mount
Operating Temperature	32-122 F
standard	cULus