



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH323NDK 100A/3P HD Fusible Safety Switch W/Neut 240V Nema *Eaton Corp*

Catalog Number	DH323NDK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 100 A, Nema 12/3R, Painted Galvanized Steel, Class H, Fusible With Neutral, Three-Pole, Four-Wire, 240 V, Max HP: 7.5, 15/ 15, 30/ 20 HP (1, 3PH @STD/TD/250 VDC), #14-#1/0 Cu/Al
Weight per unit	30.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	100
dimensions	10.2200 IN X 10.7600 IN X 24.9500 IN
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	240V

Dimensions and Weight

Depth	10.22
Height	24.95
Width	10.76

Descriptions

Description	100A/3P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA
extra long description	ETN DH323NDK 100A/3P HD FUS SftySw
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 100 A, NEMA 12/3R, Painted galvanized steel, Class H, Fusible with neutral, Three-pole, Four-wire, 240 V, Max Hp: 7.5, 15/ 15, 30/ 20 hp (1,3PH @Std/TD/250 Vdc), #14-#1/0 Cu/Al
Product Type	100A/3P HD Fus SftySw W/Neut 240V N12/3R

Manufacturer Information

Brand	Eaton
GTIN	00782113206332
Manufacturers Part Number	DH323NDK
UPC	782113206332



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Fusible safety switch

Packaging

Carton 1

Weight Per each 30

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

nema rating 12;3R

standard UL Listed,NEC 230.62 (C) Compliant Barrier