



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DSD933 1P Tumbler Switch *Crouse-Hinds*

| | |
|------------------|--|
| Catalog Number | DSD933 |
| Manufacturer | Crouse-Hinds |
| Description | Control Station Cover, Electrogalvanized Aluminum Acrylic Painted Feraloy Iron Alloy Material, 20 A, 120 to 277 V Ac, 2.5 LB |
| Weight per unit | 2.5 (lbs/each) |
| Product Category | Control Station Cover Assembl |

Features

| | |
|-----------------|-----------------------------------|
| amperage rating | 20A |
| dimensions | 5.3000 IN X 4.6000 IN X 6.7000 IN |
| Poles | Single-pole |

Descriptions

| | |
|------------------------|--|
| Description | 1P TUMBLER SWITCH |
| extra long description | CRS-H DSD933 DSD COVER DEVICE SUB A |
| Features | New DSDX series available with NEMA 4X protection for Class I, Division 2 hazardous areas.Crouse-Hinds series DSD and DSDX explosionproof cover and device sub-assemblies are for use with our EDS/EDSC back boxes and EDSCM modular multi-gang device bodies. DSD/DSDX covers are available with a wide variety of devices and configurations, including manual motor starters, front operated pushbuttons, general use snap switches, side operated pushbuttons, selector switches and pilot lights. Certified for use in CI |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Eaton |
| GTIN | 00782274235332 |
| UPC | 782274235332 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | STANDARD DUTY PUSHBUTTONS (10250H-) |
| Type | Snap switch cover and device sub-assembly |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 2.5 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Ind Facilities & Factories - Facility: Power Distribution and Control |
| Enclosure | Class I Div 1 2 Group B C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III, NEMA 3/7B/7C/7D/9E/9F/9G |
| standard | UL 1203, CSA C22.2 |