

Eaton CHEC24L125E

Catalog Number: CHEC24L125E

Eaton CH surge loadcenter, Provision only, Convertible, 125 A, E, 24 Circuits, #6-4/0 AWG

General specifications



Product Name	Catalog Number
Eaton CH surge loadcenter	CHEC24L125E
UPC	Product Length/Depth
782116200146	32 in
Product Height	Product Width
3 in	10 in
Product Weight	Warranty
7 lb	Limited lifetime
Certifications	Catalog Notes
UL Listed	Order Cover CHSUR8ES or CHSUR8EF separately. CHSPT2ULTRA and breaker not included

defaultTaxonomyAttributeLabel

Special features

Provision only

Type

Main lug only

Amperage Rating

125 A

Bus material

Aluminum

Number of circuits

32

Number of spaces

32

Phase

Single-phase

Wire size

#6-4/0 AWG

Box size

E

Enclosure

NEMA 1

Interrupt rating

25 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CHEC24L125E



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia