

Eaton CHP18B100R

Catalog Number: CHP18B100R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 100 A, X2, Copper, NEMA 3R, Metallic, CH, 36, 18, Three-wire, Single-phase, Overhead, 120/240 V



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP18B100R
UPC	Product Length/Depth
786689058548	21 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
22 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

defaultTaxonomyAttributeLabel

Special features

Cover included

Type

Main breaker

Amperage Rating

100 A

Bus material

Copper

Main circuit breaker

CH

Number of circuits

36

Number of spaces

18

Phase

Single-phase

Feed type

Overhead

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 3R

Enclosure material

Metallic

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP18B100R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)