

# Eaton CHP24L125X2

Catalog Number: CHP24L125X2

Eaton CH main lug loadcenters, PON, CH, 125 A, X2, Copper, I, NEMA 1 indoor, Steel, 25 kAIC, 48, 24, 3, Single-phase, 120/240 V, #6-2/0 AWG

## General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CHP24L125X2
UPC	Product Length/Depth
786689054311	21 in
Product Height	Product Width
4 in	14.3 in
Product Weight	Certifications
11.7 lb	UL 67

## Catalog Notes

Purchase Size X2 Cover Separately



## Product specifications

### Number of spaces

24

### Special features

PON

### Interrupt rating

25 kAIC

### Phase

Single-phase

### Bus material

Copper

### Enclosure

NEMA 1

### Amperage Rating

125 A

### Enclosure material

Steel

### Type

CH

### Number of wires

3

### Number of circuits

48

### Voltage rating

120/240 V

### Box size

X2

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP24L125X2](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)