



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E57LBL18T111 18MM STD Ind Prox 3W DC PNP *Eaton Corp*

Catalog Number	E57LBL18T111
Manufacturer	Eaton Corp
Description	Eaton E57 Premium+ Series Tubular Inductive Proximity Sensor Enclosure, 0.71 Dia, Dist. 5 MM, NC PNP Open Collector, 500 Ma At 6-30VDC, 6.6 FT. (2M) Cable, 6-48 VDC Input, <1% Accuracy, Short Circuit Protected, Shielded, 6.6 FT. (2M)
Weight per unit	0.3500 (lbs/each)
Product Category	Inductive Proximity Sensor

Features

dimensions	0.7100 IN X 0.7100 IN X 2.5400 IN
media	Yes

Descriptions

Description	18MM STD IND PROX 3W DC PNP
extra long description	ETN E57LBL18T111 18MM STD IND PROX
Features	E57G general purpose sensors are a cost-effective solution that is optimised to include only those functions that are necessary for basic, reliable sensing without lacking the performance or features you expect in an Eaton product. These sensors include various diameter options designed to fit a variety of applications.
Long Description	Eaton E57 Premium+ Series Tubular Inductive Proximity Sensor Enclosure, 0.71 dia, dist. 5 mm, NC PNP Open Collector, 500 mA at 6-30Vdc, 6.6 Ft. (2m) Cable, 6-48 Vdc input, <1% accuracy, Short circuit protected, Shielded, 6.6 Ft. (2m)
Product Type	18MM STD Ind Prox 3W DC PNP

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113743288
Manufacturers Part Number	E57LBL18T111
UPC	782113743288

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Inductive Proximity Sensor

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	0.35



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Stationary Mach Equip In Factory - Other Stationary Machinery
and Equipment - In Factory

standard

UL Listed, CSA Certified, CE Marked