



**SKU:** CLND-1-14-58

**UPC:** 0783669634785

**Features & Benefits:**

**Description:** Surecrimp Copper Compression Lug, Conductor Size 1, 2 Holes, 1/4in Bolt Size, 5/8in Hole Spacing, Long Barrel, No Sight Window, Tin Plated, UL, CSA

## Specs

### Additional Class Attributes

Barrel Marking	Ink
Barrel Type	Long
Connecting Angle	180°
Connection	Compression
Contains DE-OX®	No
Flared End	No
ILSCOs Die Catalog Number	ILD-37
ILSCOs Die Index Number	I-37
Mounting Hole Type	Thru
Narrow Tang	No
Number of Mounting Holes	2
Sight Window	No
Slotted	No
Tang End Shape	Square
Undrilled	No

### Dimensions

Barrel Length (IN)	1.375
Barrel Length (mm)	34.925
Dimension G (IN)	0.321
Dimension G (mm)	8.1534
Height (IN)	0.468
Height BX (IN)	2.25
Height (mm)	11.8872
Inside Diameter (IN)	0.359
Inside Diameter (mm)	9.1186
Length (IN)	3.142
Length (mm)	79.8068
Mounting Hole Diameter (IN)	0.281
Mounting Hole Diameter (mm)	7.1374
Mounting Hole Spacing (IN)	0.625
Mounting Hole Spacing (mm)	15.875
Outside Diameter (IN)	0.468
Outside Diameter (mm)	11.8872
Strip Length (IN)	1.437
Strip Length (mm)	36.4998
Tang Length (IN)	1.437
Tang Length (mm)	36.4998
Tang Thickness (IN)	0.109

Tang Thickness (mm)	2.7686
Tang Width (IN)	0.673
Tang Width (mm)	17.0942
Weight (LB)	0.0669266563982818
Weight BX (LB)	1.595
Width (IN)	0.673
Width BX (IN)	5
Width (mm)	17.0942

### Conductor Ranges

Conductor Range AL Stranded (Primary, run, main, line)	NA
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Stranded (Primary, run, main, line)	1 Str
Conductor Range AL Solid (Primary, run, main, line)	NA
Expanded Conductor Range	1 Str - 6 Str
Flex Conductor Range	2 G,H,I,K,M,DLO

### Material and Finish

Conductor Material	Copper
Connector Finish	Tin
Insulation	NA
Material	Copper

### Additional Technical Specifications

Conductor Type	Flex
----------------	------

### General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 10
Direct Burial	Yes
Dual Rated	No
NEMA Code	S-588-3
UPC Code	78366963478

### Bolt and Screw Sizes

Mounting Bolt/Stud Size	1/4
-------------------------	-----

### Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
NEBS Rating	Level 3
Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL Control Number	453G
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

**Environment and Temperature**

Temperature Rating 90°C

**Color**

Color Silver  
Color Code Green

**Voltage**

Voltage Rating 35 kV