



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ECD385 3/8" Drain *Crouse-Hinds*

Catalog Number	ECD385
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Ecd Universal Breather/Drain, Stainless Steel, 3/8"
Weight per unit	0.0300 (lbs/each)
Product Category	Sealing Bodies

### Features

dimensions	0.8800 IN X 0.8800 IN X 1.5300 IN
Material	Stainless Steel

### Dimensions and Weight

Size	3/8 in
------	--------

### Descriptions

Description	3/8" DRAIN
extra long description	CRS-H ECD385 3/8 UNV DRAIN OR BREAT
Features	Crouse-Hinds series ECD breathers and drains are for use in hazardous location conduit systems to drain accumulated condensate and provide ventilation to minimize condensation. A breather is installed in the top of an enclosure or in the upper section of a conduit system. A standard drain is installed in the bottom of an enclosure or in the lower section of a conduit system. At least one breather should be used with each drain. ECDs are also available in universal and combination models. A universal E
Long Description	Eaton Crouse-Hinds series ECD universal breather/drain, Stainless steel, 3/8"
Product Type	3/8 Unv Drain or Breather

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274250700
Manufacturers Part Number	ECD385
UPC	782274250700

### Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Universal breather/drain

### Packaging

Carton	1
Package	25
Weight Per each	0.03



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group B C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III
standard	UL 886, CSA C22.2