

Specifications

Eaton CRC6023BC

Eaton Crouse-Hinds series PowerMate CRC connector, 60A, 0.440-1.375", Two-wire, three-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc



Photo is representative

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Crouse-Hinds series PowerMate CRC connector |
| CATALOG NUMBER | CRC6023BC |
| UPC | 662276276581 |
| PRODUCT LENGTH/DEPTH | 8.3 in |
| PRODUCT HEIGHT | 2.32 in |
| PRODUCT WIDTH | 2.32 in |
| PRODUCT WEIGHT | 2.2 lb |



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

AMPERAGE RATING 60A

| | |
|-----------------------|-----------|
| | Locations |
| STANDARDS TYPE | NEC/CEC |
| NEMA RATING | 4X |

| | |
|-----------------------|----------------------|
| GROUNDING TYPE | Style 2 |
| CONFIGURATION | Two-wire, three-pole |
| CABLE DIAMETER | 0.440-1.375" |
| VOLTAGE RATING | 600 Vac/250 Vdc |
| MATERIAL | Copper-free aluminum |

Resources

3D CAD DRAWING PACKAGE [Eaton Crouse-Hinds CRC6023BC 3D drawing](#)

BROCHURES [PowerMate Drilling Pin and Sleeve Devices brochure](#)

CATALOGS [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

CERTIFICATION REPORTS [PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

INSTALLATION INSTRUCTIONS [IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

SPECIFICATIONS AND DATASHEETS [PowerMate Connectors](#)

[Eaton Specification Sheet - CRC6023BC](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

