

# Eaton ENR22201

Catalog Number: ENR22201

Eaton Crouse-Hinds series Ark-Gard ENR Value receptacle assembly, 20A, Double, 50-400 Hz, Copper-free aluminum, 5-20R, Two-gang, Dead end, 3/4", 125 Vac

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Ark-Gard ENR Value receptacle assembly	ENR22201
	<b>UPC</b>
	782274311036
<b>Product Length/Depth</b>	<b>Product Height</b>
7.56 in	6.72 in
<b>Product Width</b>	<b>Product Weight</b>
8 in	13.5 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

7

9

12

## Product specifications

### Number of gangs

Two-gang

### Amperage Rating

20A

### Voltage rating

125 Vac

### Style

Dead end

### Trade size

3/4"

### NEMA configuration

5-20R

### Cover type

Double

### Material

Copper-free aluminum

### Frequency rating

50-400 Hz

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds ENR22201 3D drawing](#)

### Catalogs

[Ark-Gard ENR Value Explosionproof NEMA Locking Devices catalog page](#)

### Certification reports

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices UL certification - ENR and ENP](#)

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices Canadian certification - ENR and ENP](#)

### Installation instructions

[IF 1424 - DSD, GFS, CPS and ENR Replacement Covers](#)

[IF 344 - Ark-Gard ENR Receptacles ENP Model M97 Plugs](#)

### Specifications and datasheets

[Eaton Specification Sheet - ENR22201](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)