



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG134072FBC21C DG1 480V FR4 N1 50HP 72A CT 60HP 87A VT W/ BC Eaton Corp

Catalog Number	DG134072FBC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 380-500V Input 37 KW, 50 HP CT, 3PH, 50/60 HZ, 72A, Output IP21/Type 1 Enclosure FR5 LCD Display Internal Emc Filter and DC Choke Ethernet
Weight per unit	80.0 (lbs/each)
Product Category	Ac Drives

Features

display	LCD graphical
Input Voltage	400 V, 380-500 V(-15%, +10%)
keypad	Included

Dimensions and Weight

Depth	28
Height	16.8
Width	14.7

Descriptions

Description	DG1 480V FR4 N1 50HP 72A CT 60HP 87A VT W/ BC
extra long description	ETN DG1-34072FB-C21C DG1,480V FR4,N
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 380-500V input 37 kW, 50 Hp CT, 3PH, 50/60 Hz, 72A, output IP21/type 1 enclosure FR5 LCD display Internal EMC filter and DC choke EtherNet
Product Type	DG1, 480V FR4, N1, 50HP, 72A/60HP, 87A, BC

Manufacturer Information

Brand	Eaton
GTIN	00786685887739
Manufacturers Part Number	DG1-34072FB-C21C
UPC	786685887739

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Variable Frequency Drive



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	80

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure standard	IP21/type 1 enclosure EN 62061,EN ISO 13849-1,UL 508C,UL Listed,cUL Listed,IEC 61508,C-Tick Compliant,GoST-R,CE Marked,RoHS Compliant