



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EYD816 3" Male/Female Drain Seal *Crouse-Hinds*

Catalog Number	EYD816
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Eyd Conduit Sealing Fitting With Drain, Male and Female, Feraloy Iron Alloy and/or Ductile Iron, Vertical Only, Group B Rated, 3"
Weight per unit	13.4 (lbs/each)
Product Category	Sealing Bodies

Features

connection	Female Threaded, Female Threaded
dimensions	4.2500 IN X 4.2500 IN X 8.5000 IN

Material, Color, and Finish

Finish	Untreated
--------	-----------

Descriptions

Description	3" MALE/FEMALE DRAIN SEAL
extra long description	CRS-H EYD816 3 NPT GRP B THRU MALE/
Features	In addition to restricting the passage of gases, vapors or flames from one portion of the electrical installation to another, Crouse-Hinds series EYD and EZD drain sealing fittings prevent accumulation of condensate above the seal. They are installed in vertical conduit runs and at low points in conduit systems.
Long Description	Eaton Crouse-Hinds series EYD conduit sealing fitting with drain, Male and female, Feraloy iron alloy and/or ductile iron, Vertical only, Group B rated, 3"
Product Type	3 NPT GRP B Thru Male/Fem Iron Drain
Special Features	With Drain, Vertical Position

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274365244
Manufacturers Part Number	EYD816
UPC	782274365244

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Conduit sealing fitting with drain

Packaging

Carton	1
Weight Per each	13.35



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group C D, Class II Div 1 2 Group F G, Class III
standard	UL 886, CSA C22.2