DLR56

5"& 6" Recessed LED Downlight

Product Description

The DLR56 from NICOR is a 5" & 6" recessed LED downlight that is ideal for both retrofit and new construction alike. Redesigned to boost energy efficiency, the LED light engine draws only 13 watts while producing over 800 lumens. The enriched 90+ CRI provides superior color quality, along with an R9 greater than 60*. Not only is the light quality better, but this design improvement meets new industry standards like Title 24.

Construction

- · Spun aluminum trim routes heat away from electrical components
- Low profile, integrated driver, allows for use in shallow housings

Optical System

• Polystyrene diffuser and reflector cone create a uniform light distribution that reduces glare without sacrificing lumen output

- \bullet Utilizes high performing LEDs with greater than 90 CRI and an R9 greater than 60^{\ast}
- · Dimmable to 5% with most standard triac dimmers
- Operating temperature rating of 0°F to 120°F (-18°C to 49°C)
- Input voltage of 120V
- Lifetime rated for greater than 53,000 hours
- LM-79, LM-80 testing performed in accordance with IESNA standards
- Meets FCC Part 15, Subpart B, Class B standards for conducted and radiated emissions.

- Exterior white powder coat finish, with interior high reflective finish
- · Also available in Black, Oil-Rubbed Bronze and Nickel

Installation

- Compatible with most 5" and 6" recessed housings
- Quick and easy installation with a screw-in Edison base (GU24 socket string available) and torsion spring mounting system


· 5-year limited system warranty standard

* not available in 5000K

Project			
Date			
Туре			

Date


















Photometric Data

DLR56 2700K 800Lm

Input Voltage (VAC)	120V
System Level Power (W)	12.4
Delivered Lumens (Lm)	845
System Efficacy (Lm/W)	68.1
Correlated Color Temp (K)	2774
Color Rendering Index (CRI)	93
Beam Angle	98°
Spacing Criteria	1.18



Intensity Summary (Candle Power)			
Angle	Mean CP		
0	367		
5	365		
15	347		
25	312		
35	265		
45	212		
55	151		
65	79		
75	17		
85	4		
90	0		

/3	17			
85	4	Zonal Lumen Summary		
90	0			
		Zone	Lumens	% of Luminaire
CCT Data Multiplier		0-30	276	32.7%
		0-40	442	52.3%
DLR56-3008-120-3K	1.020	0-60	741	87.6%
DLR56-3008-120-4K	1.072 0-90 90-180	0-90	844	99.8%
		90-180	1	0.2%
DLR56-3008-120-5K	1.182	0-180	845	100.0%

Mounted height

(Feet)

6


10

12

Fixture tested per LM-79-08. Photometric data is of the performance of a representative fixture. Results may vary in the field.

DLR56 2700K 1200Lm

Input Voltage (VAC)	120V
System Level Power (W)	18.0
Delivered Lumens (Lm)	1230
System Efficacy (Lm/W)	68.3
Correlated Color Temp (K)	2727
Color Rendering Index (CRI)	93
Beam Angle	98°
Spacing Criteria	1.18



Intensity Summary (Candle Power)			
Angle	Mean CP		
0	554		
5	551		
15	523		
25	471		
35	402		
45	319		
55	212		
65	93		
75	24		
85	6		
90	1		

CCT Data Multiplier				
DLR56-3012-120-3K	1.020			
DLR56-3012-120-4K	1.072			
DLR56-3012-120-5K	1.182			

Cone of Light Tabulation					
Mounted height (Feet)	Footcandles Beam Center	Diameter (Feet)			
4	34.6	4.7			
6	15.4	7.1			
8	8.7	9.4			
10	5.5	11.8			
12	3.8	14.2			
14	2.8	16.5			
16	2.2	18.9			

Cone of Light Tabulation

Footcandles

Beam Center

23.0

10.2

5.7

3.7

2.5

1.9

Diameter

(Feet)

4.7

7.1

9.4

11.8

14.2

16.5 18.9

Zonal Lumen Summary					
Zone	Lumens	% of Luminaire			
0-30	417	33.9%			
0-40	668	54.3%			
0-60	1101	89.5%			
0-90	1230	100.0%			
90-180	0	0.0%			
0-180	1230	100.0%			

 $Fixture\ tested\ per\ LM-79-08.\ Photometric\ data\ is\ of\ the\ performance\ of\ a\ representative\ fixture.\ Results\ may\ vary\ in\ the\ field.$

Performance Data				
Model Number	Lumens	Watts	Lumens/Watt	
DLR56-3008-120-2K	845	12.4	68.1	
DLR56-3008-120-3K	864	12.4	69.5	
DLR56-3008-120-4K	905	12.4	73.0	
DLR56-3008-120-5K	999	12.4	80.6	
DLR56-3012-120-2K	1230	18.0	68.3	
DLR56-3012-120-3K	1254	18.0	69.7	
DLR56-3012-120-4K	1318	18.0	73.2	
DLR56-3012-120-5K	1454	18.0	80.8	

Recommended Dimmers*	
Lutron Skylark SCL-153P	17014-LED-ID
Lutron DIVA DVCL-153P	17014AR-LED-ID
Lutron DIVA DVELV-300P	
Lutron DIVA DVELV-303P	
Lutron Skylark SELV-300P	

Lutron Skylark SELV-300P	
at a complete list. Check compatibility before installation	

Housing Compatibility*			
6" LED IC AIRTIGHT NEW CONST. HOUSING			
6" LED IC AIRTIGHT REMODEL HOUSING			
MOST 5" OR 6" RECESSED HOUSINGS			



Ordering Information				Example: DLR56-3008-120-3K-WH	
Series	Version	Voltage	CCT's	Trim Color	
DLR56	3008 (800Lm)	120 (120V)	2K (2700 K)	WH (White)	
	3012 (1200Lm)		3K (3000 K)	WH-BF (White Baffle)*	
			4K (4000 K)	BK (Black)	
			5K (5000 K)	NK (Nickel)	
				OB (Oil-Rubbed Bronze)	

^{*}Baffle available on 2K and 3K only

Specifications and dimensions subject to change without notice.

Accessories	accessories sold separately		
GU24 Socket String	GU24-IDEAL-SKT-STR		

