



DSD957 PB CVR Assy Csa Apr

Crouse-Hinds

Catalog Number	DSD957
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series DSD Blank Cover and Device Sub-Assembly, Feraloy Iron Alloy, Blank Cover, No Operators
Weight per unit	3.3 (lbs/each)
Product Category	Control Station Cover Assemblies

Features

dimensions	5.3000 IN X 4.6000 IN X 6.7000 IN
Voltage Rating	600 VAC

Descriptions

Description	PB CVR ASSY CSA APR
extra long description	CRS-H DSD957 DSD COVER AND DEVICE S
Features	New DSDX series available with NEMA 4X protection for Class I, Division 2 hazardous areas. Crouse-Hinds series DSD and DSDX explosionproof cover and device sub-assemblies are for use with our EDS/EDSC back boxes and EDSCM modular multi-gang device bodies. DSD/DSDX covers are available with a wide variety of devices and configurations, including manual motor starters, front operated pushbuttons, general use snap switches, side operated pushbuttons, selector switches and pilot lights. Certified for use in CI
Long Description	Eaton Crouse-Hinds series DSD blank cover and device sub-assembly, Feraloy iron alloy, Blank cover, no operators
Product Type	DSD Cover and Device Sub-Assemblies
Special Features	Blank cover, no operators

Manufacturer Information

Brand	Eaton
GTIN	00782274045269
Manufacturers Part Number	DSD957
Model	Blank cover and device sub-assembly
UPC	782274045269

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION MOTOR CONTROL
----------------------	----------------------------------

Packaging

Carton	1
Weight Per each	3.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Ind Facilities & Factories - Facility: Power Distribution and Control

Enclosure

Class I Div 1 2 Group B C D, Class II Div 1 Group E F G, Class II Div 2

standard

Group F G, Class III, NEMA 3/7B/7C/7D/9E/9F/9G

UL 1203, CSA C22.2