




GE
Lighting

13767 - F84T12D/HO 15PK

GE Daylight T12



CAUTIONS & WARNINGS

Caution


- Lamp may shatter and cause injury if broken
 - Wear safety glasses and gloves when handling lamp.
 - Do not use excessive force when installing lamp.

Warning


- Risk of Electric Shock
 - Turn power off before inspection, installation or removal.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution



Graphs_Lamp Mortality



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T12
Base	Recessed Double Contact (R17d)
Rated Life	12000.0 hrs
Bulb Material	Soda lime
Starting Temperature (MIN)	-29.0 °C
LEED-EB MR Credit	1325 picograms Hg per mean lumen hour
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	6500.0
Mean Lumens	5660.0
Nominal Initial Lumens per Watt	65
Color Temperature	6500.0 K
Color Rendering Index (CRI)	75.0

ELECTRICAL CHARACTERISTICS

Wattage	100.0
Voltage	135.0
Open Circuit Voltage (rapid start) Min @ Temperature	430 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.25
Cathode Resistance Ratio - Rh/Rc (MAX)	6.5
Current Crest Factor (MAX)	1.7

DIMENSIONS

Maximum Overall Length (MOL)	84.0000 in(2133.6 mm)
Minimum Overall Length	81.7200 in(2075.7 mm)
Nominal Length	84.000 in(2133.6 mm)
Bulb Diameter (DIA) (MIN)	1.410 in(35.8 mm)
Bulb Diameter (DIA) (MAX)	1.590 in(40.4 mm)
Bulb Diameter (DIA)	1.500 in(38.1 mm)
End of Base Pin to End of Opposite Pin End (C)	81.720 in(2075.7 mm)

PRODUCT INFORMATION



Product Code	13767
Description	F84T12D/HO 15PK
ANSI Code	1018-1
Standard Package	Case
Standard Package GTIN	10043168137673
Standard Package Quantity	15
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	15
UPC	043168137676



GE
Lighting

13767 - F84T12D/HO 15PK

GE Daylight T12



CAUTIONS & WARNINGS

Caution


- Lamp may shatter and cause injury if broken
 - Wear safety glasses and gloves when handling lamp.
 - Do not use excessive force when installing lamp.

Warning


- Risk of Electric Shock
 - Turn power off before inspection, installation or removal.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution



Graphs_Lamp Mortality



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T12
Base	Recessed Double Contact (R17d)
Rated Life	12000.0 hrs
Bulb Material	Soda lime
Starting Temperature (MIN)	-29.0 °C
LEED-EB MR Credit	1325 picograms Hg per mean lumen hour
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	6500.0
Mean Lumens	5660.0
Nominal Initial Lumens per Watt	65
Color Temperature	6500.0 K
Color Rendering Index (CRI)	75.0

ELECTRICAL CHARACTERISTICS

Wattage	100.0
Voltage	135.0
Open Circuit Voltage (rapid start) Min @ Temperature	430 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.25
Cathode Resistance Ratio - Rh/Rc (MAX)	6.5
Current Crest Factor (MAX)	1.7

DIMENSIONS

Maximum Overall Length (MOL)	84.0000 in(2133.6 mm)
Minimum Overall Length	81.7200 in(2075.7 mm)
Nominal Length	84.000 in(2133.6 mm)
Bulb Diameter (DIA) (MIN)	1.410 in(35.8 mm)
Bulb Diameter (DIA) (MAX)	1.590 in(40.4 mm)
Bulb Diameter (DIA)	1.500 in(38.1 mm)
End of Base Pin to End of Opposite Pin End (C)	81.720 in(2075.7 mm)

PRODUCT INFORMATION

Product Code	13767
Description	F84T12D/HO 15PK
ANSI Code	1018-1
Standard Package	Case
Standard Package GTIN	10043168137673
Standard Package Quantity	15
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	15
UPC	043168137676